



Model 6475 is a set of two each of the following five probes that fit Pomona probes that use the .054Ø test probe tips. Individual replacement probe tips are available in packages of 10.

FEATURES:

Model 6221 Sharp Stainless-Steel Tip

- Rigid stainless-steel tip is hardened for heavy duty use
- Sharp, hardened point will penetrate conformal coatings and heavy surface contamination

Model 6222 Nickel Plated Brass Tip

- Rigid nickel plated brass tip is perfect for precision measurement
- Sharp tip resists wear
- This is the best tip for every day use

Model 6219 Triple Point Micro Tip

- Gold plated pogo pin tip has .018" diameter Tip with three sharp points
- Sharp point digs into soft metals like solder for low resistance connections
- Self-cleaning tip pierces surface coatings or contamination
- Pogo pin helps to hold the test point even if the probe is moved

Model 6218 Sharp Point Tip

- Gold plated pogo pin tip has a sharp tapered point
- Sharp point digs into soft metals like solder for low resistance connections

- Self-cleaning tip pierces surface coatings or contamination
- Pogo pin helps to hold the test point even if the probe is moved

Model 6220 Triple Point Tip

- Gold plated pogo pin tip has three sharp points
- Sharp point digs into soft metals like solder for low resistance connections
- Self-cleaning tip pierces surface coatings or contamination
- Pogo pin helps to hold the test point even if the probe is moved

MATERIALS:

Retractable Tips: Beryllium Copper with Gold Plate
Fixed Tips: 6221 Stainless-Steel, 6222 Brass with Nickel Plate

RATINGS:

Maximum Current: 5 Amperes

ORDERING INFORMATION: Model 6475

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ±.005" (.127 mm).
All specifications are to the latest revisions. Specifications are subject to change without notice.
Registered trademarks are the property of their respective companies. Made in USA

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pomona:

[6219](#) [6218](#) [6220](#) [6222](#) [6221](#)