



AMPROBE®

AM-220 & AM-240 Digital Multimeters



- Measure: AC/DC Voltage up to 600V, AC/DC Current up to 10A, Resistance, Capacitance, Frequency, Duty Cycle
- Temperature measurement with selectable F/C (AM-240 only)
- AC/DC micro Amps for sensors diagnosis
- Large Backlight LCD Display
- Diode Test
- Audible Continuity Test
- Data Hold
- MAX, MIN and Relative measurements
- Auto and Manual Ranging
- Auto Power Off (can be disabled)
- Tilt stand
- Safety: CAT III 600V

Feature	AM-220	AM-240
AC/DC Voltage		400mV 4.000/40.00/400.0/600 V
AC/DC Current		400/4000µA 40/400 mA 4/10 A
Resistance		400.0Ω 4.000/40.00/400.0 kΩ 4.000MΩ/40.00 MΩ
Capacitance		40.00/400.0 nF 4.000/40.00/400.0/4000µF
Frequency		10.00/ 100.0/1000 Hz 10.00/100.0/1000 kHz 10M Hz
Duty Cycle		0.1%_99.9%
Temperature		-58° to 1382°F (-50° to 750°C)

OPTIONAL ACCESSORIES	PART NUMBER
3000AAC Flexible Clamp-on Attachment	ACF-3000 AK
1000A TRMS AC/DC Clamp-on Attachment	A-1000
600A AC/DC Clamp-on Attachment	CT-600 AC/DC
400A AC Clamp-on Attachment	A400
Milli-Amps to 30A AC/DC Clamp-on Attachment	CT-30
Dual input Thermocouple adapter with two thermocouples -50°F to 600°F	DKTA-620 and two of TPK-56
Single Input Thermocouple Temperature Adapter (Recommended for AM-220)	TMA-K
Alligator Clips (For test leads)	VRC-320
Carrying Case	SV-U

REPLACEMENT PARTS	PART NUMBER
<i>(supplied with product)</i>	
Thermocouple (AM-240 Only)	TPK-59
Test leads with set of alligator clips <i>(alligator clips are not supplied with product)</i>	MTL-90B
Fuse 250V, 0.5A	5X20-250.5
Fuse 250V, 10A	6X32-250V10A
Instruction Manual	www.AMPROBE.com

www.AMPROBE.com



AMPROBE®

AM-220 & AM-240 Digital Multimeters

DC VOLTAGE		
RANGE	Accuracy	Resolution
400mV	± (0.5%+2)	0.1mV
4V		1mV
40V		10mV
400V		100mV
600V	± (0.8%+3)	1V
Overload protection: 600V DC or AC RMS Impedance: 10MΩ, More than 100MΩ on 400mV range		

AC VOLTAGE		
RANGE	Accuracy	Resolution
400mV	± (1.5%+3)	0.1mV
4V	± (1.0%+2)	1mV
40V		10mV
400V		100mV
600V	± (1.5%+3)	1V
Average sensing, calibrated to RMS of sine wave Frequency: 40 ~ 400Hz Overload protection: 600V DC or AC RMS Impedance: 10MΩ , More than 100MΩ on 400mV range		

DC CURRENT		
RANGE	Accuracy	Resolution
400μA	± (1.2%+3)	0.1μA
4000μA		1μA
40mA		10μA
400mA		100μA
4A	1mA	1mA
10A		10mA
Overload protection: 0.5A/250V, 10A/250V fuse		

AC CURRENT		
RANGE	Accuracy	Resolution
400μA	± (1.5%+3)	0.1μA
4000μA		1μA
40mA		10μA
400mA		100μA
4A	± (2.5%+5)	1mA
10A		10mA
Average sensing, calibrated to RMS of sine wave Frequency: 40~400Hz Overload protection: 0.5A/250V, 10A/250V fuse		

RESISTANCE		
RANGE	Accuracy	Resolution
400Ω	± (1.0%+2)	0.1Ω
4kΩ		1Ω
40kΩ		10Ω
400kΩ		100Ω
4MΩ		1kΩ
40MΩ	± (2.0%+3)	10kΩ
Overload protection: 250V DC or AC RMS		

CAPACITANCE		
RANGE	Accuracy	Resolution
40nF	± (3.0%+10)	10pF
400nF	± (2.5%+5)	100pF
4μF		1nF
40μF	± (5.0%+10)	10nF
400μF		100nF
4000μF		10μF
Overload protection: 250V DC or AC RMS		

DIODE AND AUDIBLE CONTINUITY TEST		
RANGE	Description	Test Condition
→→	Display read approximately forward voltage of diode	Forward DC current approx. 0.4mA Reversed DC voltage approx. 2.8V
	Built-in buzzer sounds if resistance is less than 50Ω	Open circuit voltage approx. 0.5V
Overload protection: 250V DC or AC RMS		

FREQUENCY		
RANGE	Accuracy	Resolution
10Hz	± (0.1%+5)	0.01Hz
100Hz		0.1Hz
1000Hz		1Hz
10kHz		10Hz
100kHz		100Hz
1000kHz		1kHz
10MHz		10kHz
Sensitivity: sine wave 0.6V RMS (10MHz: 1.5V RMS) Overload protection: 250V DC or AC RMS		

Miramar, FL 33025 • Toll Free: 800-327-5060 • Phone: 954-499-5400 • Fax: 954-499-5418 • www.Amprobe.com

www.AMPROBE.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[AMPROBE:](#)

[AM-240](#)