


Model 3269
Adapter, BNC Female to Miniature Double Banana Plug**Features**

- Allows a BNC male connection to be used with equipment having 0.5" (12.7mm) spaced miniature 0.104" (2.4mm) diameter banana jacks
- Excellent for adapting test equipment to BNC coaxial cables

Materials

Upper Conn: BNC Female

Finish: Tarnish Resistant

Center Contact: Gold Plated

Insulation: ABS molded to BNC male and Banana Plug

Color: Black

Lower Conn: Miniature Double Banana Plug

Material: Spring, Beryllium Copper

Plug Body: Brass

Finish: Gold Plated

Ratings

Operating Temperature: +50° C. (+122° F.) Max.

Operating Voltage: 500 Vrms, Maximum voltage for hands free use in controlled voltage environment.
For CE compliance, do not hold in hand when voltages exceed 30V AC / 60V DC.

Ordering Information: Model 3269

USA: Sales: 800-490-2361
Technical Support: technicalsupport@pomonatest.com
Fax: 425-446-5844
Europe: 31-(0) 40 2675 150 **International:** 425-446-5500
Where to Buy: www.pomonaelectronics.com

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ±.005" (.127 mm). All specifications are to the latest revisions. Specifications are subject to change without notice. Registered trademarks are the property of their respective companies.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pomona:

3269