

Test Jacks 4 mm System



Type

BO 10

4mm panel mount test jack, nickel plated brass, M6 thread screw terminal. panel thickness 1.5-8mm

Pin Diameter

4 mm

PART NO. / Housing color

930160000



BU 10 / BU 10 Au

4mm panel mount test jack, nickel/gold plated brass, M6 thread screw/ solder terminal. max. panel thickness 11mm

4 mm

930147000

(Nickel plated)

930147700

(Gold plated)



Technical Data

Contact Type	jack Ø 4 mm
Connection Type	M6 thread
Voltage Rating	30 VAC / 60 VDC
Measurement Category (IEC61010)	CAT I
Current Rating*	16 A
Contact Resistance	5 mOhm
Mounting Type	screw thread M6
Material Specifications	
Jack Body	nickel plated brass
Contact Spring	–
Housing	–
Environmental Conditions	
Temperature Range	-25°C to +70 °C (-13 to 158°F)
Flamability Rating	
Housing	–

jack Ø 4 mm
M6 thread, solder terminal
30 VAC / 60 VDC
CAT I
16 A
5 mOhm
screw thread M6
nickel / gold plated brass
–
–
-25°C to +70 °C (-13 to 158°F)
–

Drawing

Measurements are shown in millimeters.
Multiply by 0.03937 to convert to inches.



* Please consider derating graph on page 80.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Altech:](#)

[930147000](#) [930147700](#) [930160000](#)