

Test Jacks 4 mm System



Type

PKI 100

4mm insulated panel mount binding post with 2mm cross hole, nickel plated brass, M4 thread terminal, max. panel thickness 3.5mm.

Pin Diameter

4 mm

PART NO. / Housing color

● 930757100
● 930757101
● 930757102
● 930757103
● 930757104
● 930757188



PKI 10 A / PKI 10 A Au

4mm insulated panel mount binding post with 2mm cross hole, nickel/ gold plated brass, M4 thread terminal, max. panel thickness 2mm

4 mm

Nickel Plated

● 930103100
● 930103101
● 930103102
● 930103103
● 930103104
● 930103188

Gold Plated

● 930103700
● 930103701
● 930103702
● 930103703
● 930103704
● 930103788

Technical Data

Contact Type jack Ø 4 mm, cross hole Ø 2 mm
Connection Type M4 thread terminal
Voltage Rating 30 VAC / 60 VDC
Measurement Category (IEC61010) CAT I
Current Rating* 32 A
Contact Resistance 2 mOhm
Mounting Type screw thread M4

Material Specifications

Jack Body nickel plated brass
Contact Spring –
Housing Polyamide

Environmental Conditions

Temperature Range -25°C to +100 °C (-13 to 212°F)

Flamability Rating

Housing UL 94 V-2

jack Ø 4 mm, cross hole Ø 2 mm
M 4 thread terminal
30 VAC / 60 VDC
CAT I
35 A
2 mOhm
screw thread M4

nickel plated brass | gold plated brass

–



PF

-25°C to +100 °C (-13 to 212°F)

–

Drawing

Measurements are shown in millimeters.
Multiply by 0.03937 to convert to inches.



* Please consider derating graph on page 80.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Altech:](#)

[930757100](#) [930103700](#) [930103188](#) [930757103](#) [930103103](#) [930103703](#) [930757188](#) [930103101](#) [930103702](#)
[930103788](#) [930757101](#) [930103102](#) [930103704](#) [930103100](#) [930103701](#) [930757104](#) [930757102](#) [930103104](#)