



Test Jacks 4 mm System

Type

KUN S

4mm Safety adapter, nickel plated brass with screw terminal 0.5-1.5mm², IEC61010 1000V system



Pin Diameter

PART NO. / Housing color

4 mm

- 934096100
- 934096101
- 934096102
- 934096103
- 934096104

SEB 2600 G M4

4mm panel mount safety Jack, touch proof, gold plated brass with M4 thread/ solder terminal, max. panel thickness 6mm



4 mm

- 972354100
- 972354101
- 972354102
- 972354103
- 972354104
- 972354105
- 972354106
- 972354107
- 972354109
- 972354188



Technical Data

Contact Type	jack Ø 4 mm
Connection Type	screw terminal max. 1.5mm ²
Voltage Rating	AC/DC 1000 V
Measurement Category (IEC61010)	CAT III
Current Rating*	24 A
Contact Resistance	–
Mounting Type	–
Material Specifications	
Jack Body	nickel plated brass
Contact Spring	–
Housing	Polyamide
Environmental Conditions	
Temperature Range	-15°C to +70°C (5 to 158°F)
Flamability Rating	
Housing	UL 94 V-2

jack Ø 4 mm
M4 thread, solder terminal
AC/DC 1000 V
CAT III
32 A
5 mOhm
screw thread M12
gold plated brass
–
Polymide
-40°C to +80°C (-40 to 176°F)
UL 94 V-2

Drawing

Measurements are shown in millimeters.
Multiply by 0.03937 to convert to inches.



* Please consider derating graph on page 80.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Altech:](#)

[934096103](#) [934096104](#) [972354103](#) [972354105](#) [972354104](#) [972354109](#) [972354102](#) [934096100](#) [972354100](#)
[972354188](#) [972354107](#) [972354106](#) [934096101](#) [972354101](#) [934096102](#)