

HIGHLIGHTS


FEATURES

- 2, 3, 4 Connection Ground Terminals
- Yellow / Green Color as per Industry Standard
- Snap-On feet
- 3 Marking Locations


APPLICATIONS

- Grounding Applications


CXG2.5



CXG4



CXG6



Dimensions

	CXG2.5	CXG4	CXG6
Width	5 mm	6 mm	8 mm
Length	49.7 mm	54.8 mm	62.1 mm
Height w DIN Rail	35 x 7.5 mm 35 x 15 mm	38.0 mm 45.5 mm	43.0 mm 50.5 mm
Weight per piece	8.4 g	11.0 g	20.2 g

Technical Data/Ratings

Approvals	    	  	  	  		
Wire Size (solid stranded)	24-12 AWG	0.2-2.5 mm ²	24-10 AWG	0.2-4 mm ²	24-8 AWG	0.2-6 mm ²
Voltage Rating	600 V	1000V AC/DC	600 V	1000V AC/DC	600 V	1000V AC/DC
Current Rating	—	—	—	—	—	—
Insulation Material	Polyamide 66		Polyamide 66		Polyamide 66	

Installation Instructions

Wire Stripping Length	10 mm	10 mm	14 mm
Screwdriver	Flat Head 0.5 x 3 mm	Flat Head 0.6 x 3.5 mm	Flat Head 0.8 x 4 mm





Terminal Blocks

	Cat. No.	Std. Pk.	Cat. No.	Std. Pk.	Cat. No.	Std. Pk.
Yellow / Green	CXG2.5	100	CXG4	100	CXG6	100

Accessories

	Cat. No.	Std. Pk.	Cat. No.	Std. Pk.	Cat. No.	Std. Pk.
End Plate	EPCX2.5	50	EPCX4	50	EPCX6	50
Partition Plate	PPCX4	20	PPCX4	20	PPCX10	20
DIN Rail	2511120	20	2511120	20	2511120	20
	CA701-15/S	20	CA701-15/S	20	CA701-15/S	20
End Stop	CA702	50	CA702	50	CA702	50
	CA802	50	CA802	50	CA802	50
	CA103	50	CA103	50	CA103	50
Shorting Link/ Jumpers	JX2.5/2	100	JX4/2	100	JX6/2	100
	JX2.5/3	50	JX4/3	50	JX6/3	50
	JX2.5/4	50	JX4/4	50	JX6/4	50
	JX2.5/5	50	—	—	—	—
	JX2.5/6	10	—	—	—	—
	JX2.5/7	10	—	—	—	—
	JX2.5/8	10	JX4/8	50	—	—
	JX2.5/10	10	JX4/10	10	JX6/10	10
	—	—	JX4/16	10	—	—
Test Plug	TX2.5	50	TX4	50	TX6	50
Marking Tag	MT5	100	MT6	100	MT8	100
Warning Label	WLX2.5	50	WLX4	100	WLX6	100

MULTIPLE CONNECTION GROUND / EARTH TERMINAL BLOCKS

CXG10

CXG2.5/3

CXG2.5/4

CXG4/3


Dimensions

	CXG10	CXG2.5/3	CXG2.5/4	CXG4/3
2 Connection Ground Terminal 2 Jumper Channels				
Width	10 mm	5 mm	5 mm	6 mm
Length	62.1 mm	62.2 mm	74.7 mm	70.5 mm
Height w DIN Rail 35 x 7.5 mm 35 x 15 mm	43.0 mm 50.5 mm	38.0 mm 45.5 mm	38.0 mm 45.5 mm	38.0 mm 45.5 mm
Weight per piece	29.4 g	10.2 g	12.4 g	14.0 g

Technical Data/Ratings

Approvals CE, ENEC, TUV, Lloyd's Register, IEC	C US E220514, C US 60947-7-1, IEC	C US E220514, C US 60947-7-1, IEC	C US E220514, C US 60947-7-1, IEC	C US E220514, C US 60947-7-1, IEC
Wire Size (solid stranded)	24-6 AWG, 0.2-10 mm ²	24-12 AWG, 0.2-2.5 mm ²	24-12 AWG, 0.2-2.5 mm ²	24-10 AWG, 0.2-4 mm ²
Voltage Rating	600 V, 1000V AC/DC	600 V, 1000V AC/DC	600 V, 1000V AC/DC	600 V, 1000V AC/DC
Current Rating	—	—	—	—
Insulation Material	Polyamide 66	Polyamide 66	Polyamide 66	Polyamide 66

Installation Instructions

Wire Stripping Length	18 mm	10 mm	10 mm	10 mm
Screwdriver	Flat Head 0.8 x 4 mm	Flat Head 0.5 x 3 mm	Flat Head 0.5 x 3 mm	Flat Head 0.6 x 3.5 mm


Terminal Blocks

	Cat. No.	Std. Pk.	Cat. No.	Std. Pk.	Cat. No.	Std. Pk.	Cat. No.	Std. Pk.
Yellow / Green	CXG10	50	CXG2.5/3	100	CXG2.5/4	50	CXG4/3	50



Accessories

	Cat. No.	Std. Pk.	Cat. No.	Std. Pk.	Cat. No.	Std. Pk.	Cat. No.	Std. Pk.
End Plate	EPCX10	20	EPCX2.5/3	50	EPCX2.5/4	20	EPCX4/3	20
Partition Plate	PPCX10	20	PPCX4/3	20	PPCX4/4	20	PPCX4/3	20
DIN Rail	2511120 CA701-15/S	20 20	2511120 CA701-15/S	20 10	2511120 CA701-15/S	20 10	2511120 CA701-15/S	20 10
End Stop	CA702 CA802 CA103	50 50 50	CA702 CA802 CA103	50 50 50	CA702 CA802 CA103	50 50 50	CA702 CA802 CA103	50 50 50
Shorting Link/ Jumpers	JX10/2 — — — — — — — — — —	20 — — — — — — — — — —	JX2.5/2 JX2.5/3 JX2.5/4 JX2.5/5 JX2.5/6 JX2.5/7 JX2.5/8 JX2.5/10 —	100 50 50 50 10 10 10 10 —	JX4/2 JX4/3 JX4/4 — — — JX4/8 JX4/10 JX4/16	100 50 50 — — — 50 10 10	JX6/2 JX6/3 JX6/4 — — — — JX6/10 —	100 50 50 — — — — 10 —
Test Plug	TX10	50	TX2.5	50	TX2.5	50	TX4	50
Marking Tag Warning Label	MT10 WLX10	100 100	MT5 WLX2.5	100 100	MT5 WLX2.5	100 100	MT6 WLX4	100 100



CXG4/4



CXG6/3



CXG10/3



Dimensions

	CXG4/4	CXG6/3	CXG10/3
Width	6 mm	8 mm	10 mm
Length	86.2 mm	82.2 mm	82.2 mm
Height w DIN Rail	35 x 7.5 mm 35 x 15 mm	38.0 mm 45.5 mm	43.0 mm 50.5 mm
Weight per piece	17.2 g	26.0 g	35.0 g

Technical Data/Ratings

Approvals			
Wire Size (solid stranded)	24-10 AWG 0.2-4 mm ²	24-8 AWG 0.2-6 mm ²	24-6 AWG 0.2-10 mm ²
Voltage Rating	600 V 1000V AC/DC	600 V 1000V AC/DC	600 V 1000V AC/DC
Current Rating	—	—	—
Insulation Material	Polyamide 66	Polyamide 66	Polyamide 66

Installation Instructions

Wire Stripping Length	10 mm	10 mm	18 mm
Screwdriver	Flat Head 0.6 x 3.5 mm	Flat Head 0.8 x 4 mm	Flat Head 0.8 x 4 mm

Terminal Blocks

	Cat. No.	Std. Pk.	Cat. No.	Std. Pk.	Cat. No.	Std. Pk.
Yellow / Green	CXG4/4	50	CXG6/3	50	CXG10/3	50

Accessories

Accessories		Cat. No.	Std. Pk.	Cat. No.	Std. Pk.	Cat. No.	Std. Pk.
End Plate		EPCX4/4	20	EPCX6/3	20	EPCX10/3	20
Partition Plate		PPCX4/4	20	—	—	—	—
DIN Rail		2511120 CA701-15/S	20 20	2511120 CA701-15/S	20 20	2511120 CA701-15/S	20 20
End Stop		CA702 CA802 CA103	50 50 50	CA702 CA802 CA103	50 50 50	CA702 CA802 CA103	50 50 50
Shorting Link/ Jumpers	2 pole	JX4/2	100	JX6/2	100	JX10/2	20
	3 pole	JX4/3	50	JX6/3	50	—	—
	4 pole	JX4/4	50	JX6/4	50	—	—
	5 pole	—	—	—	—	—	—
	6 pole	—	—	—	—	—	—
	7 pole	—	—	—	—	—	—
	8 pole	JX4/8	50	—	—	—	—
	10 pole	JX4/10	10	JX6/10	10	—	—
	16 pole	JX4/16	10	—	—	—	—
Test Plug		TX4	50	TX6	50	TX10	50
Marking Tag		MT6	100	MT8	100	MT10	100
Warning Label		WLX4	100	WLX6	100	WLX10	100

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Altech:](#)

[CXG2.5/4](#) [CXG6](#) [CXG4/4](#) [CXG10](#) [CXG6/3](#) [CXG10/3](#)