












Inductive sensors with increased sensing distances


Type M12	4 mm sensing distance		8 mm sensing distance	
				
	flush metal design		non-flush metal design	
	2 m cable	M12 plug	2 m cable	M12 plug
PNP normally-open contact*)	KIB-M12PS/004-KL2E 650.2903.025	KIB-M12PS/004-KLS12E 650.2943.015	KIN-M12PS/008-KL2E 650.2904.021	KIN-M12PS/008-KLS12E 650.2944.013
Dimensions				

Type M18	8 mm sensing distance		16 mm sensing distance	
				
	flush metal design		non-flush metal design	
	2 m cable	M12 plug	2 m cable	M12 plug
PNP normally-open contact*)	KIB-M18PS/008-KL2E 650.2905.022	KIB-M18PS/008-KLS12E 650.2940.005	KIN-M18PS/016-KL2E 650.2906.018	KIN-M18PS/016-KLS12E 650.2941.004
Dimensions				


*) Order only with part number, NPN- and normally-closed version on request

Wiring diagrams

Type M12/M18, cable version



Type M12/M18, plug version



Accessories

Cable couplings see page 284 ff.

General data

		M12		M18	
		flush	non-flush	flush	non-flush
Operating voltage	U_B	10–36 V			
Rated operating voltage	I_B	≤ 200 mA			
Switching hysteresis	H	10% from rated switching distance			
Reproducibility	R	$\leq 5\%$			
Switching frequency	F	800 Hz	400 Hz	500 Hz	200 Hz
Output		short circuit- and overload proof			
Polarity reversal protection		yes			
Rated switching distance	S_n	4 mm	8 mm	8 mm	16 mm
Functions-/operating voltage display		●/–	●/–	●/–	●/–
Ambient temperature		– 25 °C to + 70 °C			
Protection class		IP 67 according to IEC 529, EN 60 529			
Enclosure		nickel-plated brass (CuZn39Pb3)			
Cable PVC	mm ²	3 x 0.14		3 x 0.5	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Altech:](#)

[650.2940.005](#)