



[Article Page](#)


Product Description

inductive sensor DC



Name	KJ1,5-G6,5EB30-DNS-V1
Order number	08313651531
Switching distance	1,5 mm
Mounting	 shielded
Switch type	 N.O.
Signal Type	DC NPN
Connection	 Connector

Connection diagramm



Dimension (in mm)	6,5 x x 30
-------------------	------------

Technical Specification

Operating voltage	10 - 30 VDC
Max. ripple	≤ 10 %
Voltage drop	2,4 V
Max. load current	200 mA
No load current	≤ 10 mA
Leakage current	≤ 10 µA
Switching frequency	2000 Hz
Switching hysteresis	≤ 15 %
Operating temperature	-25 ° C to 70 ° C

Temperature drift	≤ 10 %
Repeat accuracy	≤ 5 %
Switching state	LED
Short-circuit proof	yes
Overload protection	yes
Reverse voltage protection	yes
Protection category	IP67
EMC-level	DIN EN 60947-5-2:2008
Housing material	Stainless steel V2A
Material active face	PBT
Utilisation category	DC 13
Termination	Connector M8 3pol

Errors and omissions excepted

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Altech:](#)

[08313651531](#)