













Surface Mount Gaskets and Grounding Pads

Our SMG gaskets can be used with many different types of board level shielding needs and when grounding points are required on your board. Form-in-Place gaskets can be eliminated by transferring the gasket to the board rather than to the thin edge of a casting or machined housing. No fear of damaging a thin Form-in-Place gasket during handling and assembly process. High speed SMT assembly of our tape and reel supplied gaskets make this a low cost reliable assembly option.

Part Numbers	Sizes						Packaging (parts per reel)	Core Materials	Cross Section (not to scale)
	Height		Width		Length				
SMG098118R-0.098	0.098	2.5	0.118	3	0.098	2.5	2100	Hollow High Temp. Sil. Sponge	
SMG118118R-0.079	0.118	3	0.118	3	0.079	2	1800	Hollow High Temp. Sil. Sponge	
SMG118118R-0.118	0.118	3	0.118	3	0.118	3	1800	Solid High Temp. Foam	
SMG118157R-0.197	0.118	3	0.157	4	0.197	5	1800	Hollow High Temp. Sil. Sponge	
SMG118197R-0.256	0.118	3	0.197	5	0.256	7	1500	Solid High Temp. Foam	
SMG256197R-0.118	0.256	6.5	0.197	5	0.118	3	1100	Solid High Temp. Foam	
SMG157256R-0.276	0.157	4	0.256	6.5	0.276	7	1200	Hollow High Temp. Sil. Sponge	
SMG236295R-0.157	0.236	6	0.295	7.5	0.157	4	1200	Hollow High Temp. Sil. Sponge	
SMG236354R-0.315	0.236	6	0.354	9	0.315	8	600	Hollow High Temp. Sil. Sponge	
SMG295197R-0.138	0.295	7.5	0.197	5	0.138	3.5	1000	Hollow High Temp. Sil. Sponge	

Black = inches Blue = mm Tolerance: +/- .019" (.48mm)

**LEADER
TECH**
a HEICO company

Global EMI Shielding Technology Center
12420 Race Track Rd., Tampa, Florida 33626
866.TECH.EMI (866.832.4364) † 813.855.6921 ‡ 813.855.3291

STATEMENT OF LIEU OF WARRANTY: All technical information and data in this document is based on tests and is believed to be accurate and reliable. Nevertheless, since the products described herein are not provided to conform with mutually accepted specifications and the use thereof is unknown, the manufacturer and seller of the products do not guarantee results, freedom from patent infringement, or suitability of the products for any application thereof. The manufacturer and seller of the products described in this document will provide all possible technical assistance and will replace any products proven defective. No statement or recommendations made by the manufacturer or seller not contained herein shall have any force of effect unless in conformity with an agreement signed by an officer of the seller and manufacturer. Product testing by the purchaser is recommended in order to confirm expected results.

Applications

- Mobile Electronics
- Computers
- Integrated Circuits

Benefits

- Low Cost
- Suitable for Automated Placement
- Tape & Reel Packaging
- Off-The-Shelf
- Reflow Capabilities
- Low Compression Requirements
- Resilient

Material

Outer Wrap

- Polyimide coated Sn/Cu



**SURFACE
MOUNT GASKETS**

www.LeaderTechInc.com


ISO 9001: 2015
CERTIFIED



Surface Mount Gaskets and Grounding Pads

Property	Method		Silicone Sponge	Polyurethane Foam
Outer Material	-		Polyimide coated Sn/Cu	Polyimide coated Sn/Cu
Color	-		Silver	Silver
Surface Resistance	ASTM D257		< 0.05 Ohm/in ²	< 0.05 Ohm/in ²
Hardness of Silicone	ASTM D2240		60 (Shore A)	20 (Shore C)
Deformation %	ASTM D5947	260°C, 30min	≤ 10%	≤ 10%
Resilience Ratio	ASTM D374	150°C, 100hrs, 20% compression	≥ 95%	≥ 85%
	ASTM D374	-40°C, 100hrs, 20% compression	≥ 95%	≥ 95%
	ASTM D374	85°C, 85% Rel. Humidity, 100hrs, 20% compression		
	ASTM D374	300 cycles, 20% compression		

Surface Mount Gasket - Force vs. Compression



Applications

- Mobile Electronics
- Computers
- Integrated Circuits

Benefits

- Low Cost
- Suitable for Automated Placement
- Tape & Reel Packaging
- Off-The-Shelf
- Reflow Capabilities
- Low Compression Requirements
- Resilient

Material

- Outer Wrap
- Polyimide coated Sn/Cu

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[LeaderTech:](#)

[SMG157256R-0.276](#) [SMG118197R-0.256](#) [SMG118118R-0.079](#) [SMG236295R-0.157](#) [SMG118118R-0.118](#)
[SMG098118R-0.098](#) [SMG295197R-0.138](#) [SMG236354R-0.315](#) [SMG118157R-0.197](#) [SMG256197R-0.118](#)