



NOTES:

1. Unless otherwise noted, all dimensions are in inches.
2. Foil Material: .002 thick 1145 aluminum
3. Interface Material: .0005 thick phase-change thermal compound, both sides.
Maximum shipping & storage temperature – 40°C
Reflow temperature – 60°C
Maximum recommended service temperature – 200°C
4. Thermal impedance: .030 °C/W-in² (.194 °C/W-cm²) @ 20psi
5. Used with Power DIP packages (Apex designators: CR, CU, DC & DD).

TOLERANCES - UNLESS OTHERWISE SPECIFIED
.XX = ±.01 [.254]
.XXX = ±.005 [.127]
ANG. = ±5°



TITLE:	THERMAL WASHER, P-DIP
SUBJECT:	MECHANICAL DRAWING
ENGINEER:	K.GOPP
DRAWN BY:	J.FAY
DWG. NO.:	16270
REV.:	1
QTY.:	1

MODEL:	TW05
FILENAME:	TW05
REV.:	J
DATE:	11JUL16

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Apex Microtechnology:](#)

[TW05](#)