



[Article Page](#)

Product Description

inductive sensor analogue



Name
Order number
Switching distance
Mounting

Switch type

Signal Type
Connection


Connection diagramm

KJ2-M8MB40-ANU
08317140000
from 0,5 mm to 2 mm

 shielded

 analog
Analog Voltage

 Cable



fine-pitch thread M8 x 40

Dimension (in mm)
Technical Specification
Special features
Operating voltage
Max. ripple
No load current
Switching frequency
Operating temperature
Temperature drift
Repeat accuracy
Linearity
Time delay
Protection category
EMC-level
Housing material
Material active face
Cable length
Utilisation category
Cable material
Nominal operating voltage
Cable cross
FIT / MTTF acc. to SIEMENS 29500

Output Voltage 0 ... 10 V
11 - 35 VDC
 $\leq 5 \%$
 $\leq 10 \text{ mA}$
400 Hz
-25 ° C to 70 ° C
 $\pm 8 \%$
 $\leq 1 \%$
 $\leq 3 \%$
100 ms
IP67
DIN EN 60947-5-7: 2004-06
Brass, nickel plated
ULTRAMID B3ZG3
2 m
DC 13
PVC LIYY grau (grey)
24 V DC
3x0.14 mm²
87,12 / 1310y



KJ2-M8MB40-ANU

Pulsotronic GmbH & Co. KG Neue Schichtstraße 14b 09366 Niederdorf Deutschland +49 (0)37296 930-200

Errors and omissions exceptet

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Altech:](#)

[08317140000](#)