






Name
Order number
Switching distance
Mounting

Switch type

Signal Type
Connection
Connection diagramm

KJ2-Q28KB-DPÖ-V1
08310000632
2 mm



Q 28 x 10 x 16

Dimension (in mm)
Technical Specification
Operating voltage
Max. ripple
Voltage drop
Max. load current
No load current
Leakage current
Switching frequency
Switching hysteresis
Operating temperature
Temperature drift
Repeat accuracy
Switching state
Time delay
Short-circuit proof
Overload protection
Reverse voltage protection
Protection category
EMC-level
Housing material
Utilisation category
Contact material

10 - 30 VDC
≤ 10 %
2,4 V
200 mA
≤ 13 mA
≤ 10 µA
1000 Hz
≤ 15 %
-25 ° C to 70 ° C
≤ 10 %
≤ 2 %
LED
100 ms
yes
yes
yes
IP67
DIN EN 60947-5-2: 2008
Brass, nickel plated
DC 13
Cu



KJ2-Q28KB-DPÖ-V1

Pulsotronic GmbH & Co. KG Neue Schichtstraße 14b 09366 Niederdorf Deutschland +49 (0)37296 930-200

Contact surface material

Termination

FIT / MTTF acc. to SIEMENS 29500

Housing material

NiAu

Connector M8 3pin

40,55 / 2815y

PA6 GF30 black translucent

Errors and omissions excepted

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Altech:](#)

[08310000632](#)