


## Model 7074

Type N (F) Panel Mount 50  $\Omega$  1.13" L X 0.44" W.



Model 7074 Type N (F) Panel Mount

Use for your 50  $\Omega$  N(F) panel mount applications.

### Features


- Designed for panel mount applications with convenient solder cups
- Precision machined with white bronze plating
- Gold plated (30 micro-inches) contacts
- Insulation material is PTFE (**not delrin**)

### Materials

- Body is machined brass with white bronze plating.
- Female center contacts are gold-plated (30 micro-inches) brass.
- High quality machined PTFE dielectric.

### Ordering Information

Model: 7074, N(F), Panel Mount 1.13 L X 0.44 W



### Specifications

Nominal impedance	50 $\Omega$
Frequency	0-11 GHz
VSWR	1.30 max. 0-11 GHz
Center / Outer contact resistance	1.0 / 0.2 m $\Omega$
Number of insertions	500
Insulation resistance	5000 M $\Omega$ (min)
Dielectric withstand voltage	1500 Vrms
Ratings: Voltage: 500 Vrms Operating temperature: -85 °F to +131 °F (-65 °C to +155 °C) Max.	

USA: Sales: 800-490-2361 Technical Support: 800-241-2060 Fax: 888-403-3360

Europe: 31-(0) 40 2675 150 International: 425-446-5500

e-mail: [technicalsupport@pomonatest.com](mailto:technicalsupport@pomonatest.com)

Where to Buy: [www.pomonaelectronics.com](http://www.pomonaelectronics.com)

All dimensions are in inches. Tolerances (except noted): .xx =  $\pm .02$ " (.51 mm), .xxx =  $\pm .005$ " (.127 mm). All specifications are to the latest revisions. Specifications are subject to change without notice. Registered trademarks are the property of their respective companies.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pomona:

7074