

TECHNICAL DATA

Fluke 719 Pressure Calibrator



Key features

- Pressure calibrator with built-in electric pump for one-handed pressure calibration
- Offers best-in-class pressure measurement uncertainty of 0.025%
- Measures and sources mA with best in class 0.015% accuracy to test valves and I/Ps
- Calibrates 30 psi and 100 psi pressure ranges
- Features precision pressure adjustment vernier for easy and accurate pressure calibration

Product overview: Fluke 719 Pressure Calibrator

Calibrate pressure with one hand using the Fluke 719 Electric Pressure Calibrator

Forget the hassle of hand pumping. Now you can calibrate and test pressure devices quickly and easily with one hand, saving valuable time. With the innovative, built-in electric pump, the Fluke 719 Electric Pressure Calibrator provides pressure calibration at your fingertips!

Use the programmable pump limit settings to eliminate over-pressurization, and to set “pump to” pressure values. The unique cleanout port design reduces pump failures, and makes the 719 easy to clean without repair. The compact, lightweight form, combined with one-handed calibration, makes this pressure calibrator the ideal tool for busy process professionals.

The Fluke 719 delivers pressure calibration made easy, by a name you know and trust for all your process calibration needs.

Other useful features:

- Simulates mA signals to troubleshoot 4-20 mA loops
- Powers transmitters during test using 24 V loop supply
- Comes with three-year warranty for calibrator
- Provides variable release rate bleed valve for easy pressure adjustment
- Offers ideal performance for high accuracy transmitter calibration
- Offers a programmable pressure calibrator pump limit that:
 - Eliminates over-pressurization
 - Allows the user to program target pressures for pumping
- Tests pressure switches easily with switch test function
- Provides extended pressure measurement range with any of 50 [750P series Pressure Modules](#)
- Pump cleanout ports to reduce pump failures from moisture and fluid damage

Specifications: Fluke 719 Pressure Calibrator

General Specifications	
Storage temperature	-30°C to 60°C
Operating temperature	-10°C to 55°C

Relative humidity	95% (-10°C to 30°C)
	75% (30°C to 40°C)
	45% (40°C to 50°C)
	35% (50°C to 55°C)
Shock	1 meter drop test
Safety	CSA C22.2 No. 1010.1:1992
EMC	EN50082-1:1992 and EN55022:1994 Class B
Size (H x W x L)	60 x 87 x 210 mm
	(2.19 x 3.41 x 8.28 in)
Weight	912 g (2 lb)
Baery	Two 9 V alkaline baeries
Baery life	12 hours with 12 mA into 500 Ω , 200 pump cycles to 100 psi, 500 pump cycles to 30 psi
Warranty	Three-years, one year for pump

Specifications

Fluke-719 30G	Range	-12 to 36 psi, -850 mbar to 2.4 bar
	Resolution	0.001 psi, 0.1 mbar
	Accuracy	0.025% range for 6 months 0.035% of range for one (1) year
Fluke-719 100G	Range	-12 to 120 psi, -850 mbar to 8 bar
	Resolution	0.01 psi, 1 mbar
	Accuracy	0.025% range for 6 months 0.035% of range for one (1) year
mA	Range	0 to 24 mA
	Resolution	0.001 mA
	Accuracy	.015% Rdg + 2 counts
	Max load, 1000 Ω , 750 Ω ohm in HART mode	
Loop supply	Range	24 V DC
	Resolution	N/A
	Accuracy	$\pm 10\%$

Pump Specifications

Maximum pressure generation	120 psi (8 BAR) (100 psi model)
Pump to	-30 psi in less than 15 seconds ¹
	-100 psi in less than 45 seconds ¹
	1. With 1 meter of 1/8 inch test hose
Pump cycles between rebuilds	5000



Total pump life	20,000 calibration cycle
-----------------	--------------------------

Ordering information



Fluke 719 30G

Fluke 719 30G Pressure Calibrator 30 psi, 2 bar

Includes:

- Protective yellow holster
- Instructions sheet (15 languages)
- Test leads and alligator clip
- Two 9V alkaline batteries
- Hose Kit
- NIST - Traceable calibration report and data

Fluke 719 100G

Fluke 719 100G Pressure Calibrator 100 psi, 7 bar

Includes:

- Protective yellow holster
- Instructions sheet (15 languages)
- Test leads and alligator clip
- Two 9V alkaline batteries
- Hose Kit
- NIST - Traceable calibration report and data

FPC1S-FLUKE71X-1

Premium Care 1-Year Standard Plan for Fluke 719Pro, 719, and 718

Includes:

- Premium Care 1-Year Standard Plan
-

FPC3S-FLUKE71X-1

Premium Care 3-Year Standard Plan for Fluke 719Pro, 719, and 718

Includes:

- Premium Care 3-Year Standard Plan
-

Fluke. *Keeping your world up and running.®*

Fluke Corporation

PO Box 9090, Everett, WA 98206 U.S.A.

For more information call:

In the U.S.A. (800) 443-5853

In Canada (800) 36-FLUKE

From other countries +1 (425) 446-5500

www.fluke.com

©2025 Fluke Corporation.

Specifications subject to change without notice.
03/2025

**Modification of this document is not permitted
without written permission from Fluke
Corporation.**

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Fluke:](#)

[PUMP ASSEMBLY W/O MOTOR](#)