

# **OUTPUT**

# INPUT

## PROTECTION

### ENVIRONMENT

# SAFETY & EMC

## **OTHERS**

# PSB-600 Series (3 Phase) **Specifications**











#### Features:

- Multiple overload/ short circuit protection modes
- Efficiency above 92%
- · Easy parallel connection for more power
- Small size
- DIN rail mountable
- · Cooling by free air convection
- UL508 (industrial control equipment) approved
- EN60950-1
- Built-in DC OK relay contact
- · 3 year warranty

Cat. No.	PSB-60024

DC VOLTAGE 24 V RATED CURRENT 25 A

CURRENT RANGE Refer to Output derating curve

RATED POWER 600 W RIPPLE & NOISE (max) 100 mVp-p

Ripple & noise are measured at 20MHz of bandwidth by using a 12" twisted pair-wire terminated with a 0.1µF & 47µF parallel capacitor.

VOLTAGE ADJ. RANGE 22 V ~ 27 V **VOLTAGE TOLERANCE** -0.03

Tolerance: includes set up tolerance, line regulation and load regulation.

START UP WITH STRONG LOAD  $\leq 50,000 \, \mu F$ CURRENT SHORT CIRCUIT Icc

60 A Max 2 sec.: Hiccup mode

Permanent: Continuous mode

DISSIPATION POWER LOAD mas 28 W LINE REGULATION  $\pm 0.5\%$ LOAD REGULATION ± 1% SETUP, RISE TIME 1 sec. (max)

Length of set up time is measured at cold first start. Turning ON/OFF the power supply may lead to increase of the set up time.

HOLD UP TIME (Typ.) Typ. 20 msec

330 ~ 550V AC VOLTAGE RANGE FREQUENCY RANGE 47 ~ 63 Hz +-6% >92 % EFFICIENCY (Typ.) AC CURRENT (330 - 500 Vac.) 0.95 - 0.85 AINRUSH CURRENT (Typ.) < 17 A < 5 msec INTERNAL FUSE T 6.3 A

EXTERNAL FUSE (recommended) 16 A (MCB curve B) LEAKAGE CURRENT < 1.5 mA @ 500 Vac

**OVERLOAD** In (60°C) x 1.5 3 3 min.;

Current max. Overload @ 4Vdc (permanent) Imax=In (60°C) x (1.8 ~ 2.2)

OVER VOLTAGE

DC OK AKTIV SIGNAL (max.)

Yes. Shuts down output and automatically restarts when the temperature inside goes down OVER TEMPERATURE SHORT CIRCUIT PROTECTION

1 Hiccup Mode / 2 Fold Back / 3 Restart After Main

-25 up to +70 °C WORKING TEMP. (>60°derating 2.5% °C) HUMIDITY 95 % at 25°C, no condensation

STORAGE TEMP -40 up to +85 °C TEMP. COEFFICIENT  $\pm$  0.03% / C° (0 ~ 60 °C) VIBRATION In according to IEC60068-2-6

SAFETY STANDARDS UL508 approved, IEC/EN 60950, EN 50178, IEC/EN 60950, EN60950-1, PELV EN 60204-1

WITHSTAND VOLTAGE 

 $20 \sim 30 \text{ Vdc}$ 

PROTECTION CLASS IP 20 (EN/IEC 60529) ISOLATION RESISTANCE 100 M $\Omega$  (min) @ 500 Vdc

**EMI CONDUCTION & RADIATION** EN61000-6-4 HARMONIC CURRENT EN61000-3-2

**EMS IMMUNITY** EN 61000-4-2, EN 61000-4-3, EN 61000-4-4, EN 61000-4-5,

EN 61000-4-6, EN61000-6-2, EN61000-6-4,

The power supply is considered a component which will be installed into a final equipment. The final equipment must be

re-confirmed that it still meets EMC directives

MTBF IEC 61709 > 500.000 h

POLLUTION DEGREE 2.5 mm Screw (24 ~ 14 AWG)

CONNECTION TERMINAL BLOCK DIMENSION


85x120x140 mm (3.34x4.72x5.51 in )


**PACKING** 0.75 kg (1.9 lbs) each

NOTE All parameters NOT specially mentioned are measured at 230V AC input, rated load and 25°C of ambient temperature.



## **Mechanical Specification**





TB1 Terminal Pin. No Assignment


Pin No.	Assignment (3 phase)
1	L1
2	L2
3	L3
4	FG 🖶
5	FG 🖶

TB2 Terminal Pin. No Assignment


Pin No.	Assignment
1,2	DC output -V
	DC output +V
5,6	DC OK relay contacts

# **DC OK Relay Contact**

Outputs are used for preventive function monitoring of the power supply. An electrically isolated signal contact is available. The signal contact closes when the output power is OK and opens when the output voltage falls below  $20Vdc \pm 5\%$ .




## **Output Derating Curve**



## **Parallel Connection**

A parallel connection with the same model power supply can be set up to increase the output power. The output has to be adjusted approximately to the same value (± 20mV) while applying a 1-2 A load to all devices before connecting them in parallel. In PSA-600xx, for more power, the position of the Easy Parallel jumper needs to be changed to enable a parallel connection. In this mode up to 4 power supplies can be put together in parallel.



Note: All dimensions are in millimeters, to convert to inches multiply by 0.03937.

SC Class 2 Series

PSA Flex Serio

PSB FIEX Series

PS-S Slim Series

os Low Profile Serve

os Industrial Series

PS C & W Series

CBI Type

CB Type Chargers

Accessories

Appendix

# **Mouser Electronics**

**Authorized Distributor** 

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Altech: PSB-60024