



### FEATURES:

- Converts Double Banana Jack Test Instruments to Binding Posts for test versatility.
- Banana Plugs can be stacked vertically or horizontally.
- Wires, spade lugs and pin tip plugs can be attached by means of the insulated knurl thumb knob.
- Insulated knurl thumb knob is captive to prevent misplacement.
- Banana Plugs feature Nickel/Gold Plated, Beryllium Copper for tarnish resistance & long insertion life.

### MATERIALS:

Binding Post: Body – Brass, Nickel Plated (Model 1286), Brass, Gold Plated (Model 5405)

Insulator Knurl Thumb Knob: Polycarbonate, Color: Black, Red

Insulator: ABS, Molded to the binding Post and Banana Body

Marking: “1286 POMONA ELECTRONICS” or “5405 POMONA ELECTRONICS”

Banana Plug: Body: Brass, Nickel Plated (Model 1286), Brass, Gold Plated (Model 5405)

Spring: Beryllium Copper, Nickel Plated (Model 1286)

Beryllium Copper, Gold Plated (Model 5405)

### RATINGS:

Operating Voltage: 2500 VDC

Operating Temperature: +50°C (+122°F).

Current: 15 Amperes Max.

### ORDERING INFORMATION: Model 1286 & 5405

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ±.005" (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pomona:

1286#/BULK