



Model 1452
Adapter-Binding Posts to BNC Receptacle



Model 1452
Adapter-Binding Posts to BNC Receptacle



Features

- Permits single or double banana plugs to be used with equipment having a BNC male.
- Cross holes .166 (4.2) dia. in body provide side stack up connections.

Materials

Upper Connector: Binding Posts, Insulated.

Material: Binding Post body, brass H.H. per QQ-B-626, Alloy 360.

Finish: Nickel plated per QQ-N-290, class 2 (.0002 min.).

Insulation: Acrylonitrile-Butadiene-Styrene, molded to Binding Posts and BNC receptacle.

Color: One Red and one Black (Gnd).

Operating Temperature: +115°C. (+239°F.) Max.

Marking: "POMONA 1452"

Lower Connector: BNC receptacle, comparable to UG 1094/U.

Finish: Body and fittings, tarnish resistant

Nominal Impedance: 50 Ohms

Specifications

Operating Temperature: +50°C. (+122°F.) Max.

Operating Voltage: Hand-held testing: 30 VAC/60 VDC Max.

Hands free testing in controlled voltage environments: 500 VRMS

Ordering Information

Model: 1452

USA: Sales: 800-490-2361
Technical Support: technicalsupport@pomonatest.com
Fax: 425-446-5844

Europe: 31-(0) 40 2675 150 **International:** 425-446-5500

Where to Buy: www.pomonaelectronics.com

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ±.005" (.127 mm). All specifications are to the latest revisions. Specifications are subject to change without notice. Registered trademarks are the property of their respective companies.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pomona:

1452#