



FEATURES:

- Alligator Clip features a banana jack interface for quick and easy attachment to various lengths of banana plug patch cords.
- Alligator jaw opens up to .300" (7,62mm) for attachment to most test terminals.
- Flexible boot provides insulation protection.

MATERIALS:

Alligator: Steel, Nickel Plated

Flexible Boot: Vinyl, Color per Part Number

RATINGS:

Operating Temperature: +50° C (+122° F)

Operating Voltage: 150 VRMS

Current: 5 Amperes Max.

ORDERING INFORMATION: Model 2240-*

* = Color Code, -0 Black, -2 Red

Sold in packages of 10 per color

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ±.005" (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pomona:

[2240-2](#) [2240-0](#) [2240-0#](#)