


Model 4684 Adapter – BNC Female To Banana Plug With Ground Lead



FEATURES:

- Permits BNC male to be used with equipment having standard banana jacks.
- Allows the ground jack to be located up to 63.5 (2.50) away from the output/input jack.

MATERIALS:

Upper Conn: BNC Female

Finish: Body – Tarnish resistant.

Center Contact – Gold plated per requirements of MIL-C-39012.

Insulation: Polypropylene molded to connector, plug body and wire.

Color: Red.

Marking: “POMONA 4684.”

Ground Lead: In-line Banana Plug. Spring – Beryllium Copper per QQ-C-533, Alloy 172, Cond. H.T.

Material: Body – Brass per QQ-B-626, Alloy 360, ½ Hard.

Finish: Nickel plated per QQ-N-290, Class 2, 200/300 microinches.

Wire: 18 AWG, stranding 65 x 36 t.c., PVC insulated, 3.66 (.144) O.D.

Color: Black

Banana Plug Insulation: Polypropylene molded to plug body and wire.

Color: Black.

Lower Conn: Banana Plug

Material: Spring – Beryllium Copper per QQ-C-533, Alloy 172, Cond. H.T.

Body – Brass per QQ-B-626, Alloy 360, ½ Hard.

Finish: Nickel plated per QQ-N-290, Class 2, 200/300 microinches.

RATINGS:

Operating Temperature: +55° C. (+131° F.) Max.

Voltage: Hand-held Testing: 30VAC/60VEDC Max.

Hand Free Testing in Controlled Voltage Environments: 500 VRMS Max.

ORDERING INFORMATION: Model 4684

All dimensions are in inches. Tolerances (except noted): .xx = ±.02” (.51 mm), .xxx = ± .005” (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pomona:

4684