



FEATURES:

- Mates to Model #5219
- 2 Shields provided for use in high interference areas
- Lengths other than those specified available upon request.

MATERIALS:

Conn: 1st End-

Triaxial Cable Male: BNC 3 Lug Bayonet Style.

Finish: Body and Fittings – Tarnish Resistant.

Intermediate and Center Contacts: Gold plated per requirements of MIL-C-39012.

Cable: Belden 9222. Triaxial conductors. Nominal Impedance: 50 Ohms. 20 AWG,
Polyethylene dielectric, Shield: Tinned Copper, Jacket: PVC, 6.15 (.242) O.D. Color: Yellow.

Marking: “POMONA 5223”

Conn: 2nd End- Same as first.

RATINGS:

Operating Voltage: 500 VRMS/DC.

Nominal Impedance of Cable: 50 Ohms.

ORDERING INFORMATION: Model 5223-XX

XX=Cable Length, Standard Lengths: 36” (914), 60” (1524), Ordering Example: 5223-60 indicates 60” in length.

All dimensions are in inches. Tolerances (except noted): .xx = ±.02” (.51 mm), .xxx = ±.005” (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pomona:

[5223-60](#) [5223-36](#) [EM5223-168](#) [5223-48](#)