



**Model 5900A**  
**Basic Industrial DMM Test Lead Kit**

6479

MODEL 6479

MODULAR PROBE SET WITH STAINLESS STEEL TIP


QTY 2 : 1 RED, 1 BLACK



MODEL 5907A

FLEXIBLE TEST LEAD SET WITH RIGHT ANGLE AND STRAIGHT BANANA PLUGS


QTY 2 : 1 RED, 1 BLACK



MODEL 5912B

MAXIGRABBER TEST CLIP SET WITH JAWS

QTY 2 : 1 RED, 1 BLACK



TRI-FOLD NYLON POUCH

For data sheets / specifications of the kit individual components, visit the Pomona web site at:

[www.pomonaelectronics.com](http://www.pomonaelectronics.com)

**FEATURES:**

- Test leads with a right angle banana plug are ideal for use with hand held digital multimeter.
- Flexible test leads feature high strand count silicone wire for extreme flexibility and high temperature resistance.
- Wear indication with double insulated (dual extruded) silicone leads shows white inner layer for increased safety.
- Banana plugs are molded directly to the wire for superior pull strength.
- Probe body and Maxigrabber Clip® attaches directly to the flexible test leads for test versatility.
- Tri-fold pouch of durable nylon conveniently stores the test accessories.
- Compatible with most multimeters that accepts safety style sheath banana plugs.
- CE Compliant; complies with IEC 61010-031 standard for hand held accessories.



**USA:** Sales: 800-490-2361  
Technical Support: [technicalsupport@pomonatest.com](mailto:technicalsupport@pomonatest.com)  
Fax: 425-446-5844

**Europe:** 31-(0) 40 2675 150 **International:** 425-446-5500

**Where to Buy:** [www.pomonaelectronics.com](http://www.pomonaelectronics.com)

All dimensions are in inches. Tolerances (except noted): .xx =  $\pm 0.02$ " (.51 mm), .xxx =  $\pm 0.005$ " (.127 mm). All specifications are to the latest revisions. Specifications are subject to change without notice. Registered trademarks are the property of their respective companies.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pomona:

[5900A/POM](#)