



Pomona's 7/16 DIN adapters are made in the US and feature silver plated brass bodies, Teflon insulation and silver plated, Beryllium Copper female and brass male center contacts.



RATINGS:

Impedance: 50 Ohms
 Frequency Range: DC - 7.5 GHz
 Insertion Loss: $-.01 \text{ dB} \sqrt{\text{Frequency GHz}}$
 VSWR (Max): $< 1.10:1 @ \text{DC} - 7.5 \text{ GHz}$
 3rd Order IM -dBc: $> -150 \text{ dBc}$

MATERIALS:

Bodies and Fitting – Brass, per QQ-B-626
 Finish – Silver, QQ-S-365

FEATURES:

- Reduced intermodulation generation
- Improved VSWR
- More stable electrical and mechanical connection over type N
- Peak power rating of 40 kW compared to 10kW for type N
- Higher contact pressure means lower contact resistance and better heat dissipation for greater average power handling
- Greater resistance to environmental forces
- Coupling mechanism provides higher contact pressure and full circumference contact
- Longer, more durable and long-term reliable conductors
- Longer service life under harsh conditions
- Interface dimensions and coupling nut torque is 10 times greater than type N

ORDERING INFORMATION:

Model 6257

All dimensions are in inches. Tolerances (except noted): .xx = $\pm .02$ " (.51 mm), .xxx = $\pm .005$ " (.127 mm).
 All specifications are to the latest revisions. Specifications are subject to change without notice.
 Registered trademarks are the property of their respective companies. Made in USA

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Pomona:](#)

[6257](#)