


Model 6264B**Alligator Clip with Flex Boot for standard test probe tip, .080" (2mm)****Features**

- Redesigned to meet IEC 61010-031, the latest international safety standard for test accessories.
- Medium alligator jaw grips onto test terminal up to 0.3" (7.6mm) O.D.
- Thermoplastic body and flexible boot offers insulation protection.
- Alligator clip features a recessed 2mm pin tip jack at the adapter end for added insulation protection. The pin tip jack also features internal threads for added mating with the Pomona 6601 Test Probes.
- Adapter converts a .080" (2mm) DMM probe tip to alligator clips for ease of testing.
- Interfaces to Pomona's Models 5519A, 6365, 6366, 5898 and 6601 Test Probes.

Materials

Alligator Clip:	Steel, nickel-plated
Jaw Insulation:	Polypropylene
Boot:	Santoprene™

Ratings

IEC 61010-031, Pollution Degree 2, 2000 m altitude
Voltage: 1000 V CAT II / 600 V CAT III
Temperature: -20°C to 55°C (-4°F to +131°F) 80% R.H.
Current: 10 amperes max.

Ordering Information

Model: 6264B (Set of one Black, one Red Alligator Clips)
Medium Alligator Clips are also included in many Pomona DMM Test Lead Kits.

USA: Sales: 800-490-2361
Technical Support: technicalsupport@pomonatest.com
Fax: 425-446-5844

Europe: 31-(0) 40 2675 150 **International:** 425-446-5500
Where to Buy: www.pomonaelectronics.com

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ±.005" (.127 mm). All specifications are to the latest revisions. Specifications are subject to change without notice. Registered trademarks are the property of their respective companies.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pomona:

[6264B/POM](#)