


Model MDP-X Double Banana Plug, Four Terminal Isolation



FEATURES:

- Mates to Model #2269 or any standard double banana jack..
- Provides four terminal isolation.
- Top stack-up receptacles isolated from lower plugs.
- Ideal for insertion of matching network in laboratory VTM's signal generators, etc.
- Bright tin plated solder turret terminals for permanent noise-free connections.

MATERIALS:

Upper Conn.:

Double Banana Jack

Material: Brass per QQ-B-626, Alloy 360,
½ Hard.

Finish: Nickel plated by QQ-N-290, Class 2,
200/300 microinches.

Insulation: Polypropylene molded to plug bodies.

Color: Red.

Marking: "POMONA ELECTRONICS CALIF.
MODEL MDP-X".

Lower Conn.:

Double Banana Plug

Material: Spring – Beryllium Copper per QQ-C-533, Alloy 172, Cond. HT.

Plug body – Brass per QQ-B-626, Alloy 360, ½
Hard.

Finish: Nickel plated per QQ-N-290, Class 2,
200/300 microinches.

Solder turret terminals

Material: Brass per QQ-B-626, Alloy 360, ½
Hard.

Finish: Bright tin plated per MIL-T-10727,
Type I, 100/250 microinches.

RATINGS:

Operating Temperature: +55°C. (+131°F.) MAX.

Operating Voltage: 2500 V

Current: 15 Amperes

ORDERING INFORMATION: Model MDP-X

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ±.005" (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies.

Made in USA

6/9/99

SY/EH/LS

R:\Release\DataSheet\1_Market_00\ID_MDPX_1_01.doc

Sales: 909-469-2900 Fax: 909-629-3317
Technical Assistance: 800-241-2060

PomonaACCESS **90536** (800) 444-6785 or (949) 253-3858
More drawings available at www.pomonaelectronics.com

Page 1 of 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pomona:

MDP-X