



FEATURES:

- Small measuring junction mass for fast response time.
- Excellent for low conductivity surfaces.
- Junction resists metal fatigue over 10,000 cycles.

MATERIALS:

Thermocouple – “K” Type Chromel/Alumel
 Cable – AWG #24, Type KX extension wire, insulation gray PVC.
 Connector Plug – Yellow, Hytrel 4776
 Handle – Black Valox
 Probe Tip – White PTFE

RATINGS:

Temperature Range – 32 to 500°F. (0-260°C.)
 Accuracy - $\pm 4^\circ\text{F}$. ($\pm 2.2^\circ\text{C}$.)
 Time Constant – 3 seconds max. (100°C water at sea level)

ORDERING INFORMATION: Model 6376

Note: For low environments. Do not exceed 30VAC/60VDC.

All dimensions are in inches. Tolerances (except noted): .xx = $\pm .02$ " (.51 mm), .xxx = $\pm .005$ " (.127 mm).
 All specifications are to the latest revisions. Specifications are subject to change without notice.
 Registered trademarks are the property of their respective companies. Made in USA

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pomona:

6376