

## TECHNICAL DATA

## Fluke 9132/9133 Portable Infrared Calibrator



### Key features

- Accurate, reliable performance from  $-15^{\circ}\text{C}$  to  $500^{\circ}\text{C}$
- Small, compact design in a blackbody calibrator
- These blackbody calibrator units feature a temperature controlled measurement surface with a diameter of 2.25 in (57 mm).
- Intuitive, easy-to-read display that indicates when temperature is stable.

### Product overview: Fluke 9132/9133 Portable Infrared Calibrator

#### Precision when you need it for infrared temperature calibration

##### Fluke 9132: blackbody calibration up to $500^{\circ}\text{C}$

For IR calibrations above normal ambient, the Fluke 9132 blackbody calibration source provides a stable measurement surface up to  $500^{\circ}\text{C}$  ( $932^{\circ}\text{F}$ ). Short heating and cooling times mean you won't have to wait long to get your work done. Radiometric calibration gives you confidence in your measurements to  $500^{\circ}\text{C}$ .

##### Fluke 9133: blackbody calibration from $-30^{\circ}\text{C}$ to $150^{\circ}\text{C}$

If you're calibrating IR thermometers at cold temperatures, you'll love our new Fluke 9133 blackbody calibration source. With solid-state cooling technology, this new IR calibrator reaches  $-30^{\circ}\text{C}$  ( $22^{\circ}\text{F}$ ) in normal ambient conditions. With a conveniently located dry gas fitting on the front bezel, ice build up on the target can be avoided. At the upper end of its range, the Fluke 9133 provides stable temperatures to  $160^{\circ}\text{C}$  ( $320^{\circ}\text{F}$ ).

With heating and cooling times of about 15 minutes from ambient to either extreme, the Fluke 9133 gets you to temperature quickly and performs when it gets there.

## Specifications: Fluke 9132/9133 Portable Infrared Calibrator

Specifications	9132	9133
Temperature range	50°C to 500°C (122°F to 932°F)	–30°C to 150°C at 23°C ambient (–22°F to 302°F at 73°F ambient)
Accuracy	±0.5°C at 100°C (±0.9°F at 212°F) ±0.8°C at 500°C (±1.4°F at 932°F)	±0.4°C (±0.72°F)
Stability	±0.1°C at 100°C (±0.18°F at 212°F) ±0.3°C at 500°C (±0.54°F at 932°F)	±0.1°C (±0.18°F)
Target size	57 mm (2.25 in)	57 mm (2.25 in)
Target emissivity	0.95 (±0.02 from 8 to 14 mm)	0.95 (±0.02 from 8 to 14 mm)
Resolution	0.1°	0.1°
Heating time	30 minutes (50°C to 500°C)	15 minutes (25°C to 150°C)
Cooling time	30 minutes (500°C to 100°C)	15 minutes (25°C to –20°C)
Computer interface	RS-232 I/O included	
Power	115 V AC (±10%), 3 A or 230 V AC (±10%), 1.5 A, switchable, 50/60 Hz, 340 W	115 V AC (±10%), 1.5 A, or 230 V AC (±10%), 1.0 A, switchable, 50/60 Hz, 200 W
Size (H x W x D)	102 x 152 x 178 mm (4 x 6 x 7 in)	152 x 286 x 267 mm (6 x 11.25 x 10.5 in)
Weight	1.8 kg (4 lb)	4.6 kg (10 lb)
NIST-traceable contact calibration	Data at 50°C, 100°C, 200°C, 250°C, 300°C, 400°C, and 500°C	Data at –30°C, 0°C, 25°C, 75°C, 100°C, 125°C, and 150°C

## Ordering information



### 9132

Fluke 9132 Portable Infrared Calibrator  
50°C to 500°C

---

### 9133

Fluke 9133 Portable Infrared Calibrator  
-30°C to 150°C at 23°C ambient

---

Fluke. *Keeping your world up and running.®*

**Fluke Corporation**  
PO Box 9090, Everett, WA 98206 U.S.A.

**For more information call:**  
In the U.S.A. (800) 443-5853  
In Canada (800) 36-FLUKE  
From other countries +1 (425) 446-5500  
[www.fluke.com](http://www.fluke.com)

©2024 Fluke Corporation.  
Specifications subject to change without notice.  
09/2024

**Modification of this document is not permitted  
without written permission from Fluke Corporation.**

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Fluke:](#)

[9133-156](#) [9132-156](#)