


**SERIES:** RDS-74385-SMT | **DESCRIPTION:** ROTARY DIP SWITCH**FEATURES**

- 10 and 16 positions
- flat actuator
- surface mount
- tube or tape and reel packaging

**SPECIFICATIONS**

| parameter             | conditions/description                         | min | typ    | max | units   |
|-----------------------|------------------------------------------------|-----|--------|-----|---------|
| rated voltage         | switching                                      |     |        | 42  | Vdc     |
|                       | non-switching                                  |     |        | 42  | Vdc     |
| rated current         | switching                                      |     |        | 100 | mA      |
|                       | non-switching                                  |     |        | 400 | mA      |
| withstanding voltage  | for 1 minute                                   |     | 250    |     | Vac     |
| contact resistance    |                                                |     |        | 80  | mΩ      |
| insulation resistance | at 250 Vdc                                     | 100 |        |     | MΩ      |
| operating torque      |                                                | 90  | 120    | 150 | gf*cm   |
| actuator travel       | continuous rotation                            |     | 360    |     | degrees |
| operating temperature |                                                | -60 |        | 125 | °C      |
| storage temperature   |                                                | -60 |        | 125 | °C      |
| life                  | at rated voltage, current, 15~20 cycles/minute |     | 25,000 |     | steps   |
| flammability rating   | UL94V-0                                        |     |        |     |         |
| RoHS                  | yes                                            |     |        |     |         |
| IP level              | IP67 (IEC 60529:2001)                          |     |        |     |         |

**PART NUMBER KEY**


|                                     |                                                           |                                                    |
|-------------------------------------|-----------------------------------------------------------|----------------------------------------------------|
| <b>RDS - XXS - 74385 - SMT - XX</b> |                                                           |                                                    |
| Base Number                         | No. of Positions:<br>10 =10 Positions<br>16 =16 Positions | Packaging:<br>"blank" = Tube<br>TR = Tape and Reel |

MECHANICAL DRAWING


units: mm  
tolerance: ±0.3 mm  
unless otherwise noted

| ITEM | DESCRIPTION | MATERIAL        | PLATING/COLOR                           |
|------|-------------|-----------------|-----------------------------------------|
| 1    | actuator    | LCP (UL94V-0)   | red (10 position)<br>gray (16 position) |
| 2    | housing     | LCP (UL94V-0)   | black                                   |
| 3    | face plate  | stainless steel |                                         |
| 4    | terminals   | copper alloy    | gold                                    |




10 POSITION



16 POSITION




| ON ○    |   |      |   |   |   |   |
|---------|---|------|---|---|---|---|
| OFF ●   |   | CODE |   |   |   |   |
| TYPE    |   | POS  | 1 | 2 | 4 | 8 |
| 10 STEP | 0 | ●    | ● | ● | ● | ● |
|         | 1 | ○    | ● | ● | ● | ● |
|         | 2 | ●    | ○ | ● | ● | ● |
|         | 3 | ○    | ○ | ● | ● | ● |
|         | 4 | ●    | ● | ○ | ● | ● |
|         | 5 | ○    | ● | ○ | ● | ● |
|         | 6 | ●    | ○ | ○ | ● | ● |
|         | 7 | ○    | ○ | ○ | ● | ● |
|         | 8 | ●    | ● | ● | ○ | ○ |
|         | 9 | ○    | ● | ● | ○ | ○ |
| 16 STEP | A | ●    | ○ | ● | ○ | ○ |
|         | B | ○    | ○ | ● | ○ | ○ |
|         | C | ●    | ● | ○ | ○ | ○ |
|         | D | ○    | ● | ○ | ○ | ○ |
|         | E | ●    | ○ | ○ | ○ | ○ |
|         | F | ○    | ○ | ○ | ○ | ○ |



Recommended PCB Layout  
Top View

SOLDERABILITY


| parameter        | conditions/description | min | typ | max | units |
|------------------|------------------------|-----|-----|-----|-------|
| hand soldering   | for maximum 3 seconds  |     |     | 350 | °C    |
| reflow soldering |                        | 255 |     | 260 | °C    |



PACKAGING (TUBE)

units: mm

Tube Size: 13.0 x 14.50 x 540 mm  
Tube QTY: 70 pcs




## PACKAGING (TAPE & REEL )

units: mm

Reel Size: Ø330 mm

QTY: 600 pcs



REVISION HISTORY

| rev. | description                       | date       |
|------|-----------------------------------|------------|
| 1.0  | initial release                   | 10/06/2020 |
| 1.01 | logo, datasheet style update      | 08/05/2022 |
| 1.02 | CUI Devices rebranded to Same Sky | 09/12/2024 |

The revision history provided is for informational purposes only and is believed to be accurate.



Same Sky offers a one (1) year limited warranty. Complete warranty information is listed on our website.

Same Sky reserves the right to make changes to the product at any time without notice. Information provided by Same Sky is believed to be accurate and reliable. However, no responsibility is assumed by Same Sky for its use, nor for any infringements of patents or other rights of third parties which may result from its use.

Same Sky products are not authorized or warranted for use as critical components in equipment that requires an extremely high level of reliability. A critical component is any component of a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.

**sameskydevices.com**

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Same Sky:

[RDS-10S-74385-SMT-TR](#) [RDS-16S-74385-SMT-TR](#) [RDS-10S-74385-SMT](#) [RDS-16S-74385-SMT](#)