







Marshalling / Potential Distribution Terminal Block

CP8L32

CP8L32(I.S)H

CP8L32(I.S)



Dimensions

	8-Level Terminal Block 8 Potentials	8-Level Terminal Block 2 Potentials	8-Level Terminal Block 1 Potential
Width	6 mm	6 mm	6 mm
Length	58.8 mm	58.8 mm	58.8 mm
Height w DIN Rail	35 x 7.5 mm 35 x 15 mm	72.4 mm 79.9 mm	72.4 mm 79.9 mm
Weight per piece	48.4 g	49.2 g	50.3 g

Technical Data/Ratings

Approvals				
Wire Size (solid / stranded)	24-14 AWG	0.2-1.5 mm ²	24-14 AWG	0.2-1.5 mm ²
Voltage Rating	300 V	250V AC/DC	300 V	250V AC/DC
Current Rating	10 A	8 A	10 A	8 A
Insulation Material	Polyamide 66			

Installation Instructions

Wire Stripping Length	8 mm	8 mm	8 mm
Screwdriver	SCM0.6/3.5 (0.6 x 3.5 mm blade)	SCM0.6/3.5 (0.6 x 3.5 mm blade)	SCM0.6/3.5 (0.6 x 3.5 mm blade)

Terminal Blocks




	Cat. No.	Std. Pk.	Cat. No.	Std. Pk.	Cat. No.	Std. Pk.
Grey (standard)	CP8L32	50	CP8L32(I.S)H	50	CP8L32(I.S)	50
Blue BU	CP8L32/BU	50	CP8L32(I.S)H/BU	50	CP8L32(I.S)/BU	50
Black BL	CP8L32/BL	50	CP8L32(I.S)H/BL	50	CP8L32(I.S)/BL	50

Additional colors available.



Accessories

	Cat. No.	Std. Pk.	Cat. No.	Std. Pk.	Cat. No.	Std. Pk.
DIN Rail	2511120	20	2511120	20	2511120	20
	CA701-15/S	20	CA701-15/S	20	CA701-15/S	20
End Stop	CA103	50	CA103	50	CA103	50
	CA104	50	CA104	50	CA104	50
	CA202	25	CA202	25	CA202	25
Separator Plate with marking area	SPCP8L32	10	SPCP8L32	10	SPCP8L32	10
Retaining Bracket	RBCP8C32	10	RBCP8C32	10	RBCP8C32	10
Marking Tag	MT9	1 Pk. (100 tags)	MT9	1 Pk. (100 tags)	MT9	1 Pk. (100 tags)
	MT3.5V	1 Pk. (100 tags)	MT3.5V	1 Pk. (100 tags)	MT3.5V	1 Pk. (100 tags)



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Altech:](#)

[CP8L32\(I.S\)](#) [CP8L32](#) [CP8L32\(I.S\)H](#) [CP8L32/BL](#) [CP8L32/BU](#) [CP8L32/W](#) [CP8L32\(I.S\)/BL](#) [CP8L32\(I.S\)/BU](#)
[CP8L32\(I.S\)/W](#) [CP8L32\(I.S\)H/BL](#) [CP8L32\(I.S\)H/BU](#) [CP8L32\(I.S\)H/W](#)