




Item No.	TSP0000009D	Date	01.01.2017
		Revision	00
Description	Dual Connectors, Pre-wired, Male/Female, A-Coding, Straight and Right Angle Jacket	Page	1 of 4



Type Approved
Safety
Regular Production
Surveillance

www.tuv.com
ID 1111210483



Specifications are subject to change without notice.

Item No.	TSP0000009D	Date	01.01.2017
		Revision	00
Description	Dual Connectors, Pre-wired, Male/Female, A-Coding, Straight and Right Angle Jacket	Page	2 of 4

Table-1

M12x1 User-wired Plug/Socket, A-coding

No. of Poles/Wire	Length m ¹⁾	Connections	Conductor	End A-End B Connector	End A-End B Connector Gender	End A-End B Connector Orientation	Katlax Item No.
4/3	2	1, 3, 4	0.34 ² mm	M12-M12	Female-Male	Straight-Straight	CDF12S4-M12S3-02BP34
8/8	2	1-8	0.25 ² mm	M12-M12	Female-Male	Straight-Straight	CDF12S8-M12S8-02BPVC
4/3	2	1, 3, 4	0.34 ² mm	M12-M12	Female-Male	Angled-Straight	CDF12R4-M12S3-02BP34
4/4	2	1-4	0.34 ² mm	M12-M12	Female-Male	Angled-Straight	CDF12R4-M12S4-02BP34
4/4	2	1-4	0.34 ² mm	M12-M12	Female-Male	Angled ⁴⁾ -Straight	CDF12R4-M12S4-02BP34-2LED
4/4	2	1-4	0.34 ² mm	M12-M12	Female-Male	Angled ⁵⁾ -Straight	CDF12R4-M12S4-02BP34-3LED
4/4	2	1-4	0.34 ² mm	M12-M12	Female-Male	Straight-Straight	CDF12S4-M12S4-02BP34
8/8	2	1-8	0.25 ² mm	M12-M12	Female-Male	Angled-Straight	CDF12R8-M12S8-02BPVC
4/4	2	1-4	0.34 ² mm	M12-M12	Female-Male	Angled-Straight	CDF12R4-M12S4-02BPUR ³⁾
4/4	5	1-4	0.34 ² mm	M12-M12	Female-Male	Angled-Straight	CDF12R4-M12S4-05BPUR ³⁾
5/5	2	1-5	0.34 ² mm	M12-M12	Female-Male	Angled-Straight	CDF12R5-M12S5-02BP34
4/4	2	1-4	0.75 ² mm	M12-M12	Female-Male	Straight-Straight	CDF12S4-M12S4-02BP75
4/4	5	1-4	0.75 ² mm	M12-M12	Female-Male	Straight-Straight	CDF12S4-M12S4-05BP75
5/5	2	1-5	0.34 ² mm	M12-M12	Female-Male	Straight--Straight	CDF12S5-M12S5-02BP34
5/5	5	1-5	0.34 ² mm	M12-M12	Female-Male	Straight--Straight	CDF12S5-M12S5-05BP34
5/5	2	1-5	0.34 ² mm	M12-M12	Female-Female	Straight--Straight	CDF12S5-F12S5-02BPVC
4/4	0.2	1-4	0.34 ² mm	M8-M12	Female-Male	Straight-Straight	CDF08S4-M12S4-0.2BPVC
5/5	2.5	1-5	0.34 ² mm	M12-M12	Female-Male	Straight--Straight	CDF12S5-M12S5-2.5BPUR-S ²⁾³⁾
5/5	3.5	1-5	0.34 ² mm	M12-M12	Female-Male	Straight--Straight	CDF12S5-M12S5-3.5BPUR-S ²⁾³⁾
4/4	5	1-4	0.34 ² mm	M12-M12	Female-Male	Straight-Angled	CDF12S4-M12R4-05BPUR ³⁾

- 1) Fixed length with dual housing.
- 2) Shield on the knurl nut.
- 3) Cable sheath material PUR.
- 4) Orange jacket with 2 LED PNP.
- 5) Orange jacket with 3 LED PNP.



Table-2



Specifications are subject to change without notice.

Item No.	TSP0000009D	Date	01.01.2017
		Revision	00
Description	Dual Connectors, Pre-wired, Male/Female, A-Coding, Straight and Right Angle Jacket	Page	3 of 4

Connection details

Contact / Pole	Pin / Colour (Continuously)	Contact / Pole	Pin / Colour (Continuously)	Contact / Pole	Pin / Colour (Continuously)	Contact / Pole	Pin / Colour (Continuously)
1	1 / Brown	1	1 / Brown	1	1 / Brown	1	1 / White
3	3 / Blue	2	2 / White	2	2 / White	2	2 / Brown
4	4 / Black	3	3 / Blue	3	3 / Blue	3	3 / Green
		4	4 / Black	4	4 / Black	4	4 / Yellow
				5	5 / Grey	5	5 / Grey
						6	6 / Pink
						7	7 / Blue
						8	8 / Red










 <p>M12 Female</p>	 <p>M12 Female</p>  <p>M8 Female</p>	 <p>M12 Female</p>	 <p>M12 Female</p>
 <p>M12 Male</p>	 <p>M12 Male</p>	 <p>M12 Male</p>	 <p>M12 Male</p>

Table – 4

Cable length tolerance

≤0.3 m	+25 mm -0 mm
>0.3 m – 1.5 m	+50 mm -0 mm
>1.5 m – 3.0 m	+100 mm -0 mm
>3.0 m – 7.5 m	+150 mm -0 mm
>7.5 m	+5% -0%



Type Approved
Safety
Regular Production
Surveillance

www.tuv.com
ID 1111210483



Specifications are subject to change without notice.

Item No.	TSP0000009D	Date	01.01.2017
		Revision	00
Description	Dual Connectors, Pre-wired, Male/Female, A-Coding, Straight and Right Angle Jacket	Page	4 of 4

Execution	IEC / EN	
Locking	Screw with internal threads M12x1 and sealing (Neoprene) Locking nut material: Brass (CuZn), Nickel Plated or Zinc die-casted, Nickel Plated	
Jacket	PU (Polyurethane), Black colour standard	
Plug/Socket pin carrier	Nylon or PA (Polyamide)	
Encoding	A - Coding	
Pole/Cores	See Tables on Page 1 to 6	
Cable	3x0.25mm ² PVC Shielded/Unshielded 3x0.34mm ² PVC Unshielded 3x0.34mm ² PUR Shielded/Unshielded 4x0.25mm ² PVC Shielded/Unshielded 4x0.34mm ² PVC Shielded/Unshielded 4x0.34mm ² PUR Unshielded 5x0.34mm ² PVC Shielded/Unshielded 5x0.34mm ² PUR Unshielded	8x0.25mm ² PVC Shielded/Unshielded 8x0.25mm ² PUR Shielded 2x0.5mm ² PVC Unshielded 3x0.5mm ² PVC Shielded/Unshielded 4x0.5mm ² PVC Shielded/Unshielded 3x0.75mm ² PVC Unshielded 4x0.75mm ² PVC Unshielded
Braided shield / cover	Min. 80% 3x / 4x0.34mm ²	
Lead Shielding	Shield on the knurl nut	
Cable sheath	PVC or PUR, Black colour standard	
Cable length tolerance	See Table - 4	
Contact material	Socket: Brass (CuZn)	
Contact Surface	Gold flash	
Rated Voltage (IEC 60664-1)	3, 4 Poles 250 V AC/DC 5 Poles 60 V AC/DC 8 Poles 30 V AC/DC	
Current carrying capacity (IEC 60512-3-5d)	2 to 5 Poles = 4A 6 to 8 Poles = 2A	
Contact resistance (IEC 60512-2-2a)	As per manufacturer specification	
Insulation resistance (IEC 60512-2-3a)	As per manufacturer specification	
Mating cycles (IEC 60512-5-9a)	≥100	
Protection (IEC 60529)	IP67 (when plugged in)	
Pollution degree (IEC 60664-1)	3	
Test voltage (IEC 60664-1)	As per IEC/EN 61076-2-101	



Type Approved
Safety
Regular Production
Surveillance

www.tuv.com
ID 1111210483



Specifications are subject to change without notice.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Altech:

<u>CDF12R4-M12S4-02BP34</u>	<u>CDF12R4-M12S4-02BP75</u>	<u>CDF12S5-M12S5-10BPUR</u>	<u>CDF12S8-M12S8-02BP25</u>
<u>CDF12S8-M12S8-08BP25</u>	<u>CDF12S8-M12S8-10BP25</u>	<u>CDF12S4-M12S4-10BPUR</u>	<u>CDF12S5-M12S5-02BP34</u>
<u>CDF12S5-M12S5-02BPUR</u>	<u>CDF12S5-M12S5-05BP34</u>	<u>CDF12S5-M12S5-05BPUR</u>	<u>CDF12S5-M12S5-10BP34</u>
<u>CDF12S4-M12S4-02BPUR</u>	<u>CDF12S4-M12S4-05BP34</u>	<u>CDF12S4-M12S4-05BP75</u>	<u>CDF12S4-M12S4-05BPUR</u>
<u>CDF12S4-M12S4-10BP34</u>	<u>CDF12S4-M12S4-10BP75</u>	<u>CDF12R5-M12S5-10BPUR</u>	<u>CDF12R8-M12S8-02BP25</u>
<u>CDF12R8-M12S8-08BP25</u>	<u>CDF12R8-M12S8-10BP25</u>	<u>CDF12S4-M12S4-02BP34</u>	<u>CDF12S4-M12S4-02BP75</u>
<u>CDF12R4-M12S4-10BPUR</u>	<u>CDF12R5-M12S5-02BP34</u>	<u>CDF12R5-M12S5-02BPUR</u>	<u>CDF12R5-M12S5-05BP34</u>
<u>CDF12R5-M12S5-05BPUR</u>	<u>CDF12R5-M12S5-10BP34</u>	<u>CDF12R4-M12S4-02BPUR</u>	<u>CDF12R4-M12S4-05BP34</u>
<u>CDF12R4-M12S4-05BP75</u>	<u>CDF12R4-M12S4-05BPUR</u>	<u>CDF12R4-M12S4-10BP34</u>	<u>CDF12R4-M12S4-10BP75</u>