FCL

ULTRA MINITURE RELAY 2 POLE - 2A (SLIM PROFILE SIGNAL RELAY)

FTR-B4 Series

FEATURES

- DPDT 2c
- Ultra miniature slim type relay for surface mounting
 - Height: 9.3mm maximum (THT), 10mm maximum (SMT)
 - Weight: Approximately1.0 g
- UL, CSA recognized
- Conforms to Telcordia/FCC Part 68 spacing and high breakdown voltage
 - Creepage: 1.6mm
 - Dielectric strength: 1,500V (coil to contacts)
 - Surge strength: 2,500V
- High reliable bifurcated gold overlay silver contact
- Low power consumption: 140mW (standard), 100mW (latching)
- RoHS compliant
- Plastic sealed



■ APPLICATIONS

xDSL, modems, digital equipment (signal switching), STB (line switchig), car navigation system (audio switching)

PART NUMBERS

[Example] FTR-B4 G A 4.5 Z - B05

(a) (b) (c) (d) (e) (f)

(a)	Relay type	FTR-B4 series
(b)	Terminal type	C : Through hole G : Surface mount S : Surface mount, space saving
(c)	Coil type	A: Standard type (non-latching)B: Latching type (1 coil)
(d)	Coil rated voltage	4.5 : 1.524 VDC Please refer to coil rating table
(e)	Contact material	Z : Gold overlay silver nickel (standard) P : Gold overlay silver palladium
(f)	Packaging	Nil: Tube packagingB05: Tape & reel packaging (only for surface mount type)

Remarks: Actual marking on relay would not carry code FTR and be as below: Ordering code: FTR-B4GA012Z-B10 Actual marking: B4GA012Z



■ SPECIFICATIONS

			Specifi	cations	
Item			Standard type: Latching type:		Remarks/Conditions
			FTR-B4()A	FTR-B4()B	
Contact	act Configuration		2c (2 Form C)		
Data	Construction			d contacts	
			Z: Gold overlay silver nickel		
	Material		P: Gold overlay silver palladium		
	Resistance (initi	al)	Max. 100 mΩ		At 1A, 6VDC
	Contact rating	-	1A, 30VDC / (0.3A, 125VAC	Resistive
	Max. carrying cu	urrent	2	A	
	Max. switching	/oltage	250VAC/	/220VDC	
	Max. switching	oower	62.5V/	A/30W	
	Min. switching lo	pad [*]	0.01mA,	10mVDC	Reference
Coil	Rated power		140mW to 230mW	100mW to 130mW	At 20°C
	Applied pulse w	idth	-	Min. 10ms	At 20°C
	Operate power		80mW to 130mW	57mW to 68mW	At 20°C
	Operating tempe	erature rise	-40 °C to	o +85 °C	No frost
	Storage tempera	ature / humidity	-40 °C to +85 °C	/ 5% to 85% RH	No frost
Time	Operate		Max. 3 ms	Max. 3ms (set)	At nominal voltage, without bounce
	Release		Max. 3 ms	Max. 3ms (reset)	At nominal voltage, without bounce
Life	Mechanical		Min. 50 x 10 ⁶	Min. 20 x 10 ⁶	
			operations	operations	
	Electrical	DC load	Min. 100 x 10	0 ³ operations	At 1A, 30VDC
	Electrical	AC load	Min. 100 x 10 ³ operations		At 0.3A, 125VAC
Insulation	Insulation resistance (initial)		Min. 1,000MΩ		At 500VDC
	Dielectric	Open contacs	1,000VAC (50/60Hz) 1 minute		
	strength	Adjacent contacts	1,000VAC (50/60Hz) 1 minute		
	Stiength	Contact to coil	1,500VAC (50/60Hz) 1 minute		
	Surge strength	Contact to coil	2,500V, 2 x 10µs standard wave		
	Clearance	Open contacts	0.28mm		
		Adjacent contacts	1.0mm		
		Contact to coil	1.0mm		
	Creepage	Open contacts	0.28mm		
		Adjacent contacts	1.0mm		
		Contact to coil	1.6mm		
Others	Vibration	Misoperation	10 to 55 to 10Hz single amplitude 1.65mm		Coil ON/OFF, 3 axis, total 6 cycles
	resistance	Endurance	10 to 55 to 10Hz sing	gle amplitude 2.5mm	Coil OFF, 3 axis, total 6 hours
	Shock Misoperation		750m/s² (11 ±1ms)		Coil ON/OFF, 3 axis, total 36 operations
	resistance	Endurance	1,000m/s ² (6 ±1ms)		Coil OFF, 3 axis, total 18 operations
	Dimensions / Weight		5.7 x 10.6 x 9.0mm / Approx. 1.0g		
	Sealing		RT III (plastic sealed)		

* Minimum switching loads mentioned above are reference values. Please perform the confirmation test with actual load before production since reference values may vary according to switching frequencies, environmental conditions and expected reliability levels.

COIL DATA

Standard type

Coil Code	Rated Coil Voltage (VDC)	Coil Resistance (Ω) ±10%	Must Operate Voltage ^{*1} (VDC)	Must Release Voltage ^{*1} (VDC)	Rated Power (mW)
1.5	1.5	16.1	1.13	0.15	
003	3	64.3	2.25	0.3	
4.5	4.5	145	3.38	0.45	140
006	6	257	4.5	0.6	140
009	9	579	6.75	0.9	
012	12	1,028	9.0	1.2	
024	24	2,504	18.0	2.4	230

Latching type (1 coil)

Coil Code	Rated Coil Voltage (VDC)	Coil Resistance (Ω) ±10%	Set Voltage ^{*1} (VDC)	Reset Voltage ^{*1} (VDC)	Set/Reset Current (mA)	Rated power (mW)
1.5	1.5	22.5	+1.13	-1.13	50	
003	3	90	+2.25	-2.25	25	
4.5	4.5	203	+3.38	-3.38	17	100
006	6	360	+4.5	-4.5	13	100
009	9	810	+6.75	-6.75	8	
012	12	1,440	+9.0	-9.0	6	
024	24	4,800	+18.0	-18.0	4	120

Note: All values in the table are valid at 20°C and zero contact.


*: Specified operate values are valid for pulse wave voltage.

SAFETY STANDARDS

Туре	Compliance	Contact rating		
	Flammability: UL 94-V0 (plastics)			
UL	UL508	0.5A, 125VAC (resistive)		
	File No.E63615	1A, 30VDC		
CSA	C22.2 No.14	0.3A, 110VDC		
USA	File No.LR40304	2A, 30VDC		


Comply with Telcordia specifications and FCC part 68 and meet BSI EN60950-1: Marking only for UL, CSA

DIMENSIONS



■ COIL POLARITY LATCHING TYPE

Coil terminal	1	8
Set	+	-
Reset	-	+




PART NUMBER LIST

Part Number	Coil Type	Terminal Type	Contact Material	Packaging
FTR-B4CA()Z		Through hole	Gold overlay silver nickel	Tube
FTR-B4CA()P		Through hole	Gold overlay silver palladium	
FTR-B4GA()Z			Gold overlay silver nickel	Tube
FTR-B4GA()Z-B05				Tape & reel
FTR-B4GA()P	Standard			Tube
FTR-B4GA()P-B05	(Non latching)		Gold overlay silver palladium	Tape & reel
FTR-B4SA()Z				Tube
FTR-B4SA()Z-B05		Surface mount,	Gold overlay silver nickel	Tape & reel
FTR-B4SA()P		space saving Gold	Gold overlay silver palladium	Tube
FTR-B4SA()P-B05				Tape & reel
FTR-B4CB()Z		Thursday have	Gold overlay silver nickel	
FTR-B4CB()P		Through hole	Gold overlay silver palladium	Tube
FTR-B4GB()Z				Tube
FTR-B4GB()Z-B04		Surface mount	Gold overlay silver nickel	Tape & reel
FTR-B4GB()P	Latching (1 coil)	Sunace mount		Tube
FTR-B4GB()P-B05			Gold overlay silver palladium	Tape & reel
FTR-B4SB()Z			Gold overlay silver nickel	Tube
FTR-B4SB()Z-B05		Surface mount,		Tape & reel
FTR-B4SB()P		space saving		Tube
FTR-B4SB()P-B05			Gold overlay silver palladium	Tape & reel

CHARACTERISTIC DATA

(Characteristic data is not guaranteed value but measured values of samples from production line.)


Standard type



CHARACTERISTIC DATA

(Characteristic data is not guaranteed value but measured values of samples from production line.)

Latching type



CAUTIONS

- · All values mentioned in this datasheet are provided under ideal conditions. Please perform the confirmation test before actual use.
- · Reflow soldering is not available with standard type.
- · Do not use relays in the atmosphere with sulfide gas, chloride gas or nitric oxide. Contact resistance may increase.
- · Do not use silicon or silicon-containing product or materials near relays. It may cause contact failure.

Notes for latching relays


- Latching relays are shipped in the state reset, but state may change due to shock during transportation or mounting. Before using the relays, it is advisable to bring the relays in necessary state (set or reset) and program a circuit sequence. Otherwise, it will or will not operate simultaneously with power activation.
- Please connect relay coils according to specified polarity.
- · Do not apply voltage to both set coil and reset coil at a time.

GENERAL INFORMATION

1. RoHS Compliance

• All relays produced by FCL Components are compliant with RoHS directive 2011/65/EU, including commission delegated directive 2015/863.

2. Recommended lead free solder condition



Important notes for reflow soldering

- Temperature shall be measured at PC board upper surface.
- Temperature at PC board upper surface may be changed depending on size of PC board, components mounted on the PC board and/or heating method. Please perform the confirmation test with actual PC board.
- This reflow condition is applicable only for reflow-capable relays. Do not reflow reflow-incapable relays.
- Recommended solder for assembley: Sn-3.0 Ag -0.5 Cu.

We highly recommend that you confirm your actual solder conditions

3. Moisture Sensitivity

- SMT versions of FTR-B4 relays in Tape & Reel package will be shipped in Moisture Barrier Bag (MBB).
- · Moisture Sensitivity Level (MSL) of FTR-B4 relay is indicated on the packing caution label.
- Relays must be stored in the unopened MBB at strage conditions <40°C/90% RH for a maximum 1 year.
- SMT versions of FTR-B4 relays in tube packing will not be shipped in MBB. Therefore, these relays shall be dried by baking before reflow soldering process according to IPC/Jedex J-STD-033.

4. Tin Whiskers

• Dipped SnAgCu solder is known as presenting a low risk to tin whisker development. No considerable length whisker was found by our in house test.

Contact

Japan

FCL COMPONENTS LIMITED Shinagawa Seaside Park Tower 12-4, Higashi-shinagawa 4-chome, Tokyo 140 0002, Japan Tel: +81-3-3450-1682 Email: fcl-contact@cs.fcl-components.com

Asia Pacific

FCL COMPONENTS ASIA PTE LTD. No. 20 Harbour Drive, #07-01B Singapore 117612 Tel: +65-6375-8560 Email: fcal@fcl-components.com

North and South America

FCL COMPONENTS AMERICA, INC. 2055 Gateway Place Suite 480, San Jose, CA 95110 USA Tel: +1-408-745-4900 Email: contact@fcl-components.us

China

FCL COMPONENTS (SHANGHAI) CO.,LTD. Unit 1105, Central Park - Jing An, No.329 Heng Feng Road, Shanghai 200070, China Tel: +86-21-3253 0998 Email: fcsh@fcl-components.com

Europe

FCL COMPONENTS EUROPE B.V. Diamantlaan 25 2132 WV Hoofddorp, Netherlands Tel: +31-23-556-0910 Email: info.fceu@cs.fcl-components.com

Hong Kong

FCL COMPONENTS HONG KONG CO., LIMITED Unit 2313, Seapower Tower, Concordia Plaza, No.1 Science Museum Road, TST, Kowloon, Hong Kong Tel: +852-2881-8495 Email: fcal@fcl-components.com

Web: www.fcl-components.com/en/

© 2025 FCL Components Limited. All rights reserved. All trademarks or registered trademarks are the property of their respective owners.

FCL Components Products are intended for general use, including without limitation, in personal, household and office environments, in buildings and for ordinary use in the industry. FCL Components Products are not intended to be used in applications where extremely high safety is required ("High Safety Required Applications"), such as, but not limited to, applications in nuclear facilities, in aircraft automatic flight control, in air traffic control, in mass transit system control, in missile launch system, in weapon systems, in medical equipment for life support or any application involving a direct serious risk of physical injury or death.

Please do not use FCL Components Products without securing the sufficient safety and reliability required for the High Safety Required Applications.

In addition, FCL Components shall not be liable against the customer and/or any third party for any claims or damages arising in connection with the use of FCL Components Products in the High Safety Required Applications.

FCL Components warrants that its Products, if properly used and services, will conform to their specification and will be free from defects in material and workmanship for twelve months from delivery.

The implied warranties of merchantability and fitness for a particular purpose and all other warranties, representations and conditions, express or implied by statute, trade usage or otherwise, expect as set forth in this warranty, are excluded and shall not apply to the Products delivered.

The contents, data and information in this datasheet are provided by FCL Components Limited as a service only to its user and only for general information purposes. The use of the contents, data and information provided in this datasheet is at the users' own risk.

FCL Components has assembled this datasheet with care and will endeavor to keep the contents, data and information correct, accurate, comprehensive, complete and up to date.

FCL Components Limited and affiliated companies do however not accept any responsibility or liability on their behalf, nor on behalf of its employees, for any loss or damage, direct, indirect or consequential, with respect to this datasheet, its contents, data, and information and related graphics and the correctness, reliability, accuracy, comprehensiveness, usefulness, availability and completeness thereof. Nor do FCL Components Limited and affiliated companies accept on their behalf, nor on behalf of its employees, any responsibility or liability with respect to these datasheets, its contents, data, information and related graphics and the correctness, reliability, accuracy, comprehensiveness, usefulness, availability, accuracy, comprehensiveness, usefulness, availability, accuracy, comprehensiveness, usefulness, availability and completeness thereof. Rev. January 7, 2025.