

GFL Series - 1 Pole+N, B Trip, 300 mA 10kA UL489 Listed Branch Circuit Breaker with Equipment Ground Fault Protection (RCBO)

The GFL Series range is a combined Branch Circuit Breaker and Equipment Ground Fault Protector, featuring dual pole switching (live and neutral disconnect) and designed to provide protection against short circuits, overloads, AC ground faults (residual current faults) as well as pulsating DC ground faults.

Altech Corp.



Ordering Information


Rated Current	Type/ Cat. No.	Rated Voltage
5.0A	GFL2B053002	240V AC
6.0A	GFL2B063002	240V AC
8.0A	GFL2B083002	240V AC
10A	GFL2B103002	240V AC
12A	GFL2B123002	240V AC
13A	GFL2B133002	240V AC
15A	GFL2B153002	240V AC
16A	GFL2B163002	240V AC
20A	GFL2B203002	240V AC
25A	GFL2B253002	240V AC

Technical Specification

Number of Poles	1+N
Voltage Rating (maximum)	240V AC
Ground Fault Sensitivity Level	300 mA
Rated Short Circuit Interrupt Capacity	10 kA
Rated Frequency	50/60Hz
Trip Characteristic	B
Cable Size & Tightening Torque	Stranded Wire: 16 - 3 AWG (1.5 mm ² - 25 mm ²) @ 17.5 lb-in (2.0 Nm) Solid Wire: 16 - 10 AWG (1.5 mm ² - 5.5 mm ²) @ 17.5 lb-in (2.0 Nm) 18 - 16 AWG (1 mm ² - 1.5 mm ²) @ 25 lb-in (2.8 Nm)
Electrical Life	6000 Switching Operations
Mechanical Life	10000 Switching Operations

Dimensions


(to convert to inches multiply by 0.03937)




Weight

220 g




GFL Series RCBO Overload Trip Curves



GFL Series RCBO Ground Fault Trip Curve



GFL Series - 1 Pole+N, B Trip, 300 mA
Applicable voltage systems and wiring examples.



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Altech:](#)

[GFL2B083002](#) [GFL2B163002](#) [GFL2B253002](#) [GFL2B123002](#) [GFL2B153002](#) [GFL2B103002](#) [GFL2B133002](#)
[GFL2B203002](#) [GFL2B063002](#)