

Altech Corp.®

Quality System



Quality
Endorsed
Company

Features

- Small size
- Universal input
- Three-year Warranty



Class II Isolation

UL
C US
E521519
UL62368



CB



Low Profile Power Supplies

PSD-15 Series

FEATURES

- High Efficiency
- 100% Full Load Burn-In
- Low Ripple & Noise
- Adjustable DC Voltage Output
- Class II Isolation Level
- UL62368-1 and CAN / CSA C22.2
- Protections: Overload / Over Voltage / Short Circuit
- Three-year Warranty



Input: 90-240VAC 50/60Hz
Output Voltage: 5V-48V DC
Rated Power: 15W max.



CATALOG NUMBER

PSD-1505

PSD-1512

PSD-1515

PSD-1524

PSD-1548

INPUT

Input Voltage	90-264VAC				
Input Frequency	47-63Hz				
Inrush Current	25 Amps max. at 115VAC/60Hz, Full Load & 45Amps max. at 240VAC/50Hz, Full Load				
AC Current	0.5A/115VAC 0.25A/230VAC				
Leakage Current (MAX)	<0.25mA/240VAC				
Efficiency	79%	85%	85%	86%	87%

OUTPUT

DC Voltage	5V	12V	15V	24V	48V
Rated Current	2A	1.25A	1A	0.63A	0.32A
Rated Power	10W	15W	15W	15W	15W
Ripple and Noise	80mVp-p	120mVp-p	120mVp-p	150mVp-p	240mVp-p
Line Regulation	±1%				
Load Regulation	±1%				
Setup, Rise, Hold Up Time	2S/ 80mS/ 15mS (115V/60HZ MAX ROAD); 1S/ 80mS/ 30mS (230V/50HZ MAX ROAD)				

ENVIRONMENTAL

Operating Temperature	-20°C to 50°C, Full Load, Normal Operation
Storage Temperature	-40°C to 80°C
Storage Humidity	10 ~ 95% RH
Working Humidity	20% ~ 90% RH Non-Condensing

PROTECTIONS

Overload Protection	>130%-200% Rated Output Power Protection type: Hiccup Mode- recovers automatically after fault condition is removed
Over Voltage Protection	110~145% Protection Type: Clamp by Zener diode
Short Circuit Protection	Protection to Zero Voltage
Over Current Protection	110%-180%

SAFETY & EMC


Safety Regulations	UL60950-1, UL508, BSMI CNS14336-1, TUV EN61558-2-16 IEC60950-1, EAC TPTC 004, TUV EN60950-1 UL62368-1 and CAN / CSA C22.2 No.62368-1-14
Withstand Voltage	I/P-O/P: 3KVAC
Isolation Resistance	I/P-O/P: 100M Ohms / 500VDC / 25 / 70% RH
EMC Emission	EN55032(CISPR32), CNS13438 Class B, EN61000-3-2 Class A, EN61000-3-3, EN61000-4-2,3,4,5,6,8,11, EN55024, EN55035, EN61000-6-2, EN61204-3

OTHER


MTBF	200,000 Hours Minimum at Full Load at 25°C Ambient
Size	90 x 18 x 58mm
Weight	78g / pcs
Packaging	100PCS/CTN

Mechanical Specification


Pin #	Assignment	Pin #	Assignment
1	+V	3	AC / N
2	-V	4	AC / L




Block Diagram



Deduction Curve and Temperature:



Minus Output and Input Voltage Curves:



PSD-30 Series

FEATURES

- High Efficiency
- 100% Full Load Burn-In
- Low Ripple & Noise
- Adjustable DC Voltage Output
- Class II Isolation Level
- UL62368-1 and CAN / CSA C22.2
- Protections: Overload / Over Voltage / Short Circuit
- Three-year Warranty



Input: 90-240VAC 50/60Hz
Output Voltage: 5V-48V DC
Rated Power: 30W max.



CATALOG NUMBER

PSD-3005

PSD-3012

PSD-3015

PSD-3024

PSD-3048

INPUT

Input Voltage	90-264VAC				
Input Frequency	47-63Hz				
Inrush Current	25 Amps max. at 115VAC/60Hz, Full Load & 45Amps max. at 240VAC/50Hz, Full Load				
AC Current	0.88A/115VAC 0.48A/230VAC				
Leakage Current (MAX)	<0.25mA/240VAC				
Efficiency	82%	88%	89%	89%	90%

OUTPUT

DC Voltage	5V	12V	15V	24V	48V
Rated Current	3A	2A	2A	1A	0.6A
Rated Power	15W	24W	30W	24W	29W
Ripple and Noise	80mVp-p	120mVp-p	120mVp-p	150mVp-p	240mVp-p
Line Regulation	±1%				
Load Regulation	±1%				
Setup, Rise, Hold Up Time	500mS/ 50mS/ 12mS (115V/60HZ MAX ROAD) 500mS/ 50mS/ 30mS (230V/50HZ MAX ROAD)				

ENVIRONMENTAL

Operating Temperature	-20°C to 50°C, Full Load, Normal Operation
Storage Temperature	-40°C to 80°C
Storage Humidity	10 ~ 95% RH
Working Humidity	20% ~ 90% RH Non-Condensing

PROTECTIONS

Overload Protection	>130%-200% Rated Output Power Protection type: Hiccup Mode- recovers automatically after fault condition is removed
Over Voltage Protection	110~145% Protection Type: Clamp by Zener diode
Short Circuit Protection	Protection to Zero Voltage
Over Current Protection	110%-180%

SAFETY & EMC



Safety Regulations	UL60950-1, UL508, BSMI CNS14336-1, TUV EN61558-2-16 IEC60950-1, EAC TPTC 004, TUV EN60950-1 UL62368-1 and CAN / CSA C22.2 No.62368-1-14
Withstand Voltage	I/P-O/P: 3KVAC
Isolation Resistance	I/P-O/P: 100M Ohms / 500VDC / 25 / 70% RH
EMC Emission	EN55032 (CISPR32), CNS13438 Class B, EN61000-3-2 Class A, EN61000-3-3, EN61000-4-2,3,4,5,6,8,11, EN55024, EN55035, EN61000-6-2, EN61204-3

OTHER


MTBF	200,000 Hours Minimum at Full Load at 25°C Ambient
Size	90 x 35 x 58mm
Weight	120g / pcs
Packaging	100PCS/CTN

For the latest on Altech Power Supply specifications please visit www.altechcorp.com/power.


Dimensions and Installation:



Deduction Curve and Temperature:




Minus Output and Input Voltage Curves:



PSD-60 Series

FEATURES

- High Efficiency
- 100% Full Load Burn-In
- Low Ripple & Noise
- Adjustable DC Voltage Output
- Class II Isolation Level
- UL62368-1 and CAN / CSA C22.2
- Protections: Overload / Over Voltage / Short Circuit
- Three-year Warranty



Input: 90-240VAC 50/60Hz
Output Voltage: 5V-48V DC
Rated Power: 60W max.



CATALOG NUMBER

PSD-6005

PSD-6012

PSD-6015

PSD-6024

PSD-6048

INPUT

INPUT	Input Voltage	90-264VAC									
Input Frequency	47-63Hz										
Inrush Current	30Amps max. at 115VAC/60Hz, Full Load & 60Amps max. at 240VAC/50Hz, Full Load										
AC Current	1.2A/115VAC 0.8A/230VAC										
Leakage Current (MAX)	<0.25mA/240VAC										
Efficiency	85%	88%	89%	90%	91%						

OUTPUT

DC Voltage	5V	12V	15V	24V	48V
Rated Current	4.5A	4.5A	4A	2.5A	1.25A
Rated Power	23W	54W	60W	60W	60W
Ripple and Noise	80mVp-p	120mVp-p	120mVp-p	150mVp-p	240mVp-p
Line Regulation	±1%				
Load Regulation	±1%				
Setup, Rise, Hold Up Time	500mS/ 80mS/ 12mS (115V/60HZ MAX ROAD) 500mS/ 80mS/ 30mS (230V/50HZ MAX ROAD)				

ENVIRONMENTAL

Operating Temperature	-20°C to 50°C, Full Load, Normal Operation
Storage Temperature	-40°C to 80°C
Storage Humidity	10 ~ 95% RH
Working Humidity	20% ~ 90% RH Non-Condensing

PROTECTIONS

Overload Protection	>130%-200% Rated Output Power Protection type: Hiccup Mode- recovers automatically after fault condition is removed
Over Voltage Protection	110~145% Protection Type: Clamp by Zener diode
Short Circuit Protection	Protection to Zero Voltage
Over Current Protection	110%-180%

SAFETY & EMC



Safety Regulations	UL60950-1, UL508, BSMI CNS14336-1, TUV EN61558-2-16 IEC60950-1, EAC TPTC 004, TUV EN60950-1 UL62368-1 and CAN / CSA C22.2 No.62368-1-14
Withstand Voltage	I/P-O/P: 3KVAC
Isolation Resistance	I/P-O/P: 100M Ohms / 500VDC / 25 / 70% RH
EMC Emission	EN55032 (CISPR32), CNS13438 Class B, EN61000-3-2 Class A, EN61000-3-3, EN61000-4-2,3,4,5,6,8,11, EN55024, EN55035, EN61000-6-2, EN61204-3

OTHER


MTBF	200,000 Hours Minimum at Full Load at 25°C Ambient
Size	90 x 52.5 x 58mm
Weight	190g / pcs
Packaging	100PCS/CTN

For the latest on Altech Power Supply specifications please visit www.altechcorp.com/power.


Dimensions and Installation:



Deduction Curve and Temperature:



Minus Output and Input Voltage Curves:



PSD-100 Series

FEATURES

- High Efficiency
- 100% Full Load Burn-In
- Low Ripple & Noise
- Adjustable DC Voltage Output
- Class II Isolation Level
- UL62368-1 and CAN / CSA C22.2
- Protections: Overload / Over Voltage / Short Circuit
- Three-year Warranty



Input: 90-240VAC 50/60Hz
Output Voltage: 5V-48V DC
Rated Power: 100W max.




CATALOG NUMBER	PSD-10012	PSD-10015	PSD-10024	PSD-10048	
INPUT	Input Voltage	90-264VAC			
	Input Frequency	47-63Hz			
	Inrush Current	35Amps max. at 115VAC/60Hz, Full Load & 70Amps max. at 240VAC/50Hz ,Full Load			
	AC Current	3A/115VAC 1.6A/230VAC			
	Leakage Current (MAX)	<0.25mA/240VAC			
	Efficiency	88%	89%	90%	90%
OUTPUT	DC Voltage	12V	15V	24V	48V
	Rated Current	7.1A	6.13A	3.8A	2.1A
	Rated Power	86W	92W	91W	100W
	Ripple and Noise	120mVp-p	120mVp-p	150mVp-p	240mVp-p
	Line Regulation	±1%			
	Load Regulation	±1%			
	Setup, Rise, Hold Up Time	500mS/ 60mS/ 12mS (115V/60HZ MAX ROAD) 500mS/ 60mS/ 30mS (230V/50HZ MAX ROAD)			
ENVIRONMENTAL	Operating Temperature	-20℃ to 50℃, Full Load, Normal Operation.			
	Storage Temperature	-40℃ to 80℃			
	Storage Humidity	10 ~ 95% RH			
	Working Humidity	20% ~ 90% RH Non-Condensing			
PROTECTIONS	Overload Protection	>130%-200% Rated Output Power Protection type: Hiccup Mode- recovers automatically after fault condition is removed			
	Over Voltage Protection	110~145% Protection Type: Clamp by Zener diode			
	Short Circuit Protection	Protection to Zero Voltage			
	Over Current Protection	110%-180%			
SAFETY & EMC	Safety Regulations	UL60950-1, UL508, BSMI CNS14336-1, TUV EN61558-2-16 IEC60950-1, EAC TPTC 004, TUV EN60950-1 UL62368-1 and CAN / CSA C22.2 No.62368-1-14			
	Withstand Voltage	I/P-O/P: 3KVAC			
	Isolation Resistance	I/P-O/P: 100M Ohms / 500VDC / 25 / 70% RH			
	EMC Emission	EN55032 (CISPR32), CNS13438 Class B, EN61000-3-2 Class A, EN61000-3-3, EN61000-4-2,3,4,5,6,8,11, EN55024, EN55035, EN61000-6-2, EN61204-3			
OTHER	MTBF	200,000 Hours Minimum at Full Load at 25℃ Ambient			
	Size	90 x 70 x 58mm			
	Weight	270g / pcs			
	Packaging	50 PCS/CTN			


For the latest on Altech Power Supply specifications please visit www.altechcorp.com/power.

Mechanical Specification


Pin #	Assignment	Pin #	Assignment
1,2	-V	5	AC / L
3,4	+V	6	AC / N
O	Voltage adjuster		




Block Diagram



Deduction Curve and Temperature:



Minus Output and Input Voltage Curves:



Altech Search

Google



WEB TOOLS

Drawings & Photos

Enclosure Finder

Altech Videos

Request for Quote

Sample Request

Catalog Request

Product Crossings

eBook Catalog

PRODUCT MENU

ATEX Products

Circuit Protection/Control >

Connectors >

Enclosures >

Fuses >

Digital Panel Meters

Foot Switches

Interface Modules >

Panel Accessories

Power Supplies

Power Semi-Conductors

PCB Connection Technology >

Programmable Controllers

Push Buttons & Pilot Lights >

Relays >

Sensors >

Safety Switches >

Standard Switches >

Solid State Relays

Terminal Blocks >

Test & Measurement

Tower Lights

Home Stock Check Distributors Information News Contact Rep/Dist Login Altech Mexico

New Products and Promotions

The NEW

Altech



ENCLOSURE FINDER

Click here to begin

CIRCUIT PROTECTION



Circuit
Protection
Devices



Busbar
& Power
Distribution



Contactors,
Overload
Relays, Manual
Motor Starters



Motor
Disconnect
Switches



European
Fuses &
Holders

CONNECTORS



Pin & Sleeve
Devices



Receptacles

ENCLOSURES



Industrial
& ATEX
Enclosures



DIN
Enclosures



Control
Enclosures and
Suspension
Systems

FOOT SWITCHES



Industrial



Medical

MODULES & RELAYS



Interface
Modules



Safety
Relays



Industrial
& Slimline
Relays

PANEL ACCESSORIES



Panel Lights



Heaters,
Filters &
Thermostats

SPARE PARTS



European
Spare Parts

PILOT DEVICES



22 & 30 mm
Push Buttons
& Enclosures



Pilot Lights
& E-Stops

POWER DEVICES



Power
Supplies



DC-UPS &
Battery
Chargers

POWER MANAGEMENT



Altech
Smart Relays



Digital
Panel Meters



Digital
Timers

SAFETY SWITCHES



Keyed
Safety
Switches




Keyed
Solenoid
Locking
Switches



Hinged
Safety
Switches



Non-Contact
Safety
Switches



Safety
Rope Pull
Switches

STANDARD SWITCHES



Limit
Switches



Foot
Switches



Cylindrical &
Capacitive



Flat Pack
& Ring



Metal
Detection

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Altech:](#)

[PSD-10012](#) [PSD-10015](#) [PSD-10024](#) [PSD-10048](#) [PSD-1505](#) [PSD-1512](#) [PSD-1515](#) [PSD-1524](#) [PSD-1548](#) [PSD-](#)
[3005](#) [PSD-3012](#) [PSD-3015](#) [PSD-3024](#) [PSD-3048](#) [PSD-6005](#) [PSD-6012](#) [PSD-6015](#) [PSD-6024](#) [PSD-6048](#)