

900 MHz 8 dBi Omnidirectional Antenna



Antennas Technical Data Sheet

PE51OM1016

Features

- Superior all weather performance
- Rugged industrial grade design
- Lightweight fiberglass radome
- Integral N-Female connector
- Heavy-duty steel mounting bracket

Applications

- 900 MHz ISM band
- LPWAN, LoRA, IoT, M2M applications
- GSM, SCADA applications
- 900 MHz cellular band
- Point to multi-point and Non Line Of Sight (NLOS) applications

Description

The HyperLink PE51OM1016 is a high performance omnidirectional antenna designed for the 900 MHz ISM band. It is ideally suited for multipoint, Non Line of Sight (NLOS) and mobile applications where high gain and wide coverage is desired. Typical applications include 900MHz Wireless LAN, SCADA, Wireless Video Links, LPWAN/IoT/M2M, and 900MHz Cellular band applications.

This antenna features an integral N-Female type connector that mounts through the wall of an equipment enclosure. Included with the PE51OM1016 is a dual u-bolt mast mounting kit. Consisting of a heavy-duty steel bracket and a pair of U-bolts, this kit allows installation on masts up to 2.0" in diameter.

This omni antenna's construction features a rugged 1.58" diameter fiberglass radome for durability, aesthetics and long service life. It is designed for all weather operation.

Configuration

Design	Omni
Band Type	Single
Radiation Pattern	Omni Directional
Polarization	Vertical
Cable Type	Coax lead
Connector Type	N Female
Number of Ports	1
Lightning Protection	DC Ground

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	900		928	MHz
Input VSWR		1.5:1	1.5:1	
Impedance		50		Ohms
Gain		8		dBi
Horizontal (Azimuth) Beam Width		Omnidirectional		
Vertical (Elevation) Beam Width		12		Degrees
Input Power			100	Watts

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [900 MHz 8 dBi Omnidirectional Antenna PE51OM1016](#)

900 MHz 8 dBi Omnidirectional Antenna



Antennas Technical Data Sheet

PE510M1016

Mechanical Specifications

Radome Material

Fiberglass

Size

Radome Diameter

1.5 in [38.1 mm]

Overall Length

63 in [160.02 cm]

Width

1.5 in [38.1 mm]

Height

1.5 in [38.1 mm]

Mounting Mast Diameter

1.2 to 2 in [30.48 to 50.80 mm]

Weight

7.2 lbs [3.27 kg]

Environmental Specifications

Temperature

Operating Range

-40 to +60 deg C


Wind Loading

130 MPH [209.21 KPH]

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:



Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [900 MHz 8 dBi Omnidirectional Antenna PE510M1016](#)

900 MHz 8 dBi Omnidirectional Antenna



Antennas Technical Data Sheet

PE51OM1016

900 MHz 8 dBi Omnidirectional Antenna from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.


Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: **900 MHz 8 dBi Omnidirectional Antenna PE51OM1016**

URL: <https://www.pasternack.com/single-antenna-8-dbi-gain-n-pe51om1016-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

PE51OM1016 CAD Drawing
900 MHz 8 dBi Omnidirectional Antenna

REVISIONS			
REV.	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	2/13/2020	M.MILLER



UNLESS OTHERWISE SPECIFIED
LEADING DIMENSIONS ARE INCHES
DIMENSIONS IN [] ARE MILLIMETERS

TOLERANCES:

.X = ± .2	[.08]	FRACTIONS
.XX = ± .02	[.51]	± 1/32
.XXX = ± .005	[.13]	ANGLES ± 1°

CABLE LENGTH (L) TOLERANCES:

L ≤ 12 [305]	= +1 [25] / -0
12 [305] < L ≤ 60 [1524]	= +2 [51] / -0
60 [1524] < L ≤ 120 [3048]	= +4 [102] / -0
120 [3048] < L ≤ 300 [7620]	= +6 [152] / -0
300 [7620] < L	= +5% L / -0

ALL DIMENSIONS SHOWN
ARE FOR REFERENCE ONLY.

PE PASTERNAK®
an INFINITI® brand

Pasternack Enterprises, Inc.
P.O. Box 16759, Irvine, CA 92623.
Phone: 1.949.261.1920 | 1.866.727.8376
Fax: 1.949.261.7451
Website: www.pasternack.com
E-mail: sales@pasternack.com

THIRD-ANGLE PROJECTION

THE INFORMATION AND
DESIGN IN THIS DOCUMENT
IS THE PROPERTY OF
PASTERNAK CORPORATION
ALL RIGHTS RESERVED.

SHEET 1 OF 1

SCALE N/A

REV

REV A

SIZE A

CAGE CODE 53919

DRAWN BY K.DANG

ITEM NO. PE51OM1016

REGULATORY COMPLIANCE:
EU ROHS DIRECTIVE (MOST RECENT RELEASED VERSION)

THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Pasternack:](#)

[PE51OM1016](#)