


Protection class IP 65



Protection class IP 65





Si-U1Z	SiU-UV1Z	SEK-U1Z	SiEK-UV1Z
601.3812.075	601.3832.076	601.1811.133	601.1831.134
⊕ Zb	⊕ Zb	⊕ Zb	⊕ Zb
●/-	●/-	●/-	●/-
-	-	-	-



500 V AC	500 V AC	500 V AC	500 V AC
10 A	10 A	10 A	10 A
●	●	●	●
50/min.	50/min.	50/min.	50/min.
1 x 10 ⁶	1 x 10 ⁶	1 x 10 ⁶	1 x 10 ⁶
-30 °C/+80 °C	-30 °C/+80 °C	-30 °C/+80 °C	-30 °C/+80 °C
-22 °F/+176 °F	-22 °F/+176 °F	-22 °F/+176 °F	-22 °F/+176 °F

UL, CSA	UL, CSA	BG, UL, CSA	BG, UL, CSA
1 x M 20 x 1.5 0.09 kg/0.20 lb	1 x M 20 x 1.5 0.09 kg/0.20 lb	1 x M 20 x 1.5 0.17 kg/0.37 lb	1 x M 20 x 1.5 0.17 kg/0.37 lb
●/—	●/—	●/—	●/—

All dimensions in mm (inch)





SEM2-U1Z

SIEM2-UV1Z

SIEM2-UV1Z Rast

SD-U1

SD-U1






601.2811.029

601.2831.022

601.2831.023

601.1411.856

611.1411.029



⊕ Zb

⊕ Zb

⊕ Zb

●/-






●/-

●

-

●/-

●/-



400 V AC

400 V AC

400 V AC

500 V AC

500 V AC

10 A

10 A

10 A

16 A

16 A

●

●

●

●

●

50/min.

50/min.

17/min.

50/min.

50/min.

1 x 10⁶1 x 10⁶1 x 10⁶1 x 10⁶1 x 10⁶

-30 °C/+80 °C

-30 °C/+80 °C

-30 °C/+80 °C

-30 °C/+80 °C

-30 °C/+80 °C

-22 °F/+176 °F

-22 °F/+176 °F

-22 °F/+176 °F

-22 °F/+176 °F

-22 °F/+176 °F

BG, UL, CSA

BG, UL, CSA

BG, UL, CSA

UL, CSA

UL, CSA

1 x M 20 x 1.5

1 x M 20 x 1.5

1 x M 20 x 1.5

2 x M 20 x 1.5

2 x M 20 x 1.5

0.22 kg/0.49 lb

0.22 kg/0.49 lb

0.26 kg/0.57 lb

0.33 kg/0.73 lb

0.33 kg/0.73 lb




●/-

●/-

●/-


●/-

●/-






SI-D-UV1Z Rast
611.1431.060



⊕ Zb

●/-

●



400 V AC
16 A

●

20/min.

1 x 10⁶

-30 °C/+80 °C

-22 °F/+176 °F


UL, CSA

2 x M 20 x 1.5

0.53 kg/1.17 lb

●/-


SI-D-UV1Z
601.2431.877



⊕ Zb

●/-

-



500 V AC
16 A

●

50/min.

1 x 10⁶

-30 °C/+80 °C

-22 °F/+176 °F


UL, CSA

2 x M 20 x 1.5

0.47 kg/1.04 lb

●/-


SI-D-UV1Z Rast
601.2431.883



⊕ Zb

●/-

●



500 V AC
16 A

●

20/min.

1 x 10⁶

-30 °C/+80 °C

-22 °F/+176 °F


UL, CSA

2 x M 20 x 1.5

0.70 kg/1.54 lb

●/-


SI-D-UV1Z Rast
611.2431.050



⊕ Zb

●/-

●



500 V AC
16 A

●

20/min.

1 x 10⁶

-30 °C/+80 °C



-22 °F/+176 °F

UL, CSA

2 x M 20 x 1.5

0.64 kg/1.41 lb

●/-







Metal bodied Rope Pull switches S/Si

Protection class IP 65



Designation
Part number
Circuit diagram
⤵ Forced disconnect to IEC 947-5-1 chapter 3
Za: not galvanically separated contacts
Zb: galvanically separated contacts
Slow make & break/snap-action
Internal seal (iw)/external seal (w)

SiD-UV2Z Rast	SiD-UV1Z/E1 Rast	SiN-UV1Z P-Rast
601.2441.907	611.2461.041	601.3531.367
13 — 14 25 — 26 33 — 34 45 — 46 ⊕ Zb	13 — 14 25 — 26 33 — 34 ⊕ Zb	15 — 16 23 — 24 ⊕ Zb
●/—	●/—	●/—
●	●	●





Voltage	max.
Permanent current	max.
In-rush current complies with standards	
Switching frequency	max.
Mechanical life – number of switching actions	
Operating temperature	min./max.

400 V AC	400 V AC	500 V AC
16 A	16 A	16 A
●	●	●
20/min.	20/min.	20/min.
1 x 10 ⁶	1 x 10 ⁶	1 x 10 ⁶
-30 °C/+80 °C	-30 °C/+80 °C	-30 °C/+80 °C
-22 °F/+176 °F	-22 °F/+176 °F	-22 °F/+176 °F

Approvals
Cable entry
Weight
Delivery: ex-stock/built to order


UL, CSA	UL, CSA	UL, CSA
2 x M 20 x 1.5	2 x M 20 x 1.5	2 x M 20 x 1.5
0.70 kg/1.54 lb	0.70 kg/1.54 lb	1.30 kg/2.87 lb
●/—	●/—	●/—

All dimensions in mm (inch)






Si1-U2Z AK R-Rast
601.4735.001



⊕ Zb
●/-
●

Si1-U1Z/U1Z AK R-Rast
601.4735.025




⊕ Zb
●/-
●


Si2-U2Z AK R-Rast
601.5735.002




⊕ Zb
●/-
●



250 V AC
10 A
●



250 V AC
10 A
●



500 V AC
10 A
●

10/min.

1 x 10⁶
-30 °C/+80 °C
-22 °F/+176 °F

UL, CSA

1 x M 20 x 1.5
1.60 kg/3.53 lb
●/-

10/min.

1 x 10⁶
-30 °C/+80 °C
-22 °F/+176 °F

BG, UL, CSA



1 x M 20 x 1.5
1.60 kg/3.53 lb
●/-

10/min.

1 x 10⁶
-30 °C/+80 °C
-22 °F/+176 °F

UL, CSA

3 x M 20 x 1.5
3.80 kg/8.38 lb
●/-



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Altech:](#)

[601.2431.883](#)