

## Low Loss RA TNC Male to RA TNC Male Cable LL160 Coax in 60 Inch

The RA TNC Male to RA TNC Male low loss cable using LL160 coax, part number FMCA1690-60, from Fairview Microwave is in-stock and ships same day. This TNC to TNC low loss cable assembly features a 82.5% velocity dielectric manufactured from expanded PTFE tape. This microporous dielectric contributes to the low loss and phase stability of the cables. Our triple shielded coaxial cable construction of Fairview's low loss LL160 provides shielding levels as high as 95 dB. The precision connections are constructed with stainless steel bodies and high temperature insulators, supporting a wide range of temperature from -55 to +165 degrees C. This solid combination of connectors and low loss coax are further enhanced with the addition of heavy-duty heat shrink for improved strain relief for this superior quality RF cable assembly.

Fairview's RA TNC Male to RA TNC Male low loss cable FMCA1690-60 datasheet, specifications and outline drawing are shown in this PDF below. Our extensive offering of RF, microwave and high speed digital connections allows designers to configure and customize their signals however they like. From reducing losses or improving phase stability, Fairview microwave has the right low loss cable solutions to meet your needs.

### Electrical Specifications

| Description             | Min | Typ        | Max   | Units        |
|-------------------------|-----|------------|-------|--------------|
| Frequency Range         | DC  |            | 18    | GHz          |
| VSWR                    |     |            | 1.5:1 |              |
| Velocity of Propagation |     | 82.5       |       | %            |
| RF Shielding            | -90 |            |       | dB           |
| Capacitance             |     | 25 [82.02] |       | pF/ft [pF/m] |

### Performance by Frequency

| Description           | F1  | F2 | F3   | F4   | F5   | Units |
|-----------------------|-----|----|------|------|------|-------|
| Frequency             | 1   | 2  | 4.5  | 9    | 18   | GHz   |
| Insertion Loss (Typ.) | 0.7 | 1  | 1.52 | 2.18 | 3.15 | dB    |

#### Electrical Specification Notes:

The Insertion Loss data above is based on the performance specifications of the coax cable used in this assembly. The Insertion Loss includes an estimated insertion loss of  $0.10 \times \sqrt{F(\text{GHz})}$  dB maximum per connector.

### Mechanical Specifications

#### Cable Assembly

Length\* 60 in [152.4 cm]

#### Cable

Cable Type LL160  
Impedance 50 Ohms  
Inner Conductor Type Solid  
Inner Conductor Material and Plating Copper, Silver  
Dielectric Type PTFE  
Number of Shields 3  
Shield Layer 1 Silver Plated Copper



### Configuration:

- TNC Male Right Angle
- TNC Male Right Angle
- LL160

### Features:

- Max Frequency 18 GHz
- Shielding Effectivity > -90 dB
- 82.5% Phase Velocity
- Triple Shielded
- FEP Jacket
- Low VSWR of 1.35:1 to 18 GHz
- -55 to +150 Temperature Range
- Expanded PTFE Tape Dielectric
- Same Day Shipment of Custom Lengths

### Applications:

- General Purpose
- Laboratory Use
- Automated Test Systems
- Military Electronics
- Phased Array Antennas
- RF Countermeasures

### Cable Diagram:



Fairview Microwave  
301 Leora Ln., Suite 100  
Lewisville, TX 75056  
Tel: 1-800-715-4396 / (972) 649-6678  
Fax: (972) 649-6689  
[www.fairviewmicrowave.com](http://www.fairviewmicrowave.com)  
[sales@fairviewmicrowave.com](mailto:sales@fairviewmicrowave.com)

|                 |                      |
|-----------------|----------------------|
| Shield Layer 2  | Aluminum Polyester   |
| Shield Layer 3  | Silver Plated Copper |
| Jacket Material | FEP                  |
| Jacket Diameter | 0.16 in [4.06 mm]    |

|                              |                   |
|------------------------------|-------------------|
| Repeated Minimum Bend Radius | 0.8 in [20.32 mm] |
|------------------------------|-------------------|

### Connectors

| Description                     | Connector 1                | Connector 2                |
|---------------------------------|----------------------------|----------------------------|
| Type                            | TNC Male Threaded          | TNC Male Threaded          |
| Impedance                       | 50 Ohms                    | 50 Ohms                    |
| Contact Material & Plating      | Beryllium Copper, Gold     | Beryllium Copper, Gold     |
| Contact Plating Spec.           | ASTM-B488                  | ASTM-B488                  |
| Dielectric Type                 | PTFE                       | PTFE                       |
| Body Material & Plating         | Passivated Stainless Steel | Passivated Stainless Steel |
| Coupling Nut Material & Plating | Passivated Stainless Steel | Passivated Stainless Steel |

### Environmental Specifications

#### Temperature

|                 |                   |
|-----------------|-------------------|
| Operating Range | -55 to +165 deg C |
|-----------------|-------------------|

### Compliance Certifications (see [product page](#) for current document)

### Plotted and Other Data

Notes:

### How to Order

Part Number Configuration:

**FMCA1690 - xx uu**

cm = Centimeters  
 <blank> = Inches  
 Length

Example: FMCA1690-12 = 12 inches long cable  
 FMCA1690-100cm = 100 cm long cable


Low Loss RA TNC Male to RA TNC Male Cable LL160 Coax in 60 Inch from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link to obtain additional part information: [Low Loss RA TNC Male to RA TNC Male Cable LL160 Coax in 60 Inch FMCA1690-60](https://www.fairviewmicrowave.com/low-loss-ra-tnc-male-ra-tnc-male-cable-ll160-coax-fmca1690-60-p.aspx)

URL: <https://www.fairviewmicrowave.com/low-loss-ra-tnc-male-ra-tnc-male-cable-ll160-coax-fmca1690-60-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.





**NOTES:**

1. BLACK HEAT SHRINK WITH WHITE MARKINGS 3 PLACES.

**STANDARD TOLERANCES**

.X  $\pm 0.2$   
.XX  $\pm 0.01$   
.XXX  $\pm 0.005$

\*STANDARD TOLERANCES APPLY ONLY TO DIMENSIONS IN INCHES

|                                                                             |                    |                                                                                                                                                                                     |                         |
|-----------------------------------------------------------------------------|--------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-------------------------|
| <b>FAIRVIEW MICROWAVE INC.</b><br>ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM |                    | NOTES:<br>1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.<br>2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.<br>3. DIMENSIONS ARE IN INCHES [mm]. |                         |
| TITLE                                                                       | DWG NO<br>FMCA1690 |                                                                                                                                                                                     | CAGE CODE<br>3FKR5      |
|                                                                             | CAD FILE 07/12/18  | SHEET                                                                                                                                                                               | SCALE N/A SIZE A CN2379 |

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Fairview Microwave:](#)

[FMCA1690-60](#)