

# CLAMP RG55 RG58 RG141RG142

SC9178

## SPECIFICATIONS

ELECTRICAL:



FREQUENCY: 0-11 GHZ  
VSWR 1.3:1 MAX  
IMPEDANCE: 50 OHMS

MECHANICAL:

MATERIAL BODY: NICKLE PLATED BRASS  
CENTER CONTACT: BRASS  
CONTACT PLATING: Si QQ-S-365  
INSULATOR: TEFLON  
INTERFACE: MIL-STD-348B  
ROHS COMPLIANT  
OP. TEMP RANGE: -55°C- +110°C

ASSEMBLY INSTRUCTIONS:

TRIM CABLE TO OVERALL LENGTH AS SHOWN;  
SLIDE BACKNUT, WASHER, GASKET, CLAMP ON CABLE;  
COMB BRAID WIRES OUT, FOLD BACK, TRIM FLUSH W CLAMP;  
TRIM DIELECTRIC & CENTER PIN AS SHOWN;  
ASSEMBLE REAR BUSHING;  
SOLDER CONTACT ONTO CENTER CONDUCTOR,  
INSERT ASSEMBLY INTO BODY, TIGHTEN NUT



## STRIPPING DIMENIONS

FAIRVIEW MICROWAVE INC.

ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM

TITLE

CLAMP RG55 RG58 RG141RG142

SIZE

CAGE CODE

DWG NO

REV

A

3FKR5

SC9178

--

ALL DIMENSIONS IN inches(MM) Typical

SCALE

SHEET

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Fairview Microwave:](#)

[SC9178](#)