





THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC.. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	DRAWING REPLACES TDS1039-8C-OD1 AT REV C	11/17/14	D. CASTRO



NOTES:

MATERIALS:

HOUSING: ABS UL94V-0, COLOR: IVORY
CONTACTS: PHOSPHOR BRONZE
CONTACT PLATING: 30 μINCHES GOLD OVER NICKEL

ELECTRICAL:

CURRENT RATING: 2.0 AMP MAX
DIELECTRIC WITHSTANDING VOLTAGE: 100Vrms, 60Hz, 1 MINUTE
INSULATION RESISTANCE: 10 MΩ

ENVIRONMENTAL:

OPERATING TEMPERATURE RANGE: 0°C TO +60°C
HUMIDITY: 5 TO 95% NON-CONDENSING

APPLICATION:

RATING: CATEGORY 3
WIRING: STRAIGHT THRU
INSERTION/EXTRACTION LIFE: 1000 CYCLES

MISCELLANEOUS:

DIMENSIONS ARE FOR REFERENCE ONLY.
COMPONENT SHALL BE INDIVIDUALLY PACKAGED IN
ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

REGULATORY COMPLIANCE:

CE2011/65/EU(RoHS DIRECTIVE)

WIRE MAP		
"J1"	"J2"	"J3"
1	1	1
2	2	2
3	3	3
4	4	4
5	5	5
6	6	6
7	7	7
8	8	8

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 [5.08] .XX = ±.02 [51] .XXX = ±.005 [1.27] PROJECTION 	APPROVALS	DATE	 45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845	
	DRAWN BY D. PARHAM	3/8/2001		
	CHECKED BY T. CLARK	3/21/2001	CATEGORY TELECOM/MODULAR	
	APPROVED BY C. McCORMICK	3/27/2001	PRODUCT DESCRIPTION MOD SPLITTER(8X8)F TO 2 (8X8)F	
CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		COLOR VARIATIONS MAY OCCUR	SIZE A	FSCM NO. 43321
			DWG. NO. TDS1039-8C	REV. A
		SCALE: NONE	CAD FILE: TDS1039-8C.SLDDRW	SHEET 1 OF 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[L-Com:](#)

[TDS1039-8C](#)