



[Article Page](#)


Product Description

inductive sensor DC




Name
Order number
Switching distance
Mounting


KJ5-M18MB25-DPS
08310000562
5 mm




Switch type



Signal Type
Connection



Connection diagramm



Dimension (in mm)
Technical Specification
Operating voltage
Max. ripple
Voltage drop
Max. load current
No load current
Leakage current
Switching frequency
Switching hysteresis
Operating temperature
Temperature drift
Repeat accuracy
Switching state
Short-circuit proof
Overload protection
Reverse voltage protection
Protection category
EMC-level
Housing material
Material active face
Cable length

fine-pitch thread M18 x 25

10 - 30 VDC
≤ 10 %
2,4 V
100 mA
≤ 13 mA
≤ 10 µA
800
≤ 15 %
-25 ° C to 70 ° C
≤ 10 %
≤ 10 %
LED
yes
yes
yes
IP67
DIN EN 60947-5-2: 2008
Brass, nickel plated
Schulamid
2 m



KJ5-M18MB25-DPS

Pulsotronic GmbH & Co. KG Neue Schichtstraße 14b 09366 Niederdorf Deutschland +49 (0)37296 930-200

Utilisation category
Cable material
Cable cross

DC 13
PVC grau LIYY
3x0.14 mm²

Errors and omissions excepted

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Altech:](#)

[08310000562](#)