





Name
Order number
Switching distance
Mounting

KJ6,4-Q15KN32-DPS
08310001237
6,4 mm

 non shielded


Switch type

 N.O.
DC PNP

Signal Type
Connection

 Cable

Connection diagramm



Dimension (in mm)
Technical Specification
Special features

Q 15 x 10 x 32

Operating voltage
Max. ripple
Voltage drop
Max. load current
No load current
Leakage current
Switching frequency
Switching hysteresis
Operating temperature
Temperature drift
Repeat accuracy
Switching state
Short-circuit proof
Overload protection
Reverse voltage protection
Protection category
EMC-level
Cable length

Max. tightening torque for mounting screws M3: 0.3 Nm (when used a standard washer)
10 - 30 V DC
 $\leq 10 \%$
1 V
100 mA
 ≤ 10 mA
 ≤ 10 μ A
250
 $\leq 15 \%$
-25 ° C to 70 ° C
 $\leq 10 \%$
 $\leq 3 \%$
LED
yes
yes
yes
IP67
DIN EN 60947-5-2: 2008
2 m



KJ6,4-Q15KN32-DPS

Pulsotronic GmbH & Co. KG Neue Schichtstraße 14b 09366 Niederdorf Deutschland +49 (0)37296 930-200

Utilisation category
Cable material
Cable cross

DC 13
PVC grau LIYY
3x0.14 mm²

Errors and omissions excepted

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Altech:](#)

[08310001237](#)