



[Article Page](#)

Product Description

inductive sensor pressure resistant




Name
Order number
Switching distance
Mounting


Switch type

Signal Type
Connection
Connection diagramm

KJD2-M12EB78-DPS-V2/500/14,9
08310002410
2 mm



N.O.
DC PNP
connector M12



fine-pitch thread M12 x 78

Dimension (in mm)
Technical Specification
Special features

pressure: 500 bar
length pressure resistant area: 14,9 mm
10 - 30 V DC

Operating voltage
Voltage drop
Max. load current
No load current
Leakage current
Switching frequency
Switching hysteresis
Operating temperature
Temperature drift
Repeat accuracy
Short-circuit proof
Overload protection
Reverse voltage protection
Protection category
EMC-level
Housing material
Utilisation category

2,4 V
200 mA
≤ 10 mA
≤ 10 µA
400
≤ 15 %
-25 ° C to 100 ° C
≤ 10 %
≤ 5 %
yes
yes
yes
IP69K
DIN EN 60947-5-2: 2008
Stainless steel V2A
DC 13

Errors and omissions excepted

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Altech:](#)

[08310002410](#)