


5.08mm Pin Spacing – Pluggable PCB Blocks

Pin Spacing: 5.08mm
Orientation: Dual Row
Horizontal Header
Clamp Type: –
Design: Single Mold



PDHxx-5.08

ELECTRICAL

	Current	Voltage	Wire Range
	12A	300V	–
	16A	450V	–


INSTALLATION DATA

Screw Size	–	PCB Hole Size	1.5mm
Torque	–	Stripping Lgth.	–


MATERIAL

Body	Polyamide	Screw	–
Flammability Class	UL94V-0	Terminal	Tin-Plated Brass
Temperature Limit	105°C UL 125°C IEC	Clamp	–
Color	Green		

No. Poles	Cat. #	Length (mm)	Std. Pk.
2	PDH02-5.08	12.2	100
3	PDH03-5.08	17.2	100
4	PDH04-5.08	22.3	50
5	PDH05-5.08	27.4	50
6	PDH06-5.08	32.5	50
7	PDH07-5.08	37.6	50
8	PDH08-5.08	42.6	50
9	PDH09-5.08	47.7	50
10	PDH10-5.08	52.8	50
11	PDH11-5.08	57.9	50
12	PDH12-5.08	63.0	50



Pin Spacing: 5.08mm
Orientation: Vertical Header with
Screw Flange
Clamp Type: –
Design: Single Mold



PVxx-5.08-K

ELECTRICAL

	Current	Voltage	Wire Range
	12A	300V	–
	16A	450V	–


INSTALLATION DATA

Screw Size	–	PCB Hole Size	1.5mm
Torque	–	Stripping Lgth.	–

MATERIAL

Body	Polyamide	Screw	–
Flammability Class	UL94V-0	Terminal	Tin-Plated Brass
Temperature Limit	105°C UL 125°C IEC	Clamp	Nickeled Brass
Color	Green		

No. Poles	Cat. #	Length (mm)	Std. Pk.
2	PV02-5.08 - K	20.3	100
3	PV03-5.08 - K	25.4	100
4	PV04-5.08 - K	30.5	50
5	PV05-5.08 - K	35.6	50
6	PV06-5.08 - K	40.6	50
7	PV07-5.08 - K	45.7	50
8	PV08-5.08 - K	50.8	50
9	PV09-5.08 - K	55.9	50
10	PV10-5.08 - K	61.0	50
11	PV11-5.08 - K	66.0	50
12	PV12-5.08 - K	71.1	50
13	PV13-5.08 - K	76.2	20
14	PV14-5.08 - K	81.3	20
15	PV15-5.08 - K	86.4	20
16	PV16-5.08 - K	91.4	20
17	PV17-5.08 - K	96.5	20
18	PV18-5.08 - K	101.6	20
19	PV19-5.08 - K	106.7	20
20	PV20-5.08 - K	111.8	20
21	PV21-5.08 - K	116.6	20
22	PV22-5.08 - K	121.9	20



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Altech:

[PV02-5,08](#) [PV02-5,08-K](#) [PV03-5,08](#) [PV03-5,08-K](#) [PV04-5,08](#) [PV04-5,08-K](#) [PV05-5,08](#) [PV05-5,08-K](#) [PV06-5,08](#)
[PV06-5,08-K](#) [PV07-5,08](#) [PV07-5,08-K](#) [PV08-5,08](#) [PV08-5,08-K](#) [PV09-5,08](#) [PV09-5,08-K](#) [PV10-5,08](#) [PV10-5,08-K](#)
[PV11-5,08](#) [PV11-5,08-K](#) [PV12-5,08](#) [PV12-5,08-K](#) [PV13-5,08](#) [PV13-5,08-K](#) [PV14-5,08](#) [PV14-5,08-K](#) [PV15-5,08](#)
[PV15-5,08-K](#) [PV16-5,08](#) [PV16-5,08-K](#) [PV17-5,08](#) [PV17-5,08-K](#) [PV18-5,08](#) [PV18-5,08-K](#) [PV19-5,08](#) [PV19-5,08-K](#)
[PV20-5,08](#) [PV20-5,08-K](#) [PV21-5,08](#) [PV21-5,08-K](#) [PV22-5,08](#) [PV22-5,08-K](#) [PV23-5,08](#) [PV24-5,08](#)