

COMPACT HIGH POWER RELAY

1 POLE - 40A (For automotive applications)

FBR53-HW Series

■ FEATURES

- Small 40A relay
- High temperature grade (-40°C to 125°C)
- Contact arrangement Form U (form A)
- Surface mount compatible (reflow capability)
- Inrush current 80A
- Coil wire temperature class: H



■ Part Numbers

[Example]	FBR53	N	D12	-	Υ	-	HW	-	RW	
	(a)	(b)	(c)		(d)		(e)		(f)	

(a)	Relay type	FBR53	: FBR53 series	
(b)	Enclosure	N	: Plastic sealed type	
(c)	Coil rated voltage	D12	: 912VDC Coil rating table at page 3	
(d)	Contact material	Υ	: Silver-tin oxide	
(e)	Contact rating	HW	: 40A	
(f)	Soldering	Nil RW	: Standard (Flow soldering) : Reflow capable (THR)	

Actual markings does not carry the type name: "FBR"

E.g.: Ordering code: FBR53ND12-Y-HW Actual marking: 53ND12-Y-HW

1

■ Specifications

Item			FBR53-HW	Remarks / conditions		
Contact	Configuration		1 form U			
data	Material		Silver-tin oxide			
	Voltage drop		Max. 100 mV at 1A, 12VDC. Average 1.2 m Ω at 7A, 12VDC			
	Contact rating		40A, 14VDC	Resistive load		
	Max. carrying current		40A			
	Max. inrush current		80A	Reference		
	Min. switching load		1A 6VDC	Reference *		
Coil	Rated power consumption		860mW	At 20°C		
	Operate power consumption		310mW	At 20°C		
	Operating temperature range		-40°C ~ +125°C	No frost		
Timing	Operate		Max. 10ms	At nominal voltage		
data	Release		Max. 10ms	At nominal voltage		
Life	Mechanical		Min. 1 x 10 ⁶ operations	without contact load		
	Electrical		Min. 100 x 10 ³ operations	14VDC, 40A resistive load		
Insula-	Insulation resistance		Min. 100MΩ	Initial		
tion	Dielectric withstanding voltage	Open con- tacts	500VAC (50/60Hz), 1 minute			
		Coil contact	500VAC (50/60Hz), 1 minute			
Other	Vibration resistance	Misoperation	10 to 200Hz, acceleration 44m/s²(4.4G) constant acceleration			
		Endurance	10 to 200Hz, acceleration 44m/s²(4.4G) constant acceleration			
	Shock resistance	Misoperation	100m/s² (11±1ms)	Direction X, Y, Z, contact ON/OFF total 36 times		
		Endurance	1,000m/s² (6±1ms)	Direction X, Y, Z, contact OFF total 18 times		
	Dimensions / weight		12.3 x15.7x14.0 mm / approx. 6g			

^{*:} Minimum switching loads mentioned above are reference values. Please perform the confirmation test with actual load before production since reference values may vary according to switching frequencies, environmental conditions and expected reliability levels.

Care shall be taken on the heat generated on PC board when maximum carrying current exceeds 10A. Please perform the confirmation test with actual conditions.

■ Coil Data


Coil code	Rated Coil Voltage (VDC)	Coil Resistance +/-10% (Ω)	Must Operate Voltage* (VDC)	Must Release Voltage* (VDC)
D09	9	94	5.4 7.7 (at 125°C)	0.7 1.0 (at 125°C)
D10	10	117	6.3 9 (at 125°C)	0.8 1.2 (at 125°C)
D12	12	167	7.3 10.4 (at 125°C)	1.0 1.5 (at 125°C)

Note: All values in the table are valid at 20°C and zero contact current, unless otherwise specified.

Please use at rated coil voltage. Please refer to characteristic data and set up adequate voltage in case of use at over voltage.


■ Dimensions

• Dimensions



Dimensions of the terminals do not include thickness of pre-solder.


Schematics (BOTTOM VIEW)



Pattern shall be designed to short-circuit #4 and #5 on the PC board.

^{*:} Specified operated values are valid for pulse wave voltage.


PC Board Mouting Hole Layout (BOTTOM VIEW)





Tolerance of PC board mounting hole layout: ±0.1 unless otherwise specified.


(): Reference value Unit: mm


■ Characteristic Data (Reference)




















GENERAL INFORMATION

1. ROHS Compliance

- All relays produced by Fujitsu Components are compliant with RoHS directive 2011/65/EU including amendments.
- Use of Cadmium in electrical contacts is exempted as per Annex III of the RoHS directive 2001/65/EU.
 Please consider expiry date of exemption. Relays with Cadmium containing contacts are not to be used for new designs.
- All relays are lead-free. Please refer to Lead-Free Status Info for older date codes at: http://www.fujitsu.com/downloads/MICRO/fcai/relays/lead-free-letter.pdf

2. Recommended lead free solder condition

- Lead free solder plating on relay terminals is Sn-3.0Ag-0.5Cu, unless otherwise specified. This material has been verified to be compatible with PbSn assembly process.
- Recommended solder for assembly: Sn-3.0Ag-0.5Cu.

Flow Solder Condition:

Pre-heating: maximum 120°C

within 90 sec.

Soldering: dip within 5 sec. at

255°C ± 5°C solder bath


Relay must be cooled by air immediately

after soldering

Solder by Soldering Iron:

Soldering Iron 30-60W

Temperature: maximum 350-360°C Duration: maximum 3 sec.



Important Notes for Reflow Soldering

- Temperature shall be measured at PC board upper surface.
- Temperature at PC board upper surface may be changed depending on size of PC board, components mounted on the PC board and/or heating method. Please perform the confirmation test with your actual PC boards.
- This reflow solder condition is applicable only for reflow-capable relays. Do not reflow reflow-incapable relays.
- Recommended solder for assembly: Sn-3.0 Ag-0.5 Cu.

We highly recommend that you confirm your actual solder conditions

3. Moisture Sensitivity

Moisture Sensitivity Level standard is not applicable to electromechanical relays, unless otherwise indicated. -RW THR relay will be shipped in moisture barrier bag.

4. Tin Whiskers

• Dipped SnAgCu solder is known as presenting a low risk to tin whisker development. No considerable length whisker was found by our in house test.

Fujitsu Components International Headquarter Offices

JapanFUJITSU COMPONENT LIMITED Shinagawa Seaside Park Tower 19F,

12-4, Higashi-shinagawa 4-chome, Shinagawa-ku,

Tokyo,140-0002, Japan Tel: (81-3) 3450-1682 Fax: (81-3) 3474-2385

Email: fcl-contact@cs.jp.fujitsu.com Web: www.fujitsu.com/jp/fcl/

North and South America

FUJITSU COMPONENTS AMERICA, INC 2290 North First Street, Suite 212 San Jose, CA 95131, USA Tel: (1-408) 745-4900 Fax: (1-408) 745-4970

Email: components@us.fujitsu.com Web: us.fujitsu.com/components

FUJITSU COMPONENTS EUROPE B.V.

Diamantlaan 25 2132 WV Hoofddorp Netherlands Tel: (31-23) 5560910 Fax: (31-23) 5560950

Email: info@fceu.fujitsu.com

Web: www.fujitsu.com/uk/components

Asia Pacific

FUIITSU COMPONENTS ASIA, LTD. 102E Pasir Panjang Road #01-01 Citilink Warehouse Complex

Singapore 118529 Tel: (65) 6375-8560 Fax: (65) 6273-3021 Email: fcal@sq.fujitsu.com

Web: www.fujitsu.com/sg/products/devices/components

FUJITSU ELECTRONIC COMPONENTS (SHANGHAI) CO., LTD.

Unit 4306, InterContinental Center 100 Yu Tong Road, Shanghai 200070,

China

Tel: (86-21) 3253 0998 Fax: (86-21) 3253 0997 Email: fcal@sq.fujitsu.com

Web: www.fujitsu.com/sq/products/devices/components

FUJITSU COMPONENTS HONG KONG CO., LTD Unit 506, Inter-Continental Plaza

No.94 Granville Road, Tsim Sha Tsui, Kowloon,

Hong Kong Tel: (852) 2881-8495

Tex: (852) 2894-9512 Email: fcal@sg.fujitsu.com

Web: www.fujitsu.com/sg/products/devices/components/

Когеа

FUIITSU COMPONENTS KOREA LIMITED Alpha Tower #403, 645 Sampyeong-dong, Bundang-gu, Seongnam-si, Gyeonggi-do,

13524 Korea Tel: (82) 31-708-7108 Fax: (82) 31-709-7108 Email: fcal@sq.fujitsu.com

www.fujitsu.com/sg/products/devices/components/

©2017 Fujitsu Components Europe B.V. All rights reserved. All trademarks or registered trademarks are the property of their respective owners.

The contents, data and information in this datasheet are provided by Fujitsu Component Ltd. as a service only to its user and only for general information purposes.

The use of the contents, data and information provided in this datasheet is at the users' own risk.

Fujitsu has assembled this datasheet with care and will endeavor to keep the contents, data and information correct, accurate, comprehensive, complete and up to date.

Fujitsu Components Europe B.V. and affiliated companies do however not accept any responsibility or liability on their behalf, nor on behalf of its employees, for any loss or damage, direct, indirect or consequential, with respect to this datasheet, its contents, data, and information and related graphics and the correctness, reliability, accuracy, comprehensiveness, usefulness, availability and completeness thereof.

Nor do Fujitsu Components Europe B.V. and affiliated companies accept on their behalf, nor on behalf of its employees, any responsibility or liability for any representation or warrant of any kind, express or implied, including warranties of any kind for merchantability or fitness for particular use, with respect to these datasheets, its contents, data, information and related graphics and the correctness, reliability, accuracy, comprehensiveness, usefulness, availability and completeness thereof. Rev. September 14th, 2017

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

FCL Components:

FBR53ND10-Y-HW