

SIGNAL RELAY


2 POLES - 2A HIGH INSURATION/WIDE GAP

FTR-C1 Series

RoHS Compliant

■ FEATURES

- 2 Poles, 2 form C
- Contact gap: More than 0.6mm
- High surge voltage: 2,500V between open contacts
5,000V between coil & contact
- Complies with Telcordia (former Bellcore) 2nd level surge
- Dielectric strength: 1,500VAC between open contacts
3,000VAC between coil and contact
- Dimensions of large contact gap relay
Height: 9.4mm maximum (THT), 9.7mm maximum (SMT)
Length: 15.2mm maximum
Width: 7.7mm maximum
- Conforms to IEC60950/ EN60950/UL1950/CSA C 22.2 No. 950 working voltage 250V (supplementary)
- High insulation: Clearance: min 2.0mm (coil and contacts)
Creepage: min 2.5mm (coil and contacts)
- Low power consumption 280mW (latching type 140mW)
- RoHS Compliant
- Plastic sealed



■ APPLICATIONS

xDSL modems, digital multi-function printers (signal switching), STB (line switching), car navigation (audio switching)

■ PART NUMBERS

[Example] FTR-C1 G A 4.5 G - B05
(a) (b) (c) (d) (e) (f)

(a)	Relay type	FTR-C1 series
(b)	Contact configuration	C : Through hole type G : Surface mount type S : Surface mount type reduced mounting area
(c)	Coil type	A : Standard type B : Single coil latching type
(d)	Coil rated voltage	4.5 : 3....24VDC Please refer to coil rating table
(e)	Contact material	G : Gold plated silver palladium (stationary contact) Silver palladium (movable contact)
(f)	Tape/reel version	Nil : Tube packing B05 : Tape & reel packing, only available for surface mount type

Actual marking does not carry the type name : "FTR". E.g.: Ordering code: FTR-C1CA012G Actual marking: C1CA012G

■ SPECIFICATIONS

Item			Specifications		Remarks/Conditions	
			Non-latching FTR-C1()A	Latching FTR-C1()B		
Contact Data	Configuration		2c (2 Form C)			
	Construction		Bifurcated			
	Material		Gold plated silver palladium (stationary contact) Silver palladium (movable contact)			
	Resistance (initial)		Max. 150mΩ		At 1A, 6VDC	
	Contact rating		0.3A, 125VAC/1A, 30VDC		Resistive	
	Max. switching voltage		250VAC/220VDC			
	Max. switching power		62.5VA/30W			
	Max. carrying current		2A			
	Min. switching load ^{*1}		0.01mA, 10mVDC		Reference	
Coil	Rated power		280 to 300mW	140 to 180mW		
	Operate power		158 to 162mW	158 to 162mW		
	Pulse width		-	Min. 20ms		
	Operating temperature range		-40°C to +85°C		No frost	
	Storage temperature / humidity		-40°C to +85°C / 5% to 85% RH		No frost	
Time	Operate (at nominal voltage)		Max. 6ms		Without bounce	
	Release (at nominal voltage)		Max. 6ms		Without bounce	
Life	Mechanical		Min. 10 x 10 ⁶ operations			
	Electrical (resistive)		Min. 100 x 10 ³ operations at 0.3A, 125VAC/1A, 30VDC			
Insulation	Insulation resistance		Min. 1,000MΩ		At 500VDC	
	Dielectric strength	Open contacts	1,500VAC (50/60Hz) 1min.			
		Adjacent contacts	1,500VAC (50/60Hz) 1min.			
		Contacts to coil	3,000VAC (50/60Hz) 1min.			
	Surge strength	Contacts to coil	5,000V, 2 x 10μs			
		Clearance	Open contacts	0.6mm		
			Adjacent contacts	1.0mm		
	Contacts to coil		2.0mm			
	Creepage	Open contacts	0.6mm			
		Adjacent contacts	1.0mm			
		Contacts to coil	2.5mm			
Other	Vibration resistance	Misoperation>1μs	10 to 55 to 10Hz single amplitude 1.65mm		Coil ON/OFF, 3 axis, total 6 cycles	
		Endurance	10 to 55 to 10Hz single amplitude 2.5mm		Coil OFF, 3 axis, total 6 hours	
	Shock resistance	Misoperation>1μs	Min. 500m/s ² (11±1ms)		Coil ON/OFF, 3 axis, total 36 operations	
		Endurance	Min. 1,000m/s ² (6±1ms)		Coil OFF, 3 axis, total 18 operations	
	Dimensions / Weight		7.5 x 15.0 x 9.3mm / Approximately 2g			
	Sealing		RT III (plastic sealed)			

*1: Minimum switching loads mentioned above are reference values. Please perform the confirmation test with actual load before production since reference values may vary according to switching frequencies, environmental conditions and expected reliability levels.

■ COIL DATA

● Standard (non-latching) type

Coil Code	Rated Coil Voltage (VDC)	Coil Resistance (Ω) $\pm 10\%$	Must Operate Voltage ^{*1} (VDC)	Must Release Voltage ^{*1} (VDC)	Nominal Coil Power (mW)
003	3	32.1	2.25	0.3	280
4.5	4.5	72.3	3.38	0.45	
005	5	89.3	3.75	0.5	
012	12	514	9.0	1.2	
024	24	1,920	18.0	2.4	300

● Latching type

Coil Code	Rated Coil Voltage (VDC)	Coil Resistance (Ω) $\pm 10\%$	Set Voltage ^{*1} (VDC)	Reset Voltage ^{*1} (VDC)	Nominal Coil Power (mW)
003	3	64	+2.25	-2.25	140
4.5	4.5	145	+3.38	-3.38	
005	5	179	+3.75	-3.75	
012	12	1,029	+9.0	-9.0	
024	24	3,200	+18.0	-18.0	180

Note: All values in the table are valid for 20°C and zero contact current.

* Specified operate values are valid for pulse wave voltage.

Note: Please use at rated coil voltage. Please perform the confirmation test with actual conditions.

■ SAFETY STANDARDS

Type	Compliance	Contact Rating
UL	Flammability: UL 94-V-0 (plastics)	
	UL 508 File No. E63615	0.3A, 125 VAC (general use) (UL) 0.5A, 125VAC (CSA)
CSA	C22.2 No. 14	2A, 30VDC (general use)
	File No. LR 40304	0.3A, 110VDC (general use)


■ PART NUMBER LIST

Part Number	Contact configuration	Coil Type	Contact Material	Tape/Reel version	Note
FTR-C1CA()G	Through hole	Standard	Gold plated silver palladium (stationary contact)	Tube	Tape & reel package is not available
FTR-C1CB()G		Latching			
FTR-C1GA()G	Surface mount	Standard		Tube	-
FTR-C1GA()G-B05				Tape & reel	
FTR-C1GB()G		Latching		Tube	
FTR-C1GB()G-B05				Tape & reel	
FTR-C1SA()G	Surface mount reduced mounting area	Standard	Silver palladium (movable contact)	Tube	-
FTR-C1SA()G-B05				Tape & reel	
FTR-C1SB()G		Latching		Tube	
FTR-C1SB()G-B05				Tape & reel	


■ DIMENSIONS

Through hole type


●Dimensions



●Schematics (BOTTOM VIEW)




●Recommended PCB layout (BOTTOM VIEW)




Surface mount type


●Dimensions



●Schematics (TOP VIEW)




●Recommended PCB layout (TOP VIEW)




Surface mount (space saving) type


●Dimensions



●Schematics (TOP VIEW)



●Recommended PCB layout (TOP VIEW)



Note: (...) : dimensions are reference

Note: Dimensions of the terminals do not include thickness of pre-soldering.

Note: Dimensions do not include tolerances. Please ask specification in case you need tolerances.

Note: Tolerance of PCB layout: ± 0.1 unless otherwise specified.

Unit: mm

■ RECOMMENDED SOLDERING CONDITIONS FOR SURFACE MOUNT TYPE


(Temperature profile, please see page 7)

Notes:


1. Temperature profiles show the temperature of PC board surface
2. Please perform soldering test with your actual PC board before mass production, since the temperatures of PC board surfaces vary according to the size of PC board, status of parts mounting and heating method.

■ TAPE & REEL PACKAGING SPECIFICATION


1. Taping standards: JIS C 0806 and RC-10092B (EIAJ)
2. Tape type: TB2416 or TE2416
3. Reel type: RD24D
4. Quantity of 1 reel: 500 pieces



Tape Dimensions:



Reel Dimensions:




Unit: mm


■ CHARACTERISTIC DATA

(Characteristic data is not guaranteed value but measured values of samples from production line.)


Distribution of operate/release voltage




Distribution of operate time




Distribution of release time




Set/reset time characteristics




Pulse characteristics




Distribution of contact resistance (Make contacts)




Distribution of contact resistance (Break contacts)




Maximum switching power




Life curve




Operating range



Operating range



Coil temperature rise



CAUTIONS

- All values mentioned in this datasheet are provided under ideal conditions. Please perform the confirmation test before actual use.
- Reflow soldering is not available with standard type.
- Do not use relays in the atmosphere with sulfide gas, chloride gas or nitric oxide. Contact resistance may increase.
- Do not use silicon or silicon-containing product or materials near relays. It may cause contact failure.

Notes for latching relays

- Latching relays are shipped in the state reset, but state may change due to shock during transportation or mounting.
Before using the relays, it is advisable to bring the relays in necessary state (set or reset) and program a circuit sequence.
Otherwise, it will or will not operate simultaneously with power activation.
- Please connect relay coils according to specified polarity.
- Do not apply voltage to both set coil and reset coil at a time.

GENERAL INFORMATION

1. RoHS Compliance

- All relays produced by FCL Components are compliant with RoHS directive 2011/65/EU, including commission delegated directive 2015/863.

2. Recommended lead free solder condition

Flow Solder Condition:

Pre-Heating: Maximum 120°C within 90 sec.
Soldering: Dip within 5 sec. at 255°C±5°C solder bath

Relay must be cooled by air immediately after soldering


Solder by Soldering Iron:

Soldering Iron: 30-60W
Temperature: Maximum 350-360°C
Duration: Maximum 3 sec.

Reflow Solder Condition:

(Applicable only for reflow capable type)

Recommended reflow soldering profile: IRS (infrared reflow soldering)



Important notes for reflow soldering

- Temperature shall be measured at PC board upper surface.
- Temperature at PC board upper surface may be changed depending on size of PC board, components mounted on the PC board and/or heating method. Please perform the confirmation test with actual PC board.
- This reflow condition is applicable only for reflow-capable relays. Do not reflow reflow-incapable relays.
- Recommended solder for assembly: Sn-3.0 Ag -0.5 Cu.

We highly recommend that you confirm your actual solder conditions

3. Moisture Sensitivity

- SMT versions of FTR-C1 relays in Tape & Reel package will be shipped in Moisture Barrier Bag (MBB).
- Moisture Sensitivity Level (MSL) of FTR-C1 relay is indicated on the packing caution label.
- Relays must be stored in the unopened MBB at storage conditions <40°C/90% RH for a maximum 1 year.
- SMT versions of FTR-C1 relays in tube packing will not be shipped in MBB. Therefore, these relays shall be dried by baking before reflow soldering process according to IPC/Jedex J-STD-033.

4. Tin Whiskers

- Dipped SnAgCu solder is known as presenting a low risk to tin whisker development. No considerable length whisker was found by our in house test.

Contact

Japan

FCL COMPONENTS LIMITED
Shinagawa Seaside Park Tower
12-4, Higashi-shinagawa 4-chome,
Tokyo 140 0002, Japan
Tel: +81-3-3450-1682
Email: fcl-contact@cs.fcl-components.com

North and South America

FCL COMPONENTS AMERICA, INC.
2055 Gateway Place Suite 480,
San Jose, CA 95110 USA
Tel: +1-408-745-4900
Email: contact@fcl-components.us

Europe

FCL COMPONENTS EUROPE B.V.
Diamantlaan 25
2132 WV Hoofddorp, Netherlands
Tel: +31-23-556-0910
Email: info@fcl-components.eu

Asia Pacific

FCL COMPONENTS ASIA PTE LTD.
No. 20 Harbour Drive, #07-01B
Singapore 117612
Tel: +65-6375-8560
Email: fcal@fcl-components.com

China

FCL COMPONENTS (SHANGHAI) CO.,LTD.
Unit 1105, Central Park - Jing An,
No.329 Heng Feng Road, Shanghai
200070, China
Tel: +86-21-3253 0998
Email: fcsh@fcl-components.com

Hong Kong

FCL COMPONENTS HONG KONG CO.,
LIMITED
Unit 2313, Seapower Tower, Concordia
Plaza, No.1 Science Museum Road,
TST, Kowloon, Hong Kong
Tel: +852-2881-8495
Email: fcal@fcl-components.com

Web: www.fcl-components.com/en/

© 2025 FCL Components Limited. All rights reserved. All trademarks or registered trademarks are the property of their respective owners.

FCL Components Products are intended for general use, including without limitation, in personal, household and office environments, in buildings and for ordinary use in the industry. FCL Components Products are not intended to be used in applications where extremely high safety is required ("High Safety Required Applications"), such as, but not limited to, applications in nuclear facilities, in aircraft automatic flight control, in air traffic control, in mass transit system control, in missile launch system, in weapon systems, in medical equipment for life support or any application involving a direct serious risk of physical injury or death.

Please do not use FCL Components Products without securing the sufficient safety and reliability required for the High Safety Required Applications.

In addition, FCL Components shall not be liable against the customer and/or any third party for any claims or damages arising in connection with the use of FCL Components Products in the High Safety Required Applications.

FCL Components warrants that its Products, if properly used and services, will conform to their specification and will be free from defects in material and workmanship for twelve months from delivery.

The implied warranties of merchantability and fitness for a particular purpose and all other warranties, representations and conditions, express or implied by statute, trade usage or otherwise, except as set forth in this warranty, are excluded and shall not apply to the Products delivered.

The contents, data and information in this datasheet are provided by FCL Components Limited as a service only to its user and only for general information purposes. The use of the contents, data and information provided in this datasheet is at the users' own risk.

FCL Components has assembled this datasheet with care and will endeavor to keep the contents, data and information correct, accurate, comprehensive, complete and up to date.

FCL Components Limited and affiliated companies do however not accept any responsibility or liability on their behalf, nor on behalf of its employees, for any loss or damage, direct, indirect or consequential, with respect to this datasheet, its contents, data, and information and related graphics and the correctness, reliability, accuracy, comprehensiveness, usefulness, availability and completeness thereof. Nor do FCL Components Limited and affiliated companies accept on their behalf, nor on behalf of its employees, any responsibility or liability with respect to these datasheets, its contents, data, information and related graphics and the correctness, reliability, accuracy, comprehensiveness, usefulness, availability and completeness thereof. Rev. January 7, 2025.