

SMA Male to SMA Male Low Loss Cable Using TCOM-195 Coax With Times Microwave Components




PE3C10377

Configuration

- Connector 1: SMA Male
- Connector 2: SMA Male
- Cable Type: TCOM-195
- Coax Flex Type: Flexible

Features

- Max Frequency 8 GHz
- 80% Phase Velocity
- Triple Shielded
- PE Jacket



Applications

- General Purpose
- Laboratory Use

Description

Pasternack's PE3C10377 SMA male to SMA male cable using TCOM-195 coax is part of our full line of RF components available for same-day shipping. Pasternack's flexible RF cable assemblies are ideal for applications where tight bends and flexure are required. This Pasternack SMA to SMA cable assembly has a male to male gender configuration with 50 ohm flexible TCOM-195 coax. The PE3C10377 SMA male to SMA male cable assembly operates to 8 GHz. The triple shielding of this Pasternack cable assembly provides excellent shielding effectiveness.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		8	GHz
VSWR			1.4:1	
Velocity of Propagation		80		%
Group Delay		1.27 [4.17]		ns/ft [ns/m]
Capacitance		25.4 [83.33]		pF/ft [pF/m]
Inductance		0.064 [0.21]		uH/ft [uH/m]
DC Resistance Inner Conductor		7.16 [23.49]		Ohms/1000ft [Ohms/Km]
DC Resistance Outer Conductor		3.42 [11.22]		Ohms/1000ft [Ohms/Km]
Jacket Spark			3,000	Vrms

Specifications by Frequency

SMA Male to SMA Male Low Loss Cable Using TCOM-195 Coax With Times Microwave Components



PE3C10377

Part Number	Length	Description	F1	F2	F3	F4	F5	Units	Weight (lbs)
		Frequency	500	1000	2000	4000	8000	MHz	
PE3C10377	Custom Lengths Available	Insertion Loss (Typ.)	0.073	0.106	0.153	0.217	0.32	dB/ft	
			0.24	0.35	0.51	0.72	1.05	dB/m	
PE3C10377-12	12 inch	Insertion Loss (Typ.)	0.28	0.31	0.36	0.42	0.52	dB	0.073
PE3C10377-24	24 inch	Insertion Loss (Typ.)	0.35	0.42	0.51	0.64	0.84	dB	0.108
PE3C10377-36	36 inch	Insertion Loss (Typ.)	0.42	0.52	0.66	0.86	1.16	dB	0.143
PE3C10377-48	48 inch	Insertion Loss (Typ.)	0.5	0.63	0.82	1.07	1.48	dB	0.178
PE3C10377-60	60 inch	Insertion Loss (Typ.)	0.57	0.73	0.97	1.29	1.8	dB	0.213

The insertion loss data for the base model does not include loss due to the connectors. Each length includes insertion loss due to the connectors.

Loss due to Connector 1:	0.1 dB
Loss due to Connector 2:	0.1 dB
Base Weight:	0.073 pounds
Additional Weight per Inch:	0.00291 pounds

Mechanical Specifications

Cable Assembly

Width/Diameter	0.5 in [12.7 mm]
Weight	0.073 lbs [33.11 g]

Cable

Cable Type	TCOM-195
Impedance	50 Ohms
Inner Conductor Type	Solid
Inner Conductor Material and Plating	Copper
Dielectric Type	PE (F)
Number of Shields	3
Shield Layer 1	Silver Plated Copper Braid
Shield Layer 2	Tinned Copper Braid
Jacket Material	PE, Black
Jacket Diameter	0.195 in [4.95 mm]
One Time Minimum Bend Radius	0.5 in [12.7 mm]
Repeated Minimum Bend Radius	2 in [50.8 mm]
Bending Moment	0.2 lbs-ft [0.27 N-m]
Flat Plate Crush	15 lbs/in [0.27 Kg/mm]

SMA Male to SMA Male Low Loss Cable Using TCOM-195 Coax With Times Microwave Components



PE3C10377

Connectors

Description	Connector 1	Connector 2
Type	SMA Male	SMA Male
Impedance	50 Ohms	50 Ohms
Configuration	Straight	Straight
Contact Material and Plating	Brass, Gold	Brass, Gold
Contact Plating Specification	ASTM B488	ASTM B488
Dielectric Type	Teflon	Teflon
Body Material and Plating	Passivated Stainless Steel	Passivated Stainless Steel
Coupling Nut Material and Plating	Passivated Stainless Steel	Passivated Stainless Steel
Hex Size	5/16 Inch	5/16 Inch

Environmental Specifications

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

SMA Male to SMA Male Low Loss Cable Using TCOM-195 Coax With Times Microwave Components



PE3C10377

Typical Performance Data

How to Order

Part Number Configuration:

PE3C10377

- xx

uu

Unit of Measure:
cm = Centimeters
<blank> = Inches

Length
Base Number

Example: PE3C10377-12 = 12 inches long cable
PE3C10377-100cm = 100 cm long cable


SMA Male to SMA Male Low Loss Cable Using TCOM-195 Coax With Times Microwave Components from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SMA Male to SMA Male Low Loss Cable Using TCOM-195 Coax With Times Microwave Components PE3C10377](#)

URL: <https://www.pasternack.com/sma-male-to-sma-male-low-loss-cable-using-tcom-195-pe3c10377-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Pasternack Enterprises reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack Enterprises does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack Enterprises does not assume liability arising out of the use of any part or document.

PE3C10377 CAD Drawing
SMA Male to SMA Male Low Loss Cable Using TCOM-195 Coax With Times Microwave Components



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Pasternack:](#)

[PE3C10377-48](#)