


RF PCB Connector, SMB Plug right angle, DIP (Thru Hole), Gold Plating



RFPCB-SMB-M-R-4G-18

Configuration

- SMB Male Connector
- 50 Ohms
- Right Angle Body Geometry

Features

- Max Frequency 4 GHz
- Cu Ni Au plating

Applications

- PCB Applications
- General Purpose Test

Description

RFPCB-SMB-M-R-4G-18 SMB plug PCB connector available from L-com has a 50 Ohm impedance. This RF connector is designed for a wide variety of Printed-Circuit Board (PCB) applications in RF and microwave systems. The SMB connector is available in a 0.60-inch length, 0.44-inch width, and 0.25-inch height.

The L-com SMB plug PCB connector has a PTFE dielectric type. This SMB PCB connector has a beryllium copper body with gold over nickel over copper plating. Our RFPCB-SMB-M-R-4G-18 SMB connector uses beryllium copper contact and gold over nickel over copper plating material. The SMB plug connector uses solder as an attachment method. Additional dimensions and specifications for this SMB plug PCB RF connector are on our downloadable PDF datasheet above.

This L-com SMB plug connector will ship the same day as purchased. Our SMB plug connector is part of over 40,000 RF, microwave, and millimeter wave components in stock for worldwide shipment. We also build SMB custom connector cable assemblies that will ship the same day as well.

This SMB plug connector with 50 Ohm impedance has a weight of 0.02 lbs. The RFPCB-SMB-M-R-4G-18 threaded RF connector has a right angle body style and a high-quality construction. We currently have a variety of antenna, audio/video, Ethernet, fiber optic, and USB connectors in our portfolio that are ready to ship today. For further information on similar products, our expert technical support and knowledgeable sales team can help you get the high-quality RF product that meets your requirements.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		4	GHz


Mechanical Specifications

Size

Length	0.60 in [15.24 mm]
Width	0.44 in [11.18 mm]
Height	0.25 in [6.35 mm]
Weight	0.02 lbs [9.07 g]

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications:
[RF PCB Connector, SMB Plug right angle, DIP \(Thru Hole\), Gold Plating RFPCB-SMB-M-R-4G-18](#)

RF PCB Connector, SMB Plug right angle, DIP (Thru Hole), Gold Plating



RFPCB-SMB-M-R-4G-18

Material Specifications

Description	Material	Plating
Contact	Beryllium Copper	Gold
Insulation	PTFE	
Body	Beryllium Copper	Gold

Environmental Specifications

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

RF PCB Connector, SMB Plug right angle, DIP (Thru Hole), Gold Plating from L-com has same day shipment for domestic and International orders. Our portfolio includes coaxial cable assemblies, connectors, adapters and custom products as well as lightning and surge protectors, NEMA rated enclosures, and an RF product line which includes antennas, amplifiers, passive, and active components. Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: RF PCB Connector, SMB Plug right angle, DIP (Thru Hole), Gold Plating RFPCB-SMB-M-R-4G-18

URL: <https://www.l-com.com/rf-pcb-connector-smb-plug-right-angle-dip-thru-hole-gold-plating-rfpcb-smb-m-r-4g-18-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document. The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[infinite Electronics:](#)

[RFPCB-MCX-F-S-6G-30](#)