



cablequick® FDA Type 149 (149x339 mm)




Product information


Efficient connection technology for terminal boxes, control cabinets for tool-free introduction of actuators, sensors, measuring and control instrumentation, optoelectronic, pneumatic lines and drive technology into a control panel. KDPs of product group 149 can be fitted directly into the standard cut-outs of Rittal cabinets. The FDA stainless steel version is particularly suitable for use in the food and pharmaceutical sectors. Integrated threaded bolts mean that no screws are visible from outside. Mounting set included in delivery.

- V4A : 1.4571
- FDA compliant
- Rittal cut-out 4

Information, conformities and approvals




Article	Order No.	Color	No. of openings	Openings Quantity x Ø mm	PU pcs.
FDA cablequick® KDP 149/158, 87663951 V4A		Grinded	158	126x 3.5 mm – 6.5 mm 24x 6 mm – 10 mm 6x 8 mm – 12 mm 2x 12 mm – 18 mm	1
FDA cablequick® KDP 149/56, 87663960 V4A		Grinded	56	36x 6 mm – 10 mm 8x 9 mm – 14 mm 8x 14 mm – 18 mm 4x 18 mm – 25 mm	1



Article	Order No.	A mm	B mm	a mm	b mm	c mm	d mm	e mm
FDA cablequick® KDP 87663960 149/56, V4A		339	149	303	115	120	66.5	4.5

Material properties





## cablequick® FDA Type 149 (149x339 mm)

### Thermal properties



Temperature / temperature range

-30 °C – 90 °C

### Protection class



Protection class

IP65

### Conformity



RoHS (EC Directive 2011/65/EU)

### Approvals and operating permits



FDA compliance

### Classification

ETIM 9: EC002624

ECLASS 14: 27182815

### General information



Made in Switzerland

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Murrplastik:](#)

[87663951](#)