

## DATASHEET

# CAR1612FP series rectifier

**Input: 85V<sub>AC</sub> to 264V<sub>AC</sub>; Output: 12V<sub>DC</sub> @ 1600W; 3.3V<sub>DC</sub> @ 1A**



### Description

The CAR1612FP series of Front-End rectifiers provide highly efficient isolated power from worldwide input mains in a compact 1U industry standard form factor in an unprecedented power density of 19W/in<sup>3</sup>. These rectifiers are ideal for datacom applications such as enterprise networking, mid to high-end servers, and storage equipment, where mid to light load efficiency is of key importance given the nature of the power consumption of the end application.

The high-density, front-to-back airflow is designed for minimal space utilization and is highly expandable for future growth. The industry standard PMBus compliant I<sup>2</sup>C communications buss offers a full range of control and monitoring capabilities. The SMBAlert signal pin alerts customers automatically of any state change within the power supply.

### Applications

- 12V<sub>DC</sub> distributed power architectures
- Datacom applications
- Mid to high-end Servers
- Enterprise Networking
- Network Attached Storage
- Telecom Access Nodes
- Routers/Switches
- Broadband Switches
- ATE Equipment

## Features

- Universal input with PFC
- Constant power characteristic
- 2 front panel LEDs: 1-input  
LED 2-[output, fault, over temp]
- Remote ON/OFF control of the 12V<sub>DC</sub> output
- Remote sense on the 12V<sub>DC</sub> output
- No minimum load requirements
- Redundant parallel operation
- Active load sharing (single wire)
- Hot Pluggable
- Efficiency: typically 94.5% @ 50% load
- Standby orderable either as 3.3V<sub>dc</sub> or 5V<sub>dc</sub>
- Auto recoverable OC & OT protection
- Digital status & control: I<sup>2</sup>C and PMBus serial bus
- UL and cUL approved to UL/CSA†62368-1, TUV (EN62368-1), CE<sup>s</sup> Mark
- EMI: class B FCC docket 20780 part 15, EN55032
- Meets EN6100 immunity and transient standards
- Shock & vibration: NEBS GR-63-CORE, level 3
- Compliant to RoHS Directive 2011/65/EU and amended Directive (EU) 2015/863
- Compliant to REACH Directive (EC) No 1907/2006

## Technical Specifications

### Absolute Maximum Ratings

Stresses in excess of the absolute maximum ratings can cause permanent damage to the device. These are absolute stress ratings only, functional operation of the device is not implied at these or any other conditions in excess of those given in the operations sections of the data sheet. Exposure to absolute maximum ratings for extended periods can adversely affect the device reliability.

Exposure to absolute maximum ratings for extended periods can adversely affect the device reliability.

Parameter	Device	Symbol	Min	Max	Unit
Input Voltage :Continues	All	$V_{IN}$	0	264	$V_{ac}$
Operating Ambient Temperature	All	$T_A$	-10	60 <sup>1</sup>	°C
Storage Temperature	All	$T_{stg}$	-40	85	°C
I/O Isolation voltage to Frame (100% factory Hi-Pot tested)	All			1500	$V_{ac}$

### Electrical Specifications

Unless otherwise indicated, specifications apply over all operating input voltage, load, and temperature conditions.

INPUT						
Parameter	Device	Symbol	Min	Typ	Max	Unit
Operational Range	All	$V_{IN}$	85	110/230	264	$V_{AC}$
Frequency Range (ETSI 300-132-1 recommendation)	All	$F_{IN}$	47	50/60	63	Hz
Main Output Turn_OFF	All	$V_{IN}$			80	$V_{AC}$
Maximum Input Current ( $V_O = V_{O, set}$ , $I_O = I_{O, max}$ )	All	$I_{IN}$			14.3 10.5	$A_{AC}$
Cold Start Inrush Current (Excluding x-caps, 25°C, <10 ms, per ETSI 300-132)	All	$I_{IN}$			40	$A_{peak}$
Efficiency ( $T_{AMB} = 25^\circ C$ , $V_{OUT} = 12V_{DC}$ , $I_O = I_{O, max}$ )	All	$\eta$		92.5/89 94.5/91 92.4/88		%
Power Factor ( $V_{IN} = 230V_{AC}$ , $I_O = I_{O, max}$ )	All	PF		0.99		
Holdup time <sup>2</sup> ( $V_{OUT} = 12V_{DC}$ , $T_{amb} = 25^\circ C$ , $I_{OUT} = I_{O, max}$ )	All	T		12 15		ms
Early warning prior to loss of DC output below regulation	All		2			ms
Ride through	All	T		10		ms
Leakage Current ( $V_{in} = 250V_{AC}$ , $F_{in} = 60Hz$ )	All	$I_{IN}$		3		$mA_{rms}$
Isolation	All		3000			$V_{AC}$
			1500			$V_{AC}$
			100			$V_{DC}$

12VDC MAIN OUTPUT						
Parameter	Device	Symbol	Min	Typ	Max	Unit
Output Power						
High Line Operation	All	W	0	-	1600	W
Low Line Operation	All	W	0	-	1200	W
Set point	All	$V_{OUT}$	11.9	12.00	12.1	$V_{DC}$
Overall regulation (load, temperature, aging)	All		-3		+3	%
Ripple and noise <sup>3</sup>	All				120	$mV_{p-p}$
Turn-ON overshoot	All				+3	%
Turn-ON delay	All	T			2	sec

See footnotes on page no. 7

Page 3

## Technical Specifications (continued)

### Electrical Specifications (continued)

12V <sub>DC</sub> MAIN OUTPUT (continued)							
Parameter	Device	Symbol	Min	Typ	Max	Unit	
Remote ON/OFF delay time	All				40	ms	
Turn-ON rise time (10 – 90% of V <sub>OUT</sub> )					50	ms	
Transient response 50% step [10%-60%, 50% - 100%] (di/dt – 1A/μs, recovery 300μs)			V <sub>OUT</sub>	-5		+5	%V <sub>OUT</sub>
Programmable range (hardware <sup>4</sup> & software)				10.8		13.2	V <sub>DC</sub>
Overvoltage protection, latched (recovery by cycling OFF/ON via hardware or software)				13.8	14.8	15.8	V <sub>DC</sub>
Output current			I <sub>OUT</sub>	0		134	A <sub>DC</sub>
		V <sub>in</sub> – HL V <sub>in</sub> – LL			100		
Current limit, Hiccup (programmable level)				110		130	% of FL
Active current share				-5		+5	% of FL

AUXILIARY OUTPUT						
Parameter	Device	Symbol	Min	Typ	Max	Unit
Set point	All	V <sub>OUT</sub>		3.3/5.0		V <sub>DC</sub>
Overall regulation (load, temperature, aging)	All		-5		+5	%
Ripple and noise	All				50	mV <sub>p-p</sub>
Output current		I <sub>OUT</sub>	0		1	A <sub>DC</sub>
Overload protection -			1.1		2.6	A <sub>DC</sub>
Overvoltage protection						
Isolation Output/Frame	All		100			V <sub>DC</sub>

Environmental, Reliability						
Parameter	Min	Typ	Max	Units	Notes	
Ambient Temperature			70 <sup>6</sup>	°C	Air inlet from sea level to 5,000 feet. 7400 ft 51°C to 70°C (60°C max where TUV/VDE is required)	
Operating						
Altitude Operating	-10 <sup>5</sup>		2250	m		
Power Derating			2.5	%/°C		
Storage			85	°C		
Altitude non-operating	-40		8200	m	30,000 ft	
Overload Protection shutdown		125				
restart		110		°C		
Humidity					Relative humidity, non-condensing	
Operating	30		95	%		
Storage	10		95			
Shock and Vibration acceleration			6	Grms	NEBS GR-63-CORE, Level 3, 20 -2000Hz, minimum 30 minutes	
Earthquake Rating	4			Zone	NEBS GR-63-CORE, all floors, Seismic Zone 4 Designed and tested to meet NEBS specifications.	
Reliability	25°C	320,000		Hrs	Full load, MTBF per Bellcore RPP	
	50°C	100,000		Hrs	Full load, MTBF per Bellcore RPP	
		200,000		Hrs	Full load, demonstrated MTBF	

See footnotes on page no. 7

## Technical Specifications (continued)

### Electrical Specifications (continued)

EMC				
Parameter	Criteria	Standard	Level	Test
AC input	Conducted emissions	EN55032, FCC Docket 20780 part 15, subpart J EN61000-3-2	A*	0.15 – 30MHz 0 – 2 KHz
	Radiated emissions**	EN55032	A*	30 – 10000MHz
	Voltage dips	EN61000-4-11	B	-30%, 10ms
			B	-60%, 100ms
			B	-100%, 5sec
	Voltage surge	EN61000-4-5	A	4kV, 1.2/50µs, common mode
A			2kV, 1.2/50µs, differential mode	
Immunity	Fast transients	EN61000-4-4	B	5/50ns, 2kV (common mode)
Enclosure immunity	Conducted RF fields	EN61000-4-6	A	130dBµV, 0.15-80MHz, 80%AM
	Radiated RF fields	EN61000-4-3	A	10V/m, 80-1000MHz, 80% AM
		ENV 50140	A	
	ESD	EN61000-4-2	B	4kV contact, 8kV air

\* Note: Contact the factory for a recommended external EMI filter to meet Class B emissions

\*\* Radiated emissions compliance is contingent upon the final system configuration.

### Status and Control

Details of analog controls are provided in this data sheet under Signal Definitions. OmniOn Energy will provide separate application notes on the I<sup>2</sup>C protocol. Contact your local OmniOn Energy representative for details.

### Signal Definitions

All signals and outputs are referenced to Output return. These include 'Vstb return' and 'Signal return'.

### Input Signals

Voltage programming (V<sub>prog</sub>): An analog voltage on this signal can vary the output voltage ± 10% from 10.8V<sub>dc</sub> to 13.2V<sub>dc</sub>. The equation of this signal is:

$$V_{out} = 10.8 + (V_{prog} * 0.96) \quad 0 < V_{prog} < 2.5$$

If  $2.5 < V_{prog} < 3$ , the output is 13.2V. If  $V_{prog} > 3V$  or left open the programming signal is ignored and the unit output is set at the setpoint of 12V<sub>dc</sub>.

**Load share (Ishare):** This is a single wire analog signal that is generated and acted upon automatically by power supplies connected in parallel. The Ishare pins should be tied together for power supplies if active current share among the power supplies is desired. No resistors or capacitors should get connected to this pin.

**Remote ON/OFF:** Controls the presence of the main 12V<sub>dc</sub> output voltage. This is an open collector, TTL level control signal. This signal needs to be pulled HI externally through a resistor. Maximum collector voltage is 12V<sub>dc</sub> and the maximum sink current is 4mA. A Logic 1 (TTL HI level) turns ON the 12V<sub>dc</sub> output, while a Logic 0 (TTL LO level) turns OFF the 12V<sub>dc</sub> output.

A turn OFF command either through this signal (Remote ON/OFF) or firmware commanded would turn OFF the 12V output.

**Enable:** This is a short signal pin that controls the presence of the 12V<sub>dc</sub> main output. This pin should be connected to 'output return' on the system side of the output connector. The purpose of this pin is to ensure that the output turns ON after engagement of the power blades and turns OFF prior to disengagement of the power blades.

**Write protect (WP):** This signal protects the contents of the EEPROM from accidental over writing. When left open the EEPROM is write protected. A LO (TTL compatible) permits writing to the EEPROM. This signal is pulled HI internally by the power supply.

## Technical Specifications (continued)

### Output signals

**Output current monitor (I<sub>mon</sub>):** A voltage level proportional to the delivered output current is present on this pin. 134A = 3V, 100A = 2.25V; accuracy: ± 10%.

**AC OK:** A TTL compatible status signal representing whether the input voltage is within the anticipated range. This signal needs to be pulled HI externally through a resistor. Maximum sink current ≤ 4mA and the max voltage is 12V<sub>dc</sub>. Open collector (HI) on this signal indicates that the input voltage is applied within the specified input range.

**DC OK:** A TTL compatible status signal representing whether the output voltage is present. This signal needs to be pulled HI externally through a resistor. Maximum sink current ≤ 4mA and the max voltage is 12V<sub>dc</sub>. Open collector (HI) on this signal indicates that the output voltage is present.

**Over temp warning:** A TTL compatible status signal representing whether an over temperature exists. This signal needs to be pulled HI externally through a resistor. Maximum sink current ≤ 4mA and the max voltage is 12V<sub>dc</sub>. Open collector (HI) on this signal indicates that temperatures are normal.

If an over temperature should occur, this signal would pull LO for approximately 10 seconds prior to shutting down the power supply. The unit would restart if internal temperatures recover within normal operational levels. At that time the signal reverts back to its open collector (HI) state.

**Fault:** A TTL compatible status signal representing whether a Fault occurred. This signal needs to be pulled HI externally through a resistor. Maximum sink current ≤ 4mA and the max voltage is 12V<sub>dc</sub>. Open collector (HI) on this signal indicates that no Fault is present.

This signal activates for OTP, OVP, OCP, AC fault or No output.

**PS Present:** This pin is connected to 'output return' within the power supply. Its intent is to indicate to the system that a power supply is present. This signal may need to be pulled HI externally through a resistor.

**Interrupt (SMBAlert):** A TTL compatible status signal, representing the SMBusAlert# feature of the PMBus compatible I<sup>2</sup>C protocol in the power supply. This signal needs to be pulled HI externally through a resistor.

Maximum sink current ≤ 4mA and the pull up resistor should be tied to 3.3V<sub>dc</sub>. Open collector (HI) on this signal indicates that no Interrupt has been triggered.

### Serial Bus Communications

The I<sup>2</sup>C interface facilitates the monitoring and control of various operating parameters within the unit and transmits these on demand over an industry standard I<sup>2</sup>C Serial bus.

All signals are referenced to 'Signal Return'.

**Device addressing:** The microcontroller (MCU) and the EEPROM have the following addresses:

Device	Address	Address Bit Assignments (Most to Least Significant)							
		1	0	1	1	A2	A1	A0	R/W
MCU	0xBx	1	0	1	1	A2	A1	A0	R/W
EEPROM	0xAx	1	0	1	0	A2	A1	A0	R/W

**Address lines (A2, A1, A0):** These signal pins allow up to eight (8) modules to be addressed on a single I<sup>2</sup>C bus. The pins are pulled HI internal to the power supply. For a logic LO these pins should be connected to 'Output Return'

**Serial Clock (SCL):** The clock pulses on this line are generated by the host that initiates communications across the I<sup>2</sup>C Serial bus. This signal is pulled up internally to 3.3V by a 10kΩ resistor. The end user should add additional pull up resistance as necessary to ensure that rise and fall time timing and the maximum sink current is in compliance to the I<sup>2</sup>C specifications.

**Serial Data (SDA):** This line is a bi-directional data line. This signal is pulled up internally to 3.3V by a 10kΩ resistor. The end user should add additional pull up resistance as necessary to ensure that rise and fall time timing and the maximum sink current is in compliance to the I<sup>2</sup>C specifications.

### EEPROM

The microcontroller has 96 bytes of EEPROM memory available for the system host.

Another separate EEPROM IC will provide another 128 bytes of memory with write protect feature. Minimum information to be included in this separate EEPROM: model number, revision, date code, serial number etc.

See the communications protocol for further information.

## Technical Specifications (continued)

### Serial Bus Communications (continued)

#### Communications Protocol

The I<sup>2</sup>C protocol is described in detail by the I<sup>2</sup>C and PMBus Serial Communications Protocol for the CAR Family of Power Supplies application note.

#### LEDs

Two LEDs are located on the front faceplate. The AC\_OK LED provides visual indication of the INPUT signal function. When the LED is ON GREEN the power supply input is within normal design limits.

The second LED DC/FLT provides visual indication of three different states of the power supply. When the LED is GREEN then there are no faults and the DC output is present. When the LED is AMBER then a fault condition exists but the power supply still provides output power. When the LED is RED then a fault condition exists and the power supply does not provide output power.

#### FOOTNOTES

<sup>1</sup> Derated above 50°C at 2.5%/°C

<sup>2</sup> 12V output can decay down to 10.8V

<sup>3</sup> Measured across a 10µf tantalum and a 0.1µf ceramic capacitors in parallel. 20MHz bandwidth

<sup>4</sup>  $V_{out} = 10.8 + (V_{prog} * 0.96)$  where  $0 < V_{prog} < 2.5$ . Unit stays at 13.2V when  $2.5 < V_{prog} < 3$ . Unit stays at 12V when  $V_{prog} > 3V$  or no-connect.

<sup>5</sup> Designed to start at an ambient down to -40°C; meet spec after 30 min warm up period, may not meet operational limits below -10°C.

<sup>6</sup> 60°C max where TUV/VDE is required


# Technical Specifications (continued)

## Alarm Table

Test Condition	LED Indicator		Monitoring Signals			
	LED1 AC	Tri-Color LED2 DC / FLT	FAULT	DC OK	INPUT OK	TEMP OK
1 Normal Operation	Green	Green	High	High	High	High
2 Low or NO INPUT	Off	Red	Low	Low	Low	High
3 OVP	Green	Red	Low	Low	High	High
4 Over Current	Green	Red	Low	Low	High	High
5 Temp Alarm Warning	Green	Orange	High	High	High	Low
6 Fault Over Temp	Green	Red	Low	Low	High	Low
7 Remote ON/OFF	Green	Red	Low	Low	High	High

Note: Test condition #2 had 2 modules plug in. One module is running and the other one is with no AC.

## Outline Drawing






## Technical Specifications (continued)

### Connector Pin Assignments

**Input Mating Connector:** IEC320, C19 type

**Output Connector:** FCI Berg P/N: 51732-021 or equivalent  
Mating connector: 51762-10802400ABLF (right angle mount)



Pin	Function	Pin	Function	Pin	Function	Pin	Function	
A1	Vstb [3.3V]	B1	Fault	C1	ISHARE	D1	VProg	
A2	Vstb [3.3V] Return	B2	I Monitor (IMON)	C2	N/C	D2	OVP Test Point	
A3	Signal Return	B3	Enable: "0" -ON "1" -OFF	C3	Over Temp Warning	D3	Remote ON/OFF	
A4	Write Protect (WP)	B4	PS Present	C4	I <sup>2</sup> C Address (A0)	D4	DC OK	
A5	Remote Sense (+)	B5	SDA (I <sup>2</sup> C bus)	C5	I <sup>2</sup> C Address (A1)	D5	AC OK	
A6	Remote Sense (-)	B6	SCL (I <sup>2</sup> C bus)	C6	I <sup>2</sup> C Address (A2)	D6	SMBAlert	
P1-P4		Output Return				P5-P8		+12Vout

### Ordering Information

Please contact your OmniOn Energy Sales Representative for pricing, availability and optional features.

PRODUCT	DESCRIPTION	PART NUMBER
1600W Front-End	+12Vout Front-End, 3.3Vaux, with bezel and PMBus interface	CAR1612FPBCXZ01A
1600W Front-End	+12Vout Front-End, 5Vaux, with bezel and PMBus interface	CAR1612FPBC5Z01A
1600W Front-End	+12Vout Front-End, 3.3Vaux, reverse airflow, with bezel and PMBus interface	CAR1612FPBRXZ01A
1600W Front-End	+12Vout Front-End, 5Vaux, reverse airflow, with bezel and PMBus interface	CAR1612FPBR5Z01A

### Contact Us

For more information, call us at

+1-877-546-3243 (US)

+1-972-244-9288 (Int'l)

## Change History (excludes grammar & clarifications)

Revision	Date	Description of the change
3.3	12/09/2021	Updated as per template
3.4	12/14/2023	Updated as per OmniOn template

**OmniOn Power Inc.**

601 Shiloh Rd.  
Plano, TX USA

[omnionpower.com](http://omnionpower.com)

We reserve the right to make technical changes or modify the contents of this document without prior notice. OmniOn Power does not accept any responsibility for errors or lack of information in this document and makes no warranty with respect to and assumes no liability as a result of any use of information in this document.

We reserve all rights in this document and in the subject matter and illustrations contained therein. Any reproduction, disclosure to third parties or utilization of its contents – in whole or in parts – is forbidden without prior written consent of OmniOn Power. This document does not convey license to any patent or any intellectual property right. Copyright© 2023 OmniOn Power Inc. All rights reserved.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[OmniOn Power:](#)

[CAR1612FPBCXZ01A](#)