



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	9/4/14	D. CASTRO



MODEL NUMBER	LENGTH METERS [FEET]
TRD8RGMT2-01	1.0 [3.28]
TRD8RGMT2-02	2.0 [6.56]
TRD8RGMT2-03	3.0 [9.84]
TRD8RGMT2-05	5.0 [16.41]
TRD8RGMT2-10	10.0 [32.81]

NOTES:

CRUSH RESISTANCE (1 IN SQ. AREA): 1500 POUNDS, MIN.

TEMPERATURE RANGE: -40°C TO +80°C (-40°F TO +176°F)

CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.

CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

REGULATORY COMPLIANCE:
CE2011/65/EU (RoHS DIRECTIVE)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 [5.08] .XX = ±.02 [51] .XXX = ±.005 [13] PROJECTION 	APPROVALS	DATE	 45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845
	DRAWN BY D. FRISIELLO	9/26/13	
	CHECKED BY D. GUTTAUARO	9/26/13	
	APPROVED BY D. GALLAGHER	9/26/13	
CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY			CATEGORY TELECOM/MODULAR
COLOR VARIATIONS MAY OCCUR			PRODUCT DESCRIPTION IP68 RGRJ45 P/P ANOD TPE
SIZE A		FSCM NO. 43321	DWG. NO. TRD8RGMT2
SCALE: NONE		CAD FILE: TRD8RGMT2.SLDDRW	REV. A
		SHEET 1 OF 1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[infinite Electronics:](#)

[TRD8RGMT2-01](#) [TRD8RGMT2-03](#) [TRD8RGMT2-02](#) [TRD8RGMT2-05](#) [TRD8RGMT2-10](#)