

## Silicon Fast Recovery Diode

$V_{RRM} = 800 \text{ V} - 1000 \text{ V}$

$I_F = 85 \text{ A}$


### Features

- High Surge Capability
- Types from 800 V to 1000 V  $V_{RRM}$
- Not ESD Sensitive

### Note:

1. Standard polarity: Stud is cathode.
2. Reverse polarity (R): Stud is anode.
3. Stud is base.

DO-5 Package



Maximum ratings, at  $T_j = 25^\circ\text{C}$ , unless otherwise specified ("R" devices have leads reversed)

| Parameter                                            | Symbol     | Conditions                                        | FR85K(R)05 | FR85M(R)05 | Unit             |
|------------------------------------------------------|------------|---------------------------------------------------|------------|------------|------------------|
| Repetitive peak reverse voltage                      | $V_{RRM}$  |                                                   | 800        | 1000       | V                |
| RMS reverse voltage                                  | $V_{RMS}$  |                                                   | 560        | 700        | V                |
| DC blocking voltage                                  | $V_{DC}$   |                                                   | 800        | 1000       | V                |
| Continuous forward current                           | $I_F$      | $T_C \leq 100^\circ\text{C}$                      | 85         | 85         | A                |
| Surge non-repetitive forward current, Half Sine Wave | $I_{F,SM}$ | $T_C = 25^\circ\text{C}$ , $t_p = 8.3 \text{ ms}$ | 1369       | 1369       | A                |
| Operating temperature                                | $T_j$      |                                                   | -55 to 150 | -55 to 150 | $^\circ\text{C}$ |
| Storage temperature                                  | $T_{stg}$  |                                                   | -55 to 150 | -55 to 150 | $^\circ\text{C}$ |


Electrical characteristics, at  $T_j = 25^\circ\text{C}$ , unless otherwise specified

| Parameter             | Symbol | Conditions                                        | FR85K(R)05 | FR85M(R)05 | Unit          |
|-----------------------|--------|---------------------------------------------------|------------|------------|---------------|
| Diode forward voltage | $V_F$  | $I_F = 85 \text{ A}$ , $T_j = 25^\circ\text{C}$   | 1.3        | 1.3        | V             |
| Reverse current       | $I_R$  | $V_R = 100 \text{ V}$ , $T_j = 25^\circ\text{C}$  | 25         | 25         | $\mu\text{A}$ |
|                       |        | $V_R = 100 \text{ V}$ , $T_j = 125^\circ\text{C}$ | 20         | 20         | mA            |

### Recovery Time


|                               |          |                                                                              |     |     |    |
|-------------------------------|----------|------------------------------------------------------------------------------|-----|-----|----|
| Maximum reverse recovery time | $T_{RR}$ | $I_F = 0.5 \text{ A}$ , $I_R = 1.0 \text{ A}$ ,<br>$I_{RR} = 0.25 \text{ A}$ | 500 | 500 | nS |
|-------------------------------|----------|------------------------------------------------------------------------------|-----|-----|----|

Figure .1-Typical Forward Characteristics




Instantaneous Forward Voltage - Volts

Figure .2-Forward Derating Curve




Case Temperature - °C

Figure .3-Peak Forward Surge Current




Number Of Cycles At 60Hz - Cycles

Figure .4-Typical Reverse Characteristics



## Package dimensions and terminal configuration

Product is marked with part number and terminal configuration.



|   | Inches      |       | Millimeters |       |
|---|-------------|-------|-------------|-------|
|   | Min         | Max   | Min         | Max   |
| A | 1/4 -28 UNF |       |             |       |
| B | 0.669       | 0.687 | 17.19       | 17.44 |
| C | -----       | 0.794 | -----       | 20.16 |
| D | -----       | 1.020 | -----       | 25.91 |
| E | 0.422       | 0.453 | 10.72       | 11.50 |
| F | 0.115       | 0.200 | 2.93        | 5.08  |
| G | -----       | 0.460 | -----       | 11.68 |
| J | -----       | 0.280 | -----       | 7.00  |
| K | 0.236       | ----- | 6.00        | ----- |
| M | -----       | 0.589 | -----       | 14.96 |
| N | -----       | 0.063 | -----       | 1.60  |
| P | 0.140       | 0.175 | 3.56        | 4.45  |

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[GeneSiC Semiconductor:](#)

[FR85MR05](#)